

10		9	8		7	6		5	4		3	2	1								
F	MATERIAL NUMBER	ALTERNATE NUMBER	WIRE SIZE AWG	INSULATION COLOR	CONNECTOR ID	MAX. WIRE INSUL. DIA.		LENTH "L2"	TAPE HEIGHT "T"	DESCRIPTION											
	STANDARD END		FUNNEL END																		
	I92020010	AS-932	22-18	LIGHT RED	.061	.161	.147	1.07	----	LOOSE PIECE											
	I92020011	AS-932-DK	22-18	DARK RED	.061	.161	.147	1.07	----	LOOSE PIECE											
	I92020012	AS-932-DKT	22-18	DARK RED	.061	.161	.147	1.07	.480	TAPE MOUNTED											
	I92020026	BS-942	16-14	LIGHT BLUE	.087	.199	.185	1.07	----	LOOSE PIECE											
	I92020030	BS-942T	16-14	LIGHT BLUE	.087	.199	.185	1.07	.480	TAPE MOUNTED											
	I92020027	BS-942-DK	16-14	DARK BLUE	.087	.199	.185	1.07	----	LOOSE PIECE											
	I92020029	BS-942-DKT	16-14	DARK BLUE	.087	.199	.185	1.07	.480	TAPE MOUNTED											
	I92020028	BS-942-DKBT	16-14	DARK BLUE	.087	.199	.185	1.07	.480	TAPE MOUNTED LARGE REEL											
E	I92020131	BS-942-B	16-14	BLUE	.087	.199	.185	1.07	----	LOOSE PIECE											
	I92020130	BS-932-BBT	16-14	BLUE	.087	.199	.185	1.07	.480	TAPE MOUNTED LARGE REEL											
	I92020045	CS-952	12-10	YELLOW	.138	.276	.262	1.15	----	LOOSE PIECE											
	I92020046	CS-952-DK	12-10	DARK YELLOW	.138	.276	.262	1.15	----	LOOSE PIECE											
	I92020047	CS-952-DKT	12-10	DARK YELLOW	.138	.276	.262	1.15	.440	TAPE MOUNTED											
D	I92020048	CS-952-DKBT	12-10	DARK YELLOW	.138	.276	.262	1.15	.440	TAPE MOUNTED LARGE REEL											
	I92020141	CS-952 BULK	12-10	YELLOW	.138	.276	.262	1.15	----	BULK PACKED, 2500 PER PACKAGE											
	I92020142	CS-952-DK BULK	12-10	DARK YELLOW	.138	.276	.262	1.15	----	BULK PACKED, 2500 PER PACKAGE											
	"L" STANDARD END "ID" FUNNEL END "T" PARTS ON TAPE CUSTOMER DRAWING																				
NOTES: 1. MATERIAL: COPPER. 2. PLATING: ELECTRON-TIN. 3. INSULATION: 6/6 NYLON DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°<table><tr><th></th><th>INCH</th><th>METRIC</th></tr><tr><td>3 PLACE</td><td>± .005</td><td>± ---</td></tr><tr><td>2 PLACE</td><td>± .01</td><td>± 0.13</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± 0.25</td></tr></table> DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DRWG. BYHEBCHK'D. BYRWDAPP'D. BYRWDSCALENO:NE FILE NAMESD I9202001 DGN REVISE ONLY ON CAD SYSTEM TITLE FUNNEL ENTRY SEAMLESS NYLAKRIMP BUTT CONNECTOR molex ETC INC. PINELLAS PARK, FLA. 33781 U.S.A. SHEET NO. 1 OF 1 DATE 00/07/18 PART NO. SEE TABLE DRWG. NO. SD-I9202-001 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX-ETC INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION. DIV. ET SIZE B											INCH	METRIC	3 PLACE	± .005	± ---	2 PLACE	± .01	± 0.13	1 PLACE	± ---	± 0.25
	INCH	METRIC																			
3 PLACE	± .005	± ---																			
2 PLACE	± .01	± 0.13																			
1 PLACE	± ---	± 0.25																			
10		9	8		7	6		5	4		3	2	1								