



In-Sure™ Push-In, 5-Port



Models Models Wire Sizes

	Model	Color	Ports	Quantity	Catalog Number
	32	Red	2	Box of 100	30-1032
				Jar of 300	30-1032J
				Box of 5000	30-1632
	33	Orange	3	Box of 100	30-1033
				Jar of 250	30-1033J
				Box of 5000	30-1633
	34	Yellow	4	Box of 100	30-1034
				Jar of 200	30-1034J
				Box of 5000	30-1634
	39	Blue	3	Box of 50	30-1039
				Jar of 150	30-1039J
				Box of 5000	30-1639
	87	Gray	5	Jar of 150	30-087J
				Box of 1000	30-187
				Box of 5000	30-687
	88	Blue	6 stacked	Jar of 100	30-088J
				Box of 1000	30-188

In-Sure™ Push-In, 5-Port

				Box of 5000	30-688
	90	Black	8	Jar of 100	30-090J
				Box of 1000	30-190
				Box of 5000	30-690

©2012 IDEAL INDUSTRIES, INC. All rights reserved.



In-Sure™ Push-In, 5-Port



<u>Models</u>	<u>Models</u>	<u>Wire Sizes</u>	
Models	Solid	Stranded	Stranded (Tin Bonded)
32, 33, 34	#12 AWG - #20 AWG	#12 AWG - #16 AWG (19 strand or less) #18 AWG (7 strand)	#14 AWG - #18 AWG (19 strand or less)
39	#10 AWG - #14 AWG	#10 AWG - #12 AWG (19 strand or less)	#10 AWG - #14 AWG (19 strand or less)
87, 88, 90	#12 AWG - #20 AWG	#14 AWG - #16 AWG (19 strand or less) #18 AWG (7 strand or less)	#12 AWG - #14 AWG (19 strand or less) #16 AWG (26 strand or less) 318 AWG (16 strand or less)

©2012 IDEAL INDUSTRIES, INC. All rights reserved.