



Mounting Dimensions for Double Lever Panel Bases



HOUSING SERIES					CAT. NO.	DIMENSIONS ARE IN INCHES / (MILLIMETERS)						
A, B, T, K	C, V	D	DD	M		A	B	C	D	E	F	G
A32		D50			PB132A	3.62 / (92)	4.02 / (102)	5.04 / (128)	1.65 / (28)	2.24 / (57)	2.76 / (70)	1.10 / (28)
B10, T10	V3		DD42	M3	PB110E	3.27 / (83)	3.66 / (93)	4.33 / (110)	1.26 / (32)	1.69 / (43)	2.28 / (58)	1.06 / (27)
B16, T16	C6, V6	D40	DD72	M5	PB116E	4.05 / (103)	4.49 / (114)	5.16 / (131)	1.26 / (32)	1.69 / (43)	2.28 / (58)	1.06 / (27)
B24, T24, K12	V10, V16	D64	DD108	M7	PB124E	5.12 / (130)	5.51 / (140)	6.19 / (157)	1.26 / (32)	1.69 / (43)	2.28 / (58)	1.06 / (27)
B32	C12	D80	DD144		PB132E	4.33 / (110)	4.88 / (124)	5.28 / (134)	2.56 / (65)	3.11 / (79)	3.62 / (92)	1.18 / (30)

Mounting Dimensions for Single Lever Panel Bases



HOUSING SERIES					CAT. NO.	DIMENSIONS ARE IN INCHES / (MILLIMETERS)						
A, B, T, K	C, V	D	DD	M		A	B	C	D	E	F	G
A3, A4		D7, D8			PB303A (P) ▶	—	1.10 / (28)	1.34 / (34)	1.18 / (30)	1.50 / (38)	1.67 / (42.5)	.95 / (24)
					PB403A (P) ▶	—	1.10 / (28)	1.38 / (35)	1.18 / (30)	1.58 / (40)	1.85 / (47)	.95 / (24)
					PB503A (P)	1.10 / (28)	1.59 / (40.5)	1.00 / (25.5)	1.42 / (36)	1.18 / (30)	1.50 / (38)	
A10		D15			PB310A	2.76 / (70)	3.19 / (81)	—	.68 / (17.5)	1.20 / (30.5)	1.93 / (49)	1.02 / (26)
					PB410A	2.76 / (70)	3.19 / (81)	—	.68 / (17.5)	1.20 / (30.5)	2.95 / (75)	1.02 / (26)
A16	D25				PB316A	3.39 / (86)	3.78 / (96)	—	.68 / (17.5)	1.20 / (30.5)	1.93 / (49)	1.02 / (26)
					PB416A	3.39 / (86)	3.78 / (96)	—	.68 / (17.5)	1.20 / (30.5)	2.95 / (75)	1.02 / (26)
B6, T6			DD24	M2	PB306	2.76 / (70)	3.15 / (80)	—	1.26 / (32)	1.69 / (43)	2.56 / (65)	1.06 / (27)
					PB406	2.76 / (70)	3.15 / (80)	—	1.26 / (32)	1.69 / (43)	3.54 / (90)	1.06 / (27)
B10, T10	V3		DD42	M3	PB310	3.27 / (83)	3.66 / (93)	—	1.26 / (32)	1.69 / (43)	2.64 / (67)	1.06 / (27)
					PB410	3.27 / (83)	3.66 / (93)	—	1.26 / (32)	1.69 / (43)	3.62 / (92)	1.06 / (27)
B16, T16	C6, V6	D40	DD72	M5	PB316	4.06 / (103)	4.49 / (114)	—	1.26 / (32)	1.69 / (43)	2.64 / (67)	1.06 / (27)
					PB416	4.06 / (103)	4.49 / (114)	—	1.26 / (32)	1.69 / (43)	3.62 / (92)	1.06 / (27)
B24, T24, K12	V10, V16	D64	DD108	M7	PB324	5.12 / (130)	5.51 / (140)	—	1.26 / (32)	1.69 / (43)	2.64 / (67)	1.06 / (27)
					PB424	5.12 / (130)	5.51 / (140)	—	1.26 / (32)	1.69 / (43)	3.62 / (92)	1.06 / (27)
B48, K24 V32	V20, V26, V32	D128	DD216		PB348	5.83 / (148)	6.50 / (165)	—	2.76 / (70)	3.54 / (90)	6.18 / (157)	1.61 / (41)
					PB448	5.83 / (148)	6.50 / (165)	—	2.76 / (70)	3.54 / (90)	6.81 / (173)	1.61 / (41)

► SUFFIX: A - ALUMINUM, P - PLASTIC