

J

I

H

G

F

E

D

C

B

A

13

12

11

10

9

8

7

6

5

4

3

2

1

J

I

H

G

F



E

D

C

B


A



MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
1201140056	BTY603P-FBA	-

VOLTAGE RATING	10-30 VDC
AMPERAGE RATING PER PORT	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 90°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E46237
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
2	O-RING	VITON	RED
3	RECEPTACLE SHELL	BRASS	NICKEL PLATED
4	HOUSING	PBT	YELLOW
5	LABEL	ABS	WHITE
6	LENS	NYLON	CLEAR

DESCRIPTION EC NO: WEU2010-0445 DRWN: LSTEMMLE 2010/03/19 CHKD: NSTAUDIG APPR: NSTAUDIG 2010/03/23		DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 FIRST ANGLE PROJECTION			
					mm	INCH	DRAWN BY LSTEMMLE	DATE 2010/03/19	MICRO-CHANGE MPIS 6 PORT PNP TWIN PORT 5P FIELD ATTACHABLE					
			 = 0	4 PLACES	± ---	± ---	CHECKED BY FP	DATE 2010/03/22						
			 = 0	3 PLACES	± ---	± ---	APPROVED BY	DATE				 MOLEX INCORPORATED		
				2 PLACES	± ---	± .01	NSTAUDIG	2010/03/22						
				1 PLACE	± 0.3	± ---	MATERIAL NO.	DOCUMENT NO.	SHEET NO.					
				ANGULAR ± --- °			SEE TABLE		SD-120114-066			1 OF 1		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A2	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
			1		REV									

13

12

11

10

9

8

7

6

5

4

3

2

1