




AMGIS

CT Series • Current Sensor for 50/60 Hz

Part Number	CT 1030
Customer	
Product Type	Current transformer

SCHEMATIC:



ELECTRICAL SPECIFICATION:

— Rated input current	: 30Amps
— Primary to Secondary isolation	: 2500VAC
— Operating frequency	: 50 / 60Hz
— Turns ratio	: 1:1000
— DCR	: 48Ω
— I_o @ $V_{rms} = 4.38V$	: 644μArms
— Ratio correction factor (RCF*)	: 1.020 @10% (Multiply current reading by this factor to compensate for transformer losses)
— Operating temperature range	: -55°C to 120°C
— Flammability rating	: UL 94V0

Volt/Amp at rated I_p for different loads			
100Ω	500Ω	2000Ω	5000Ω
0.10	0.47	0.95	1.16

LOAD TEST DETAILS:

Rated I_p =30A
 R_L =100Ω/0.09W
 U_s =3.0V


MARKING INFORMATION:

AMGIS
YY/WW CT1030

Trafo Weight:

0.036Kg/pc

MECHANICAL DIMENSIONS:



All dimensions are in mm
Linear dimensional tolerance ± 0.2 mm

AMGIS, LLC * 10830 Kinghurst Dr. Houston, TX 77099
Phone: 832-775-1319 * Fax: 281-933-9067* email: sales@amgistoroids.com
Toll Free: 877-762-6447 * www.amgistoroids.com