





LOC	DIST	REVISIONS ÄNDERUNGEN						
		P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD	
A1	-							
PROJEKT NR.: EGLPC00034		M1	PINCH RING SEAL-INMOLDED. ASSY CHANGED TO GEN. 4			06DEC2012	V.P	T.J



SECTION A-A
SCHNITT A-A



-3 AS SHOWN
-3 WIE GEZEICHNET



SCALE 2:1 / M 2:1

[illegible]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 25-JAN-02 E. WERNER CHK 25-JAN-02 H. SCHERER APVD 25-JAN-02 G. FELDMEIER		 TE Connectivity	
DIMENSIONS: MASSE IN mm (mm)		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEIN TOLERANZEN		NAME PHOTOVOLTAIK CONNECTOR 1 POS. PHOTOVOLTAIK STECKVERBINDER 1 POL. -	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES/WINKEL ± FINISH/OBERFLÄCHE/FARBE -			
MATERIAL -		PRODUCT SPEC Produktspez. 108-18701 APPLICATION SPEC Verarbeitungspez. 114-18488-1		SIZE A2	
		WEIGHT Gewicht -		CAGE CODE 00779	
				DRAWING NO. ZEICHNUNGS-NR. C=1394462	
				RESTRICTED TO NUR FUER -	
		Customer Drawing		SCALE MASSSTAB 2:1	
		/KUNDENZEICHNUNG		SHEET BLATT 1 OF 3	
				REV M1	

4

3

2

1

THIS DRAWING IS UNPUBLISHED
VERTRAULICHE UNVERÖFFENTLICHTE ZEICHNUNG

RELEASED FOR PUBLICATION
FREI FÜR VERÖFFENTLICHUNG

16-MAR- 2006

MATED WITH:
PASSEND ZU:

1394461

LOC
A I

DIST
-

REVISIONS
ÄNDERUNGEN
DESCRIPTION
BESCHREIBUNG

DATE

DWN

APVD

PROJECT NR.:
EGLPC00034

-

SEE SHEET 1

-

-

-

1

PACKAGING INSTRUCTION:

100 PIECES SOCKET HOUSINGS (ITEM NO. 1 OR 2) AND PINCH RING SEAL, ASSY (ITEM NO. 3) OR PINCH RING SEAL INMOLDED ASSY (ITEM NO. 4) PREASSEMBLED WITH CABLE SCREW JOINT (ITEM NO. 5).
PREASSEMBLED PARTS PACKAGED IN ESD PLASTIC BAG (ITEM NO. 13).
ESD PLASTIC BAG (ITEM NO. 13) PROVIDED WITH LABEL AND LABEL MARKED WITH PART NUMBER, QUANTITY AND DESCRIPTION.

SOCKET CONTACT ASSY'S (ITEM NO. 6, 7 OR 8) PACKAGED ACCORDING TO 2 .

2

PACKAGING INSTRUCTION:

100 PIECES OF EACH PART PACKAGED IN ZIP LOCK BAG (ITEM NO. 12).
ZIP LOCK BAG (ITEM NO. 12) PROVIDED WITH LABEL AND LABEL MARKED WITH PART NUMBER, QUANTITY AND DESCRIPTION.

3

PACKAGING UNIT:

ALL COMPONENTS OF EACH DASH-NUMBER PACKAGED ACCORDING TO 1 AND 2
PACKAGED IN CORRUGATED SHIPPING BOX.
PUT INSIDE ON TOP CORRUGATED SHIPPING BOX INSTRUCTION SHEET (ITEM NO. 14).
CORRUGATED SHIPPING BOX PROVIDED WITH LABEL AND LABEL MARKED WITH PART NUMBER, QUANTITY AND DESCRIPTION.

4

O-RINGS (ITEM NO. 9 OR 10) ASSEMBLED ON SOCKET HOUSING (ITEM NO. 1 OR 2)

5

FOR CABLE DIAMETER 4.5mm TO 6.9mm

6

FOR CABLE DIAMETER 5.5mm TO 7.8mm

7

TIGHTENING TORQUE SEE APPLICATION SPECIFICATION 114-18488-1

8

USE ONLY SOLAR CABLE TYPE: OKONITE USE-2

9

LABEL (ITEM NO. 11), ZIP LOCK BAG (ITEM NO. 12), ESD PLASTIC BAG (ITEM NO. 13), AND INSTRUCTION SHEET (ITEM NO. 14) NOT SHOWN

1

VERPACKUNGSANWEISUNG:

100 STÜCK BUCHSENGEHÄUSE (POS. 1 ODER 2) UND KLEMMKORB DICHTUNG, ASSY (POS. 3) BZW. KLEMMKORB DICHTUNG UMSPRITZT, ASSY (POS. 4) VORASSEMBLIERT MIT KABELVERSCHRAUBUNG (POS. 5).
VORASSEMBLIERTE TEILE VERPACKT IN ESD KUNSTSTOFF-BEUTEL (POS. 13).
ESD KUNSTSTOFF-BEUTEL (ITEM NO. 13) MIT ETIKETT VERSEHEN UND ETIKETT MIT TEILENUMMER, STÜCKZAHL UND BEZEICHNUNG BESCHRIFTET.

BUCHSENKONTAKT ASSY'S (POS. 6, 7, ODER 8) VERPACKT GEMÄSS 2 .

2

VERPACKUNGSANWEISUNG:

100 STÜCK VON JEDEM TEIL IM MINIGRIP-BEUTEL (POS. 12) VERPACKT.
MINIGRIP-BEUTEL (ITEM NO. 12) MIT ETIKETT VERSEHEN UND ETIKETT MIT TEILENUMMER, STÜCKZAHL UND BEZEICHNUNG BESCHRIFTET.

3

VERPACKUNGSEINHEIT:

ALLE KOMPONENTEN EINER STRICHVARIANTE VERPACKT GEMÄSS 1 UND 2
IN VERSANDKARTON VERPACKT.
VERSANDKARTON VERARBEITUNGSANWEISUNG (POS. 14) OBENAUF GELEGT.
VERSANDKARTON MIT ETIKETT VERSEHEN UND ETIKETT MIT TEILENUMMER, STÜCKZAHL UND BEZEICHNUNG BESCHRIFTET.

4

O-RINGE (POS. 9 ODER 10) AUF BUCHSENSTECKER (POS. 1 ODER 2) MONTIERT

5

FÜR LEITUNGSDURCHMESSER 4.5mm BIS 6.9mm

6

FÜR LEITUNGSDURCHMESSER 5.5mm BIS 7.8mm

7

ANZUGSDREHMOMENT SIEHE VERARBEITUNGSSPEZIFIKATION 114-18488-1

8

NUR SOLARKABEL TYP: OKONITE USE-2 VERWENDEN

9

ETIKETT (POS. 11), MINIGRIP-BEUTEL (POS. 12), KUNSTSTOFF-BEUTEL (POS. 13), UND VERARBEITUNGSANWEISUNG (POS. 14) NICHT DARGESTELLT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
E. WERNER
CHK
H. SCHERER
APVD
G. FELDMEIER

25-JAN-02
25-JAN-02
25-JAN-02

DIMENSIONS :
MASSEINHEITEN:
(MM)

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES/WINKEL ±
FINISH/OBERFLÄCHE/FARBE

MATERIAL
-

PRODUCT SPEC
PRODUKTSPEZ.
108-18701

APPLICATION SPEC
VERARBEITUNGSSPEZ.
114-18488-1

WEIGHT
GEWICHT
-

Customer Drawing

NAME
PHOTOVOLTAIK CONNECTOR 1 POS.
PHOTOVOLTAIK STECKVERBINDER 1 POL.
-

SIZE
A2

CAGE CODE
00779

DRAWING NO.
ZEICHNUNGS-NR.
1394462

RESTRICTED TO
NUR FÜR
-

SCALE
MASSSTAB
2:1

SHEET
BLATT
2

OF
VON
3

REV.
M1

1471-9 (3/11)

D

C

B


A

D


C

B




A




SECTION A-A
SCHNITT A-A





4- -8 PREASSEMBLED AS SHOWN
4- -8 VORASSEMBLIERT WIE GEZEICHNET




SECTION A-A
SCHNITT A-A



4- -9 PREASSEMBLED AS SHOWN
4- -9 VORASSEMBLIERT WIE GEZEICHNET



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. WERNER 25-JAN-02	 TE Connectivity			
DIMENSIONS: MASSEINHEITEN: (MM)		CHK H. SCHERER 25-JAN-02				
		APVD G. FELDMEIER 25-JAN-02	NAME PHOTOVOLTAIK CONNECTOR 1 POS. PHOTOVOLTAIK STECKVERBINDER 1 POL.			
		PRODUCT SPEC PRODUKTSPEZ. 108-18701	SIZE A2			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN		APPLICATION SPEC VERARBEITUNGSSPEZ. 114-18488-1	CAGE CODE 00779		DRAWING NO. ZEICHNUNGS-NR. C-1394462	RESTRICTED TO NUR FÜR -
MATERIAL -		WEIGHT GEWICHT -	Customer Drawing		SCALE MASSSTAB 2:1	SHEET BLATT 3 OF VON 3
			/KUNDENZEICHNUNG		REV M1	