







## Dimensions: mm (In.)



## Function

4P SPST  
(LED)Led rating @ 10MA V<sub>f</sub>=1.85

## Cut-out



## Terminal



.250" Sq.

## Electrical Specifications:

- Rating: 16A/125VAC; 10A/250VAC
- Contact resistance: 50mΩ max.
- Insulation resistance: 500VDC 100MΩ min.
- Dielectric strength: 1500VAC for 1 min.

## Note:

- RoHS Compliant

| Mouser Stock No.    | Button                 |
|---------------------|------------------------|
| 103-R13-205L-01G-EV | Green Spot Illuminated |
| 103-R13-205L-01R-EV | Red Spot Illuminated   |

**Illuminated Rocker Switches**  
103-R13-205L-01G-EV, 103-R13-205L-01R-EV

**Mountain**  
**Switch**

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-R13-205L-01G-EV](#) [103-R13-205L-01R-EV](#)