


# Screwdrivers, Nut Drivers and Accessories

Offering a variety of tip types, hex sizes, shaft lengths, and handle designs, Klein has the screwdrivers and nut drivers professionals demand to get the job done with comfort and ease.




For Professionals...  
Since 1857™

## Introduction

Extra-quality features have made the Klein name famous for hand tools – features that assure greater convenience, comfort and efficiency in use, plus exceptional strength and durability.

All Klein drivers are made of the highest quality tempered steel and carefully heat-treated for maximum strength. Shafts have integral flanges that provide an extra-strong, torque-proof anchor in the handle. Strong, durable black tips are forged and precision ground with square edges to fit screw openings securely. They resist slip-page and provide positive turning action.

Cushion-Grip screwdrivers feature super-comfortable, sure-grip handles on top-quality blades for the professional. All Klein screwdrivers meet or exceed applicable ANSI and MIL specifications.



## Using Screwdrivers and Nut Drivers

The size of the screw or nut and the type of opening it has determines which driver to use. Here are a few tips on how to use a driver that can be of benefit, because screwdrivers are the most often misused and abused hand tools of all.

### 1. Never use a driver to do another tool's job.

Using a driver as a pry bar, scraper, or a chisel can ruin the tool, spoil the work and cause injury.

### 2. Never push a driver beyond its capacity.

Make a pilot hole for the screw for easier driving. Use square-shank drivers for heavy work.

### 3. Never expose a driver to excessive heat.

Direct flame can draw the temper from the metal, weakening and possibly warping it, making it unsafe and inefficient to use.

### 4. Never use a driver at an angle to the screw.

Always keep the shank perpendicular to the screw head. Driving at an angle or using a point that is too small can spoil the screw or slip and damage the work.

### 5. Never depend on a driver's handle or covered blade to insulate you from electricity.

Plastic and Cushion-Grip handles are intended only to provide a firm, comfortable grip. Insulated blades are intended only as a protective measure against shorting out components. Only use insulated tools that are marked with the official international 1000-volt rating symbol if there is any chance that the tool will make contact with an energized source.

### 6. Discard damaged or worn drivers.

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

# MAGNETIZER

**NEW!**

Quickly **magnetize** and **demagnetize** screwdriver tips and bits using powerful rare-earth magnets

#### To magnetize screwdriver:

Insert screwdriver shaft fully into magnetizing slot; avoid rotating shaft while drawing out slowly

#### To demagnetize screwdriver:

Insert shaft fully into smallest demagnetizing slot that fits; avoid rotating shaft while drawing out slowly




| Cat. No. | Overall Length     | Overall Height   | Overall Width     | Weight        |
|----------|--------------------|------------------|-------------------|---------------|
| MAG2     | 2-13/64" (56.0 mm) | 45/64" (17.9 mm) | 1-3/32" (26.2 mm) | 1.1 oz (32 g) |



## Fits these drivers

- #3 Phillips
- 1/4" Keystone (round or square shank)
- 5/16" Cabinet
- #2 Phillips Insulated
- 1/4" Cabinet Insulated
- Most precision screwdrivers



See page 310 for additional information on warnings.



## Cushion-Grip Screwdrivers

**Meets or exceeds** applicable ASME / ANSI specifications

**Tip-Ident®** quickly identifies the type of screwdriver and tip orientation

**Precision-machined** tip for exact fit

**Heat-treated, premium chrome-plated shank** for smooth feel and corrosion resistance

**Integral flanges** inside handle provide solid, twist-resistant blade anchor

**Cushion-Grip** handle allows for greater torque and comfort

**MADE IN USA**

## Color-Coded Cushion-Grip Screwdrivers

Includes core Cushion-Grip screwdriver features plus:

- Color-coded handle ends for quick and easy identification
- TORX® tip drive cuts slippage, saves fasteners and transmits more torque to the work



660

| Cat. No. | Tip Type         | Shank Type | Shank Length     | Color Code | Overall Length     | Weight            |
|----------|------------------|------------|------------------|------------|--------------------|-------------------|
| 660      | #0 Square-Recess | Round      | 4" (101.6 mm)    | Yellow     | 7-3/4" (196.9 mm)  | 0.20 lb (0.09 kg) |
| 661      | #1 Square-Recess | Round      | 4" (101.6 mm)    | Green      | 7-3/4" (196.9 mm)  | 0.20 lb (0.09 kg) |
| 662      | #2 Square-Recess | Round      | 4" (101.6 mm)    | Red        | 8-1/4" (209.6 mm)  | 0.30 lb (0.14 kg) |
| 663      | #3 Square-Recess | Round      | 4" (101.6 mm)    | Black      | 8-1/4" (209.6 mm)  | 0.30 lb (0.14 kg) |
| 665      | #1 Square-Recess | Round      | 8" (203.2 mm)    | Green      | 11-3/4" (298.5 mm) | 0.30 lb (0.14 kg) |
| 666      | #2 Square-Recess | Round      | 8" (203.2 mm)    | Red        | 12-1/4" (311.2 mm) | 0.40 lb (0.18 kg) |
| 667      | #3 Square-Recess | Round      | 8" (203.2 mm)    | Black      | 12-1/4" (311.2 mm) | 0.40 lb (0.18 kg) |
| 668      | #1 Square-Recess | Round      | 1-1/2" (38.1 mm) | Green      | 3-7/16" (87.3 mm)  | 0.15 lb (0.07 kg) |
| 19542    | T15 TORX®        | Round      | 4" (101.6 mm)    | Yellow     | 8-5/16" (211.1 mm) | 0.20 lb (0.09 kg) |
| 19543    | T20 TORX®        | Round      | 4" (101.6 mm)    | Green      | 8-5/16" (211.1 mm) | 0.25 lb (0.11 kg) |
| 19544    | T25 TORX®        | Round      | 4" (101.6 mm)    | Blue       | 8-5/16" (211.1 mm) | 0.25 lb (0.11 kg) |
| 19545    | T27 TORX®        | Round      | 4" (101.6 mm)    | Brown      | 8-5/16" (211.1 mm) | 0.25 lb (0.11 kg) |
| 19546    | T30 TORX®        | Round      | 4" (101.6 mm)    | Red        | 8-5/16" (211.1 mm) | 0.25 lb (0.11 kg) |

TORX® is a registered trademark of Acument Intellectual Properties, LLC.

| Cat. No. | Set Contains                            | Weight          |
|----------|-----------------------------------------|-----------------|
| 19555    | TORX® Cushion-Grip Screwdriver Set 5 Pc | 1.2 lb (0.5 kg) |

| Cat. No. | Description                       |
|----------|-----------------------------------|
| 19542    | T15 TORX® Screwdriver Round Shank |
| 19543    | T20 TORX® Screwdriver Round Shank |
| 19544    | T25 TORX® Screwdriver Round Shank |
| 19545    | T27 TORX® Screwdriver Round Shank |
| 19546    | T30 TORX® Screwdriver Round Shank |

| Cat. No. | Set Contains                          | Weight          |
|----------|---------------------------------------|-----------------|
| 85664    | 4 Piece Square Recess Screwdriver Set | 1.5 lb (0.7 kg) |

| Cat. No. | Description                           |
|----------|---------------------------------------|
| 660      | #0 Square Recess Screwdriver 4" Shank |
| 661      | #1 Square Recess Screwdriver 4" Shank |
| 662      | #2 Square Screwdriver 4" Round Shank  |
| 663      | #3 Square Recess Screwdriver 4" Shank |

## Miniature Screwdrivers

Includes core Cushion-Grip screwdriver features

| Cat. No. | Tip Type                 | Shank Type | Shank Length   | Overall Length     | Weight           |
|----------|--------------------------|------------|----------------|--------------------|------------------|
| 604-3    | #0 Phillips              | Round      | 3" (76.2 mm)   | 5-3/4" (146.1 mm)  | 0.64 oz (18.1 g) |
| 606-2    | 1/16" (1.59 mm) Keystone | Round      | 2" (50.8 mm)   | 4-3/4" (120.7 mm)  | 0.48 oz (13.6 g) |
| 607-3    | 3/32" (2.4 mm) Cabinet   | Round      | 3" (76.2 mm)   | 5-3/4" (146.1 mm)  | 0.64 oz (18.1 g) |
| 607-4    | 3/32" (2.4 mm) Cabinet   | Round      | 4" (101.6 mm)  | 6-3/4" (171.5 mm)  | 0.64 oz (18.1 g) |
| 608-2    | 1/8" (3.2 mm) Cabinet    | Round      | 2" (50.8 mm)   | 4-3/4" (120.7 mm)  | 0.48 oz (13.6 g) |
| 608-3    | 1/8" (3.2 mm) Cabinet    | Round      | 3" (76.2 mm)   | 5-3/4" (146.1 mm)  | 0.64 oz (18.1 g) |
| 608-4    | 1/8" (3.2 mm) Cabinet    | Round      | 4" (101.6 mm)  | 6-3/4" (171.5 mm)  | 0.80 oz (22.7 g) |
| 608-6    | 1/8" (3.2 mm) Cabinet    | Round      | 6" (152.4 mm)  | 8-3/4" (222.3 mm)  | 0.80 oz (22.7 g) |
| 608-8    | 1/8" (3.2 mm) Cabinet    | Round      | 8" (203.2 mm)  | 10-3/4" (273.1 mm) | 0.80 oz (22.7 g) |
| 608-10   | 1/8" (3.2 mm) Cabinet    | Round      | 10" (254.0 mm) | 12-3/4" (323.9 mm) | 0.80 oz (22.7 g) |

| Cat. No. | Set Contains                           | Weight            |
|----------|----------------------------------------|-------------------|
| 85484    | Mini Cushion-Grip Screwdriver Set 4 Pc | 0.14 lb (0.06 kg) |

| Cat. No. | Description                            |
|----------|----------------------------------------|
| 604-3    | #0 Phillips Mini Screwdriver 3" Shank  |
| 606-2    | 1/16" Keystone Tip Mini Screwdriver 2" |
| 607-3    | 3/32" Cabinet Tip Mini Screwdriver 3"  |
| 608-3    | 1/8" Cabinet Tip Mini Screwdriver 3"   |



## Cushion-Grip Screwdrivers

### Cushion-Grip Screwdrivers

Includes core Cushion-Grip screwdriver features plus:

- Narrow cabinet-tip permits blade access where space is limited
- Precision machined combo-tip designed for combination head screws
- Precision machined Phillips tip provides a more consistent geometric symmetry than conventional Phillips screwdrivers to accurately fit and torque without slippage
- Heavy-duty square shank and hex bolster allows wrench-assisted turning
- Bolster reinforces shank for hard use



| Cat. No.                           | Tip Type                | Shank Type | Shank Length     | Overall Length       | Weight            |
|------------------------------------|-------------------------|------------|------------------|----------------------|-------------------|
| 600-1                              | 5/16" (7.9 mm) Cabinet  | Round      | 1-1/2" (38.1 mm) | 3-7/16" (87.3 mm)    | 0.10 lb (0.05 kg) |
| 601-3                              | 3/16" (4.8 mm) Cabinet  | Round      | 3" (76.2 mm)     | 6-3/4" (171.5 mm)    | 0.10 lb (0.05 kg) |
| 601-4                              | 3/16" (4.8 mm) Cabinet  | Round      | 4" (101.6 mm)    | 7-3/4" (196.9 mm)    | 0.15 lb (0.07 kg) |
| 601-6                              | 3/16" (4.8 mm) Cabinet  | Round      | 6" (152.4 mm)    | 9-3/4" (247.7 mm)    | 0.15 lb (0.07 kg) |
| 601-8                              | 3/16" (4.8 mm) Cabinet  | Round      | 8" (203.2 mm)    | 11-3/4" (298.5 mm)   | 0.20 lb (0.09 kg) |
| 601-10                             | 3/16" (4.8 mm) Cabinet  | Round      | 10" (254.0 mm)   | 13-3/4" (349.3 mm)   | 0.20 lb (0.09 kg) |
| 7314                               | #1 Combo                | Round      | 4" (101.6 mm)    | 8-11/32" (211.9 mm)  | 0.30 lb (0.14 kg) |
| 7324                               | #2 Combo                | Round      | 4" (101.6 mm)    | 8-11/32" (211.9 mm)  | 0.30 lb (0.14 kg) |
| 603-1                              | #2 Phillips             | Round      | 1-1/2" (38.1 mm) | 3-7/16" (87.3 mm)    | 0.10 lb (0.05 kg) |
| 603-3                              | #1 Phillips             | Round      | 3" (76.2 mm)     | 6-3/4" (171.5 mm)    | 0.15 lb (0.07 kg) |
| 603-4                              | #2 Phillips             | Round      | 4" (101.6 mm)    | 8-1/4" (209.6 mm)    | 0.25 lb (0.11 kg) |
| 603-6                              | #3 Phillips             | Round      | 6" (152.4 mm)    | 11" (279.4 mm)       | 0.35 lb (0.16 kg) |
| 603-7                              | #2 Phillips             | Round      | 7" (177.8 mm)    | 11-5/16" (287.3 mm)  | 0.30 lb (0.14 kg) |
| 603-10                             | #2 Phillips             | Round      | 10" (254.0 mm)   | 14-5/16" (363.5 mm)  | 0.35 lb (0.16 kg) |
| <b>Heavy Duty</b>                  |                         |            |                  |                      |                   |
| 605-4                              | 1/4" (6.4 mm) Cabinet   | Round      | 4" (101.6 mm)    | 8-11/32" (211.9 mm)  | 0.25 lb (0.11 kg) |
| 605-6                              | 1/4" (6.4 mm) Cabinet   | Round      | 6" (152.4 mm)    | 10-11/32" (262.7 mm) | 0.30 lb (0.14 kg) |
| 605-8                              | 1/4" (6.4 mm) Cabinet   | Round      | 8" (203.2 mm)    | 12-11/32" (313.5 mm) | 0.30 lb (0.14 kg) |
| 605-10                             | 1/4" (6.4 mm) Cabinet   | Round      | 10" (254.0 mm)   | 14-11/32" (364.3 mm) | 0.35 lb (0.16 kg) |
| <b>Heavy Duty with Bolster</b>     |                         |            |                  |                      |                   |
| 600-4                              | 1/4" (6.4 mm) Keystone  | Square     | 4" (101.6 mm)    | 8-11/32" (211.9 mm)  | 0.25 lb (0.11 kg) |
| 600-6                              | 5/16" (7.9 mm) Keystone | Square     | 6" (152.4 mm)    | 10-15/16" (277.8 mm) | 0.40 lb (0.18 kg) |
| 600-8                              | 3/8" (9.52 mm) Keystone | Square     | 8" (203.2 mm)    | 13-7/16" (341.3 mm)  | 0.65 lb (0.29 kg) |
| 600-12                             | 1/2" (12.7 mm) Keystone | Square     | 12" (304.8 mm)   | 17-7/16" (443.0 mm)  | 0.80 lb (0.36 kg) |
| <b>Heavy Duty with Hex Bolster</b> |                         |            |                  |                      |                   |
| 602-3                              | 7/32" (5.6 mm) Keystone | Round      | 3" (76.2 mm)     | 6-3/4" (171.5 mm)    | 0.15 lb (0.07 kg) |
| 602-4                              | 1/4" (6.4 mm) Keystone  | Round      | 4" (101.6 mm)    | 8-11/32" (211.9 mm)  | 0.25 lb (0.11 kg) |
| 602-6                              | 5/16" (7.9 mm) Keystone | Round      | 6" (152.4 mm)    | 10-15/16" (277.8 mm) | 0.35 lb (0.16 kg) |
| 602-8                              | 3/8" (9.52 mm) Keystone | Round      | 8" (203.2 mm)    | 13-7/16" (341.3 mm)  | 0.55 lb (0.25 kg) |
| 602-10                             | 3/8" (9.52 mm) Keystone | Round      | 10" (254.0 mm)   | 15-7/16" (392.1 mm)  | 0.60 lb (0.27 kg) |
| 602-12                             | 3/8" (9.52 mm) Keystone | Round      | 12" (304.8 mm)   | 17-7/16" (443.0 mm)  | 0.65 lb (0.29 kg) |

| Cat. No. | Set Contains                         | Weight          |
|----------|--------------------------------------|-----------------|
| 85078    | 8 Piece Cushion-Grip Screwdriver Set | 1.7 lb (0.8 kg) |

| Cat. No. | Description                            |
|----------|----------------------------------------|
| 600-4    | 1/4" Screwdriver HD Square Shank       |
| 602-6    | 5/16" Keystone Tip Screwdriver 6" L    |
| 600-1    | 5/16" Cabinet Tip Screwdriver 1-1/2"   |
| 601-3    | 3/16" Cabinet Tip Screwdriver 3"       |
| 603-3    | #1 Phillips Screwdriver 3" Round Shank |
| 603-1    | #2 Stubby Phillips Screwdriver 1-1/2"  |
| 603-4    | #2 Phillips Screwdriver 4" Round Shank |
| 603-6    | #3 Phillips Screwdriver 6" Round Shank |

| Cat. No. | Set Contains                         | Weight          |
|----------|--------------------------------------|-----------------|
| 85076    | 7 Piece Cushion-Grip Screwdriver Set | 1.5 lb (0.7 kg) |

| Cat. No. | Description                            |
|----------|----------------------------------------|
| 600-4    | 1/4" Screwdriver HD Square Shank       |
| 602-6    | 5/16" Keystone Tip Screwdriver 6" L    |
| 601-3    | 3/16" Cabinet Tip Screwdriver 3"       |
| 601-6    | 3/16" Cabinet Tip Screwdriver 6"       |
| 605-4    | 1/4" Cabinet Tip Screwdriver 4" Shank  |
| 603-3    | #1 Phillips Screwdriver 3" Round Shank |
| 603-4    | #2 Phillips Screwdriver 4" Round Shank |

| Cat. No. | Set Contains                         | Weight          |
|----------|--------------------------------------|-----------------|
| 85074    | 6 Piece Cushion-Grip Screwdriver Set | 1.5 lb (0.7 kg) |

| Cat. No. | Description                            |
|----------|----------------------------------------|
| 600-4    | 1/4" Screwdriver HD Square Shank       |
| 600-6    | 5/16" Keystone Screwdriver 6" SQ Shank |
| 601-3    | 3/16" Cabinet Tip Screwdriver 3"       |
| 603-3    | #1 Phillips Screwdriver 3" Round Shank |
| 603-4    | #2 Phillips Screwdriver 4" Round Shank |
| 603-6    | #3 Phillips Screwdriver 6" Round Shank |

| Cat. No. | Set Contains                         | Weight          |
|----------|--------------------------------------|-----------------|
| 85075    | 5 Piece Cushion-Grip Screwdriver Set | 1.3 lb (0.6 kg) |

| Cat. No. | Description                                |
|----------|--------------------------------------------|
| 602-6    | 5/16" Keystone Tip Screwdriver 6" L        |
| 600-4    | 1/4" Screwdriver HD Square Shank           |
| 601-6    | 3/16" Cabinet Tip Screwdriver 6"           |
| 605-6    | 1/4" Cabinet Tip Screwdriver Heavy Duty 6" |
| 603-4    | #2 Phillips Screwdriver 4" Round Shank     |

| Cat. No. | Set Contains                         | Weight          |
|----------|--------------------------------------|-----------------|
| 85105    | 4 Piece Cushion-Grip Screwdriver Set | 1.5 lb (0.7 kg) |

| Cat. No. | Description                            |
|----------|----------------------------------------|
| 600-6    | 5/16" Keystone Screwdriver 6" SQ Shank |
| 600-4    | 1/4" Screwdriver HD Square Shank       |
| 601-6    | 3/16" Cabinet Tip Screwdriver 6"       |
| 603-4    | #2 Phillips Screwdriver 4" Round Shank |

| Cat. No. | Set Contains                   | Weight            |
|----------|--------------------------------|-------------------|
| 85071    | 2 Piece Stubby Screwdriver Set | 0.30 lb (0.14 kg) |

| Cat. No. | Description                           |
|----------|---------------------------------------|
| 600-1    | 5/16" Cabinet Tip Screwdriver 1-1/2"  |
| 603-1    | #2 Stubby Phillips Screwdriver 1-1/2" |

| Cat. No. | Set Contains            | Weight          |
|----------|-------------------------|-----------------|
| 32378    | 4" Combo Tip Driver Set | 1.5 lb (0.7 kg) |

| Cat. No. | Description                         |
|----------|-------------------------------------|
| 7314     | #1 Combo-Tip Driver, 4" Fixed Blade |
| 7324     | #2 Combo Tip Driver, 4" Fixed Blade |

| Cat. No. | Set Contains                           | Weight            |
|----------|----------------------------------------|-------------------|
| 85072    | 2 Piece 10" Long Blade Screwdriver Set | 0.70 lb (0.32 kg) |

| Cat. No. | Description                             |
|----------|-----------------------------------------|
| 603-10   | #2 Phillips Screwdriver 10" Round Shank |
| 605-10   | 1/4" Cabinet Tip Screwdriver 10" Shank  |



## Cushion-Grip Screwdrivers

### Demolition Screwdrivers

Includes core Cushion-Grip screwdriver features plus:

- Engineered, manufactured and tested for prying, chiseling and punching
- Plated metal strike cap to protect handle from hammer blows
- Heat treated metal shaft runs complete length of handle to metal strike cap to transfer metal strike force



602-7DD



| Cat. No. | Tip Type                | Shank Type | Shank Length  | Overall Length     | Weight            |
|----------|-------------------------|------------|---------------|--------------------|-------------------|
| 602-4DD  | 1/4" (6.4 mm) Cabinet   | Round      | 4" (101.6 mm) | 9" (228.6 mm)      | 0.37 lb (0.17 kg) |
| 602-7DD  | 5/16" (7.9 mm) Keystone | Round      | 7" (177.8 mm) | 12-3/8" (314.3 mm) | 0.56 lb (0.25 kg) |
| 6034DD   | #2 Phillips             | Round      | 4" (177.8 mm) | 9" (228.6 mm)      | 0.37 lb (0.17 kg) |

| Cat. No. | Set Contains                              | Weight            |
|----------|-------------------------------------------|-------------------|
| 32008    | Demolition Driver Set                     | 0.70 lb (0.32 kg) |
| Cat. No. | Description                               |                   |
| 602-4DD  | 1/4" Keystone Demolition Driver, 4" Shank |                   |
| 6034DD   | #2 Phillips Demolition Driver, 4" Shank   |                   |

### Electronics Screwdrivers

Includes core Cushion-Grip screwdriver features plus:

- Rotating cap for optimum and precise control



614-6



| Cat. No. | Tip Type                | Shank Type | Shank Length  | Overall Length    | Weight           |
|----------|-------------------------|------------|---------------|-------------------|------------------|
| 613-3    | #0 Phillips             | Round      | 3" (76.2 mm)  | 6-1/2" (165.1 mm) | 0.80 oz (22.7 g) |
| 614-2    | 1/16" (1.59 mm) Cabinet | Round      | 2" (50.8 mm)  | 5-1/2" (139.7 mm) | 0.80 oz (22.7 g) |
| 614-3    | 3/32" (2.4 mm) Cabinet  | Round      | 3" (76.2 mm)  | 6-1/2" (165.1 mm) | 0.80 oz (22.7 g) |
| 614-4    | 1/8" (3.2 mm) Cabinet   | Round      | 4" (101.6 mm) | 7-1/2" (190.5 mm) | 0.80 oz (22.7 g) |
| 614-6    | 1/8" (3.2 mm) Cabinet   | Round      | 6" (152.4 mm) | 9-1/2" (241.3 mm) | 0.80 oz (22.7 g) |

| Cat. No. | Set Contains                                    | Weight            |
|----------|-------------------------------------------------|-------------------|
| 85614    | 5 Piece Electronics Screwdriver Set             | 0.80 lb (0.36 kg) |
| Cat. No. | Description                                     |                   |
| 614-2    | 1/16" Slotted Electronics Screwdriver, 2" Shank |                   |
| 614-3    | 3/32" Slotted Electronics Screwdriver, 3" Shank |                   |
| 614-4    | 1/8" Electronics Screwdriver 4" Shank           |                   |
| 614-6    | 1/8" Electronics Screwdriver 6" Shank           |                   |
| 613-3    | #0 Phillips Electronics Screwdriver, 3" Shank   |                   |

### Coated Screwdrivers

Includes core Cushion-Grip screwdriver features plus:

- Plastic coated for circuit protection only. NOT INSULATED
- Special plastic coating resists cutting, cracking and chipping
- Thin coating permits use in confined areas



620-4

| Cat. No. | Tip Type               | Shank Type | Shank Length  | Overall Length       | Weight            |
|----------|------------------------|------------|---------------|----------------------|-------------------|
| 620-3    | 3/16" (4.8 mm) Cabinet | Round      | 3" (76.2 mm)  | 6-3/4" (171.5 mm)    | 0.15 lb (0.07 kg) |
| 620-4    | 1/4" (6.4 mm) Cabinet  | Round      | 4" (101.6 mm) | 8-11/32" (211.9 mm)  | 0.20 lb (0.09 kg) |
| 620-6    | 5/16" (7.9 mm) Cabinet | Round      | 6" (152.4 mm) | 10-15/16" (277.8 mm) | 0.40 lb (0.18 kg) |
| 620-8    | 3/8" (9.52 mm) Cabinet | Round      | 8" (203.2 mm) | 13-7/16" (341.3 mm)  | 0.60 lb (0.27 kg) |
| 621-6    | 3/16" (4.8 mm) Cabinet | Round      | 6" (152.4 mm) | 9-3/4" (247.7 mm)    | 0.20 lb (0.09 kg) |
| 621-8    | 3/16" (4.8 mm) Cabinet | Round      | 8" (203.2 mm) | 11-3/4" (298.5 mm)   | 0.20 lb (0.09 kg) |

### 2-in-1 Rapi-Driv®


- Interchangeable bit holder allows quick switching between tip styles and works with other standard size bits
- Crank-action handle allows you to spin screws fast with one hand
- Blast finish bit provides firm grip on fasteners to reduce cam out



67100



| Cat. No. | Phillips Bits | Slotted Bits   | Shank Length  | Handle Color | Overall Length    | Weight            |
|----------|---------------|----------------|---------------|--------------|-------------------|-------------------|
| 67100    | #2            | 3/16" (4.8 mm) | 6" (152.4 mm) | Black        | 9-3/4" (247.7 mm) | 0.26 lb (0.12 kg) |



## Cushion-Grip Screwdrivers


### Rapi-Driv® Screwdrivers

- Crank-action handle spins screws fast with one hand
- Saves time and effort, especially on long-threaded screws in switch plates, light fixtures, etc.



670-6

| Cat. No. | Tip Type               | Shank Type       | Shank Length  | Overall Length    | Weight            |
|----------|------------------------|------------------|---------------|-------------------|-------------------|
| 670-3    | 3/16" (4.8 mm) Cabinet | Round Rapi-Driv® | 4" (101.6 mm) | 7-3/4" (196.9 mm) | 0.15 lb (0.07 kg) |
| 670-6    | 3/16" (4.8 mm) Cabinet | Round Rapi-Driv® | 6" (152.4 mm) | 9-3/4" (247.7 mm) | 0.20 lb (0.09 kg) |
| 671-6    | 1/4" (6.4 mm) Cabinet  | Round Rapi-Driv® | 6" (152.4 mm) | 9-3/4" (247.7 mm) | 0.20 lb (0.09 kg) |
| 682-6    | #2 Phillips            | Round Rapi-Driv® | 6" (152.4 mm) | 9-3/4" (247.7 mm) | 0.25 lb (0.11 kg) |
| 691-6    | #1 Square              | Round Rapi-Driv® | 6" (152 mm)   | 9-3/4" (248 mm)   | 0.35 lb (0.16 kg) |



### 7-Piece Multiple-Application Screwdriver Set

- Specialty set for a wide variety of applications

| Cat. No. | Set Contains                           | Weight          |
|----------|----------------------------------------|-----------------|
| 85077    | Multi Application Screwdriver Set 7 Pc | 1.7 lb (0.8 kg) |

| Cat. No. | Tip Type                | Shank Type       | Shank Length  | Overall Length       |
|----------|-------------------------|------------------|---------------|----------------------|
| 600-4    | 1/4" (6.4 mm) Keystone  | Square           | 4" (101.6 mm) | 8-11/32" (211.9 mm)  |
| 602-6    | 5/16" (7.9 mm) Keystone | Round            | 6" (152.4 mm) | 10-15/16" (277.8 mm) |
| 601-6    | 3/16" (4.8 mm) Cabinet  | Round            | 6" (152.4 mm) | 9-3/4" (247.7 mm)    |
| 605-6    | 1/4" (6.4 mm) Cabinet   | Round            | 6" (152.4 mm) | 10-11/32" (262.7 mm) |
| 670-6    | 3/16" (4.8 mm) Cabinet  | Round Rapi-Driv® | 6" (152.4 mm) | 9-3/4" (247.7 mm)    |
| K36      | 1/4" (6.4 mm) Slotted   | Round            | 6" (152.4 mm) | 9-3/4" (247.7 mm)    |
| 603-4    | #2 Phillips             | Round            | 4" (101.6 mm) | 8-1/4" (209.6 mm)    |



85077

### Adjustable Length Screwdrivers

- Removable shank adjusts within 4" to 8" (102-208 mm) range for numerous length combinations
- Blades feature two tips for multiple screwdrivers in one tool
- Proprietary system securely holds blade - as durable as a traditional Klein fixed blade screwdriver
- Press down to extend or lengthen the shank
- Push up to retract or shorten the shank
- Components sold separately



32751



US Patent: 6,561,523

| Cat. No. | Type                          | Tip Size                            | Shank Length                 | Overall Length     | Weight            |
|----------|-------------------------------|-------------------------------------|------------------------------|--------------------|-------------------|
| 32751    | Adjustable Length Screwdriver | #2 Phillips, 1/4" (6.4 mm) Slotted  | 4" to 8" (101.6 to 203.2 mm) | 13-3/8" (339.7 mm) | 0.70 lb (0.32 kg) |
| 32708    | Adjustable Length Screwdriver | #1, #2 Square                       | 4" to 8" (101.6 to 203.2 mm) | 13-3/8" (339.7 mm) | 0.10 lb (0.05 kg) |
| 32709    | Replacement Blade             | #1, #2 Square                       | 7-3/4" (196.9 mm)            | 9" (228.6 mm)      | 0.10 lb (0.05 kg) |
| 32713    | Replacement Blade             | #1 Phillips, 3/16" (4.8 mm) Slotted | 7-3/4" (196.9 mm)            | 9" (228.6 mm)      | 0.10 lb (0.05 kg) |
| 32618    | Replacement Blade             | #2 Phillips, 1/4" (6.4 mm) Slotted  | 4" to 8" (101.6 to 203.2 mm) | 9-1/8" (231.8 mm)  | 0.25 lb (0.11 kg) |
| 32619    | Screwdriver Handle            | —                                   | —                            | 5-3/8" (136.5 mm)  | 0.20 lb (0.09 kg) |

| Cat. No. | Set Contains                            | Weight            |
|----------|-----------------------------------------|-------------------|
| 32715    | Adjustable Length Replacement Blade Set | 0.10 lb (0.05 kg) |

| Cat. No. | Description                             |
|----------|-----------------------------------------|
| 32713    | Adj. Length Blade, #1 PH, 3/16" Slotted |
| 32618    | Adj. Length Blade, #2, 1/4" Slotted     |
| 32709    | Adj. Length Blade, Sq #1, #2            |

See page 310 for additional information on warnings.



## Specialty Cushion-Grip Screwdrivers

### 2-in-1 Hex Slide Driver/Nut Driver

- Unique, patented tip switches from 1/4" size to 5/16" size
- Magnetic regardless of which driver is selected
- Twist the thumb nut to lock tip setting
- U.S. Patent 7,654,175 B2

**NEW!**


65129



| Cat. No.          | Type       | Tip Size    | Shank Length     | Overall Length     | Weight            |
|-------------------|------------|-------------|------------------|--------------------|-------------------|
| 65129 <b>NEW!</b> | Hex Driver | 1/4", 5/16" | 6" (152.4 mm)    | 10-1/4" (260.4 mm) | 0.50 lb (0.23 kg) |
| 65131 <b>NEW!</b> | Hex Driver | 1/4", 5/16" | 1-1/2" (38.1 mm) | 3-23/64" (85.3 mm) | 0.18 lb (0.08 kg) |

### 2-in-1 Hex Head Screwdriver

- 1/4" and 5/16" six-point hex nut driver
- Powerful magnets for maximum fastener retention
- Solid build quality; feels like a conventional nut driver
- Color coded bands for easy identification
- Wrench-assist to help remove stubborn fasteners



65064



| Cat. No. | Type       | Tip Size       | Shank Length     | Overall Length | Weight            |
|----------|------------|----------------|------------------|----------------|-------------------|
| 65064    | Hex Driver | 1/4" and 5/16" | 3-5/8" (92.1 mm) | 8" (203.2 mm)  | 0.10 lb (0.05 kg) |

### Screw-Holding Screwdrivers

- Starts and drives screws with one hand when working in hard-to-reach spaces



32215



| Cat. No. | Tip Type              | Shank Type | Shank Length  | Overall Length     | Weight            |
|----------|-----------------------|------------|---------------|--------------------|-------------------|
| 32215    | 1/4" (6.4 mm) Cabinet | Round      | 7" (177.8 mm) | 11-1/4" (285.8 mm) | 0.32 lb (0.15 kg) |
| 32216    | #2 Phillips           | Round      | 7" (177.8 mm) | 11-1/4" (285.8 mm) | 0.32 lb (0.15 kg) |

### Terminal Block Screwdriver

Includes core Cushion-Grip screwdriver features plus:


- Provides exact fit for terminal block screws
- Tip is up to 19% stronger than competitors and provides 76% higher torque value than the required ASME B107 Standard



612-4



| Cat. No. | Tip Type              | Shank Type | Shank Length  | Overall Length    | Weight            |
|----------|-----------------------|------------|---------------|-------------------|-------------------|
| 612-4    | 1/8" (3.2 mm) Cabinet | Round      | 4" (101.6 mm) | 7-3/4" (196.9 mm) | 0.15 lb (0.07 kg) |



## Specialty Cushion-Grip Screwdrivers

### Wire Bending Screwdrivers

Includes core Cushion-Grip screwdriver features plus:

- Metal stud offers a convenient and easy way to bend, loop and connect solid wire when installing outlets and switches



605-6B



| Cat. No. | Bends                      | Tip Type | Tip Size      | Shank Type | Shank Length  | Overall Length       | Weight            |
|----------|----------------------------|----------|---------------|------------|---------------|----------------------|-------------------|
| 605-4B   | AWG Gauges Nos. 10, 12, 14 | Cabinet  | 1/4" (6.4 mm) | Round      | 4" (101.6 mm) | 8-11/32" (211.9 mm)  | 0.25 lb (0.11 kg) |
| 605-6B   | AWG Gauges Nos. 10, 12, 14 | Cabinet  | 1/4" (6.4 mm) | Round      | 6" (152.4 mm) | 10-11/32" (262.7 mm) | 0.30 lb (0.14 kg) |
| 603-4B   | AWG Gauges Nos. 10, 12, 14 | Phillips | #2            | Round      | 4" (101.6 mm) | 8-5/16" (211.1 mm)   | 0.25 lb (0.11 kg) |

## Multi-Bit Cushion-Grip Screwdrivers/Nut Drivers

### 15-in-1 Screwdriver/Nut Drivers

- Includes 14 different screwdriver tips plus a 1/4" (6.4 mm) nut driver
- Internal storage for screwdriver bits



INTERNAL STORAGE  
in handle



32290



| Cat. No. | Description                              | Nut Driver Sizes | Phillips Bits  | Slotted Bits | Square Bits | Hex Bits                        | Combo Bits | TORX® Bits                         | Other Bits                             | Shank Length  | Handle Color | Overall Length    | Weight            |
|----------|------------------------------------------|------------------|----------------|--------------|-------------|---------------------------------|------------|------------------------------------|----------------------------------------|---------------|--------------|-------------------|-------------------|
| 32290    | Multi-Bit Screwdriver with Storage 15 Pc | 1/4"             | #0, #1, #2, #3 | 4 mm, 6 mm   | #1, #2      | —                               | #1, #2     | #10, #15, #20, #25                 | —                                      | 4" (101.6 mm) | Black        | 8-1/2" (215.9 mm) | 0.50 lb (0.23 kg) |
| 32291    | Tamperproof Multi-Bit Screwdriver 15 Pc  | 1/4"             | —              | —            | —           | Pins: 1/8", 9/64", 5/32", 3/16" | —          | Pins: #10, #15, #20, #25, #27, #30 | Spanners: #6, #8, #10, #12             | 4" (101.6 mm) | Black        | 8-1/2" (215.9 mm) | 0.50 lb (0.23 kg) |
| 32292    | HVAC Multi-Bit Screwdriver 15 Pc         | 1/4"             | #0, #1, #2, #3 | 4 mm, 6 mm   | #1, #2      | —                               | —          | #10, #15, #20, #25                 | Schrader Valve Insertion, Core Removal | 4" (101.6 mm) | Black        | 8-1/2" (215.9 mm) | 0.50 lb (0.23 kg) |

Schrader® is a registered trademark of Schrader-Bridgeport International, Inc. TORX® is a registered trademark of Acument Intellectual Properties, LLC.

### 11-in-1 Combo-Tip Screwdriver/Nut Driver

- Precision machined tip designed for combination head screws



32505



| Cat. No. | Nut Driver Sizes | Phillips Bits | Slotted Bits                  | Square Bits | Combo Bits | Shank Length  | Handle Color | Overall Length    | Weight            |
|----------|------------------|---------------|-------------------------------|-------------|------------|---------------|--------------|-------------------|-------------------|
| 32505    | 1/4", 5/16" 3/8" | #1, #2        | 1/4" (6.4 mm), 5/16" (7.9 mm) | #1, #2      | #1, #2     | 4" (101.6 mm) | Yellow/Black | 7-1/4" (184.2 mm) | 0.50 lb (0.23 kg) |



## Multi-Bit Cushion-Grip Screwdrivers/Nut Drivers

### 11-in-1 Screwdriver/Nut Driver with Schrader® Valve Removal/Installation Bit

- Great for HVAC and other industrial applications
- Includes unique style bit for installation/removal of common TR-4 Schrader® valves and aggressive thread extractor tip for backing out broken cores



32527



| Cat. No. | Nut Driver Sizes  | Phillips Bits | Slotted Bits                  | Square Bits | Other Bits                             | Shank Length | Handle Color | Overall Length    | Weight            |
|----------|-------------------|---------------|-------------------------------|-------------|----------------------------------------|--------------|--------------|-------------------|-------------------|
| 32527    | 3/8", 5/16", 1/4" | #1, #2        | 1/4" (6.4 mm), 3/16" (4.8 mm) | #1, #2      | Schrader Valve Insertion, Core Removal | 3" (76.2 mm) | Yellow/Black | 7-3/4" (196.9 mm) | 0.44 lb (0.20 kg) |

Schrader® is a registered trademark of Schrader International, Inc.


### 8-in-1 HVAC Slide Driver™ Screwdriver/Nut Driver

**NEW!**

- Unique, patented head slides back and forth to switch from 1/4" to 5/16" magnetic hex-head screwdriver
- Thumb nut locks tip setting
- Features a specialty bit for installation/removal of common TR-4 Schrader® valves
- Includes 1/4" and 3/8" hollow nut drivers, as well as #2 Phillips, 1/8" (3 mm) and 1/4" (6 mm) slotted screwdriver tips
- Great for HVAC applications including thermostat installation and control work
- U.S. patent 7,654,175 B2



32596



| Cat. No.          | Nut Driver Sizes  | Phillips Bits | Slotted Bits                 | Other Bits                   | Shank Length     | Handle Color | Overall Length    | Weight           |
|-------------------|-------------------|---------------|------------------------------|------------------------------|------------------|--------------|-------------------|------------------|
| 32596 <b>NEW!</b> | 1/4", 5/16", 3/8" | #2            | 1/8" (3.2 mm), 1/4" (6.4 mm) | Schrader® Valve Core Removal | 3-1/4" (82.6 mm) | Yellow/Black | 7-1/2" (190.5 mm) | 0.50 lb (0.2 kg) |

Schrader® is a registered trademark of Schrader-Bridgeport International, Inc.

### 4-in-1 Electronics Precision Screwdrivers

- Four different tips in one tool
- Rotating cap for optimum and precise control




32581



| Cat. No.          | Phillips Bits | Slotted Bits                  | TORX® Bits       | Shank Length       | Handle Color | Overall Length    | Weight        |
|-------------------|---------------|-------------------------------|------------------|--------------------|--------------|-------------------|---------------|
| 32581             | #0, #00       | 1/8" (3.2 mm), 3/32" (2.4 mm) | —                | 2-51/64" (71.0 mm) | Yellow/Black | 6-1/2" (165.1 mm) | 1.1 oz (31 g) |
| 32585 <b>NEW!</b> | —             | —                             | T7, T8, T10, T15 | 2-51/64" (71.0 mm) | Yellow/Black | 6-1/2" (165.1 mm) | 1.1 oz (31 g) |

TORX® is a registered trademark of Acument Intellectual Properties, LLC.



## Multi-Bit Cushion-Grip Screwdrivers/Nut Drivers

### Ratcheting Multi-Bit Screwdriver/Nut Driver

- High torque 3-way ratcheting mechanism, forward, reverse and locked positions for tough applications
- Interchangeable shaft holds six universal tips; converts to three nut driver sizes and one hex driver
- Strong, heat-treated nut drivers for improved torque



32558



| Cat. No. | Nut Driver Sizes  | Phillips Bits | Slotted Bits                     | Square Bits | Hex Bits | Shank Length          | Handle Color | Overall Length         | Weight               |
|----------|-------------------|---------------|----------------------------------|-------------|----------|-----------------------|--------------|------------------------|----------------------|
| 32558    | 1/4", 5/16", 3/8" | #1, #2        | 1/4" (6.4 mm),<br>3/16" (4.8 mm) | #1, #2      | 3/8"     | 2-61/64"<br>(75.0 mm) | Yellow/Black | 7-57/64"<br>(200.4 mm) | 0.48 lb<br>(0.22 kg) |

### 6-in-1 Ratcheting Stubby Screwdrivers

- Ratcheting mechanism allows user to work faster with more efficiency



32593



| Cat. No. | Nut Driver Sizes | Phillips Bits | Slotted Bits                     | Square Bits | Shank Length          | Handle Color | Overall Length      | Weight               |
|----------|------------------|---------------|----------------------------------|-------------|-----------------------|--------------|---------------------|----------------------|
| 32593    | 1/4", 5/16"      | #1, #2        | 1/4" (6.4 mm),<br>3/16" (4.8 mm) | —           | 1-19/64"<br>(32.9 mm) | Yellow/Black | 3-1/2"<br>(88.9 mm) | 0.10 lb<br>(0.05 kg) |
| 32594    | 1/4", 5/16"      | #2            | 3/16" (4.8 mm)                   | #1, #2      | 1-19/64"<br>(32.9 mm) | Yellow/Black | 3-1/2"<br>(88.9 mm) | 0.10 lb<br>(0.05 kg) |

### Heavy-Duty Multi-Bit Screwdriver/Nut Driver

- Superior torque for tough applications
- Interchangeable shaft holds six universal tips; converts to three nut driver sizes and one hex driver
- Strong, heat-treated nut drivers for improved torque



32557



| Cat. No. | Nut Driver Sizes  | Phillips Bits | Slotted Bits                     | Square Bits | Hex Bits | Shank Length          | Handle Color | Overall Length         | Weight               |
|----------|-------------------|---------------|----------------------------------|-------------|----------|-----------------------|--------------|------------------------|----------------------|
| 32557    | 1/4", 5/16", 3/8" | #1, #2        | 1/4" (6.4 mm),<br>3/16" (4.8 mm) | #1, #2      | 3/8"     | 2-61/64"<br>(75.0 mm) | Yellow/Black | 7-57/64"<br>(200.4 mm) | 0.48 lb<br>(0.22 kg) |



## Multi-Bit Cushion-Grip Screwdrivers/Nut Drivers

### Multi-Bit Screwdriver/Nut Drivers

- Integrated screwdriver/nut driver shaft holds popular tips and converts nut driver sizes



32476



| Cat. No. | Nut Driver Sizes  | Phillips Bits | Slotted Bits                     | Square Bits | TORX® Bits | Shank Length     | Handle Color | Overall Length       | Weight               |
|----------|-------------------|---------------|----------------------------------|-------------|------------|------------------|--------------|----------------------|----------------------|
| 32476    | 5/16"             | #1, #2        | 1/4" (6.4 mm),<br>3/16" (4.8 mm) | —           | —          | 4"<br>(101.6 mm) | Yellow/Black | 7-3/4"<br>(196.9 mm) | 0.48 lb<br>(0.22 kg) |
| 32477    | 5/16", 1/4"       | #1, #2        | 1/4" (6.4 mm),<br>3/16" (4.8 mm) | #1, #2      | T10, T15   | 4"<br>(101.6 mm) | Yellow/Black | 7-3/4"<br>(196.9 mm) | 0.50 lb<br>(0.23 kg) |
| 32500    | 3/8", 5/16", 1/4" | #1, #2        | 1/4" (6.4 mm),<br>3/16" (4.8 mm) | #1, #2      | T10, T15   | 3"<br>(76.2 mm)  | Yellow/Black | 7-1/4"<br>(184.2 mm) | 0.50 lb<br>(0.23 kg) |

Cat. No. 32476 has 5/16" nut driver only, TORX® is a registered trademark of Acument Intellectual Properties, LLC

### Stubby Multi-Bit Screwdriver/Nut Driver

- Compact design features standard 1-1/4" (32 mm) shaft allowing easy access to tight work spaces
- Shaft holds four universal tips and converts to two nut driver sizes




32561



| Cat. No. | Nut Driver Sizes | Phillips Bits | Slotted Bits                     | Square Bits | Shank Length          | Handle Color | Overall Length        | Weight               |
|----------|------------------|---------------|----------------------------------|-------------|-----------------------|--------------|-----------------------|----------------------|
| 32561    | 1/4", 5/16"      | #1, #2        | 3/16" (4.8 mm),<br>1/4" (6.4 mm) | —           | 1-17/64"<br>(32.1 mm) | Yellow/Black | 3-13/32"<br>(86.5 mm) | 0.16 lb<br>(0.07 kg) |
| 32562    | 1/4", 5/16"      | #2            | 3/16" (4.8 mm)                   | #1, #2      | 1-17/64"<br>(32.1 mm) | Yellow/Black | 3-13/32"<br>(86.5 mm) | 0.16 lb<br>(0.07 kg) |

### Extended-Reach Multi-Bit Screwdrivers/Nut Drivers

- Interchangeable shaft holds four universal tips and converts to two nut driver sizes
- Extended shafts and blades provide 39% longer reach
- Small diameter shaft for comfortable grip and quick, easy turning



32559



| Cat. No. | Nut Driver Sizes | Phillips Bits | Slotted Bits                     | Square Bits | Shank Length          | Handle Color | Overall Length        | Weight               |
|----------|------------------|---------------|----------------------------------|-------------|-----------------------|--------------|-----------------------|----------------------|
| 32559    | 1/4", 5/16"      | #1, #2        | 1/4" (6.4 mm),<br>3/16" (4.8 mm) | —           | 4-7/64"<br>(104.4 mm) | Yellow/Black | 9-7/64"<br>(231.4 mm) | 0.41 lb<br>(0.19 kg) |
| 32560    | 1/4", 5/16"      | #2            | 1/4" (6.4 mm)                    | #1, #2      | 4-7/64"<br>(104.4 mm) | Yellow/Black | 9-7/64"<br>(231.4 mm) | 0.41 lb<br>(0.19 kg) |

## Multi-Bit Screwdrivers/Nut Drivers

### 10-in-1 Folding Screwdriver/Nut Driver

- Conveniently folds up for easy storage or to fit into your pocket
- Each driver arm contains four interchangeable bit styles and two nut drivers
- Unfold each driver arm up to a full 180° for straight on driving power, or at 90° for extra leverage on stubborn fasteners
- The quick release button easily unlocks a fully extended driver arm

10-FOLD™



32535

32434  
Schrader®



32535  
Standard



32536  
TORX®



32537  
Tamperproof TORX®



32538  
Standard Hex



32539  
Metric Hex



| Cat. No. | Nut Driver Sizes | Phillips Bits | Slotted Bits                     | Square Bits | Hex Bits                                                  | TORX® Bits                             | Other Bits                                      | Handle Color | Weight               |
|----------|------------------|---------------|----------------------------------|-------------|-----------------------------------------------------------|----------------------------------------|-------------------------------------------------|--------------|----------------------|
| 32534    | 5/16", 1/4"      | #1, #2        | 1/4" (6.4 mm),<br>3/16" (4.8 mm) | #1, #2      | —                                                         | —                                      | Valve Core Removal/<br>Installation - Extractor | Blue         | 0.37 lb<br>(0.17 kg) |
| 32535    | 5/16", 1/4"      | #1, #2        | 1/4" (6.4 mm),<br>3/16" (4.8 mm) | #1, #2      | —                                                         | T10, T15                               | —                                               | Black        | 0.37 lb<br>(0.17 kg) |
| 32536    | 5/16", 1/4"      | —             | —                                | —           | —                                                         | T6, T7, T8, T10,<br>T15, T20, T25, T27 | —                                               | Green        | 0.37 lb<br>(0.17 kg) |
| 32537    | 5/16", 1/4"      | —             | —                                | —           | —                                                         | T7, T8, T9, T10,<br>T15, T20, T25, T27 | —                                               | Green        | 0.37 lb<br>(0.17 kg) |
| 32538    | 5/16", 1/4"      | —             | —                                | —           | 1/16", 5/64", 3/32", 7/64", 1/8",<br>9/64", 5/32", 3/16"  | —                                      | —                                               | Red          | 0.37 lb<br>(0.17 kg) |
| 32539    | 5/16", 1/4"      | —             | —                                | —           | 0.9 mm, 1.3 mm, 1.5 mm, 2 mm,<br>2.5 mm, 3 mm, 4 mm, 5 mm | —                                      | —                                               | Blue         | 0.37 lb<br>(0.17 kg) |

Schrader® is a registered trademark of Schrader-Bridgeport International, Inc., TORX® is a registered trademark of Acument Intellectual Properties, LLC.

## Magnetic Screwdriver Bit Sets

### Non-Ratcheting Magnetic Screwdriver with 32-Piece Tamperproof Bit Set

- Sturdy bit and screw holding magnet allows for screws to fit securely in place for easy use
- Durable PVC black block allows for easy storage of standard 1/4" bits
- Includes complete tamperproof bit set in block



32510



TAMPERPROOF BIT SET INCLUDED  
WITH SET, ALSO SOLD SEPARATELY  
32525



STANDARD BIT SET  
SOLD SEPARATELY  
32526

| Cat. No.                 | Nut Driver Sizes | Phillips Bits     | Slotted Bits                                           | Square Bits | Hex Bits                                                                                                                                             | TORX® Bits                                         | Other Bits                                                       | Shank Length        | Handle Color     | Overall Length   | Weight               |
|--------------------------|------------------|-------------------|--------------------------------------------------------|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------|------------------------------------------------------------------|---------------------|------------------|------------------|----------------------|
| 32510                    | 1/4"             | —                 | —                                                      | —           | 3/32", 7/64", 1/8", 9/64", 5/32",<br>3/16", 2 mm, 2.5 mm, 3 mm,<br>4 mm, 5 mm                                                                        | —                                                  | Spanner: 4, 6, 8, 10;<br>Tri-Wing®: 1, 2;<br>TORQ-SET®: 6, 8, 10 | 3-1/2"<br>(88.9 mm) | Yellow/<br>Black | 8"<br>(203.2 mm) | 0.71 lb<br>(0.32 kg) |
| <b>32-Piece Bit Sets</b> |                  |                   |                                                        |             |                                                                                                                                                      |                                                    |                                                                  |                     |                  |                  |                      |
| 32526                    | —                | #0, #1,<br>#2, #3 | 3-4, 5-6,<br>6-8, 8-10,<br>10-12, 12-14<br>Screw Sizes | #1, #2, #3  | 2mm, 3/32", 7/64", 1/8", 9/64", 4mm, 3/16"                                                                                                           | T6, T7, T8,<br>T10, T15,<br>T20, T25               | Clutch: 5/32" (4 mm),<br>3/16" (4.8 mm)                          | —                   | —                | 1"<br>(25.4 mm)  | 0.43 lb<br>(0.20 kg) |
| 32525                    | —                | —                 | —                                                      | —           | 5/64" (2 mm), 3/32" (2.4 mm), 7/64" (2.8 mm),<br>1/8" (3.2 mm), 9/64" (3.6 mm),<br>5/32" (4.0 mm), 3/16" (4.8 mm), 2 mm,<br>2.5 mm, 3 mm, 4 mm, 5 mm | T7, T8, T10,<br>T15, T20,<br>T25, T27,<br>T30, T40 | Spanner: 4, 6, 8, 10;<br>Tri-Wing®: 1, 2, 3, 4                   | —                   | —                | 1"<br>(25.4 mm)  | 0.43 lb<br>(0.20 kg) |

TORX® is a registered trademark of Acument Intellectual Properties, LLC. TORQ-SET® and Tri-Wing® are registered trademarks of Phillips Screw Co.



## Multi-Bit Screwdriver/Nut Driver Replacement Parts and Bits

### Replacement Parts for Multi-Bit Screwdriver/Nut Drivers

- Precision-machined tips for exact fit into fastener



32398



32396



32397



32484



32478



32784



32781



13105

| Cat. No. | Tip Type                                         | For Use With                                              | Package Quantity |
|----------|--------------------------------------------------|-----------------------------------------------------------|------------------|
| 32392    | —                                                | Heavy Duty (32557) and Ratcheting (32558)                 | 1 Piece          |
| 32394    | —                                                | Heavy Duty (32557) and Ratcheting (32558)                 | 2 Piece          |
| 32395    | —                                                | Extended Reach Drivers (32559 and 32560)                  | 1 Piece          |
| 32396    | —                                                | Stubby Drivers (32561 and 32562)                          | 1 Piece          |
| 32397    | #2 Phillips; #1 Square                           | Heavy Duty (32557) and Ratcheting (32558)                 | 2 Bits           |
| 32398    | #1 Phillips; 1/4" (6.4 mm) Slotted               | Heavy Duty (32557), Ratcheting (32558) and Stubby (32561) | 2 Bits           |
| 32399    | #2 Square; 3/16" (4.8 mm) Slotted                | Heavy Duty (32557) and Ratcheting (32558)                 | 2 Bits           |
| 32400    | #1, #2 Phillips                                  | Extended Reach (32559)                                    | 2 Bits           |
| 32401    | 3/16" (4.8 mm), 1/4" (6.4 mm) Slotted            | Extended Reach (32559)                                    | 2 Bits           |
| 32410    | #2 Square; #2 Phillips                           | Stubby Driver (32560)                                     | 2 Bits           |
| 32411    | #1 Square; 1/4" (6.4 mm) Slotted                 | Stubby Driver (32560)                                     | 2 Bits           |
| 32412    | #2 Phillips; 3/16" (4.8 mm) Slotted              | Stubby Driver (32561)                                     | 2 Bits           |
| 32478    | #1 Phillips; 3/16" (4.8 mm) Slotted              | 5-in-1 (32476)                                            | 1 Bit            |
| 32479    | #2 Phillips; 9/32" (7.1 mm) Slotted              | 5-in-1 (32476)                                            | 1 Bit            |
| 32482    | #1 Phillips; 3/16" (4.8 mm) Slotted              | 10-in-1, 11-in-1 and 10-Fold™                             | 2 Bits           |
| 32483    | #2 Phillips; 1/4" (6.4 mm) Slotted               | 10-in-1, 11-in-1 and 10-Fold™                             | 2 Bits           |
| 32484    | #1, #2 Square                                    | 10-in-1, 11-in-1 and 10-Fold™                             | 2 Bits           |
| 67101    | #2 Phillips; 3/16" (4.8 mm) Slotted              | 2-in-1 Rapi-Drive®, 10-in-1, 11-in-1 and 10-Fold          | 2 Bits           |
| 32540    | TT7, TT8 TORX®                                   | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32541    | TT9, TT10 TORX®                                  | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32542    | TT15, TT20 TORX®                                 | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32543    | TT25, TT27 TORX®                                 | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32544    | T6, T7 TORX®                                     | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32485    | T10 and T15 TORX®                                | 10-in-1, 11-in-1 and 10-Fold™                             | 2 Bits           |
| 32545    | T8, T10 TORX®                                    | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32546    | T25, T27 TORX®                                   | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32547    | 3/32", 7/64" Hex                                 | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32548    | 5/32", 3/16" Hex                                 | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32549    | 1/8", 5/64" Hex                                  | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32550    | 1/8", 9/64" Hex                                  | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32551    | 0.9 mm, 1.3 mm Hex                               | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32552    | 1.5 mm, 2.0 mm Hex                               | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32553    | 2.5 mm, 3.0 mm Hex                               | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32554    | 4.0 mm, 5.0 mm Hex                               | 10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers           | 2 Bits           |
| 32752    | #1, #2 Combo                                     | Combo-Tip Multi-Tool (32505)                              | 2 Bits           |
| 32528    | Schrader® Valve Core Tool                        | 11-in-1 Schrader (32527)                                  | 1 Bit            |
| 32770    | #1, #2 Phillips                                  | 15-in-1 Screwdrivers (32290, 32291, 32292)                | 1 Bit            |
| 32771    | #0, #3 Phillips                                  | 15-in-1 Screwdrivers (32290, 32291, 32292)                | 1 Bit            |
| 32772    | #1, #2 Square                                    | 15-in-1 Screwdrivers (32290, 32291, 32292)                | 1 Bit            |
| 32773    | T10, T15 TORX®                                   | 15-in-1 Screwdrivers (32290, 32291, 32292)                | 1 Bit            |
| 32774    | T20, T25 TORX®                                   | 15-in-1 Screwdrivers (32290, 32291, 32292)                | 1 Bit            |
| 32775    | 4 mm, 6 mm Slotted                               | 15-in-1 Screwdrivers (32290, 32291, 32292)                | 1 Bit            |
| 32776    | #1, #2 Combo                                     | 15-in-1 Screwdrivers (32290, 32291, 32292)                | 1 Bit            |
| 32777    | 6, 8 Spanner                                     | 15-in-1 Screwdrivers (32290, 32291, 32292)                | 1 Bit            |
| 32778    | 10, 12 Spanner                                   | 15-in-1 Screwdrivers (32290, 32291, 32292)                | 1 Bit            |
| 32779    | 1/8, 9/64 Hex Pin                                | 15-in-1 Screwdrivers (32290, 32291, 32292)                | 1 Bit            |
| 32780    | 5/32, 3/16 Hex Pin                               | 15-in-1 Screwdrivers (32290, 32291, 32292)                | 1 Bit            |
| 32781    | 10, 15 Tamperproof                               | 15-in-1 Tamperproof Screwdriver (32291)                   | 1 Bit            |
| 32782    | 20, 25 Tamperproof                               | 15-in-1 Tamperproof Screwdriver (32291)                   | 1 Bit            |
| 32783    | 27, 30 Tamperproof                               | 15-in-1 Tamperproof Screwdriver (32291)                   | 1 Bit            |
| 32784    | Schrader® Valve Core Tool                        | 15-in-1 HVAC Screwdriver (32292)                          | 1 Bit            |
| 13391    | #0 Phillips; 3/32" (2.4 mm) Slotted              | 4-in-1 Electronics Screwdriver (32581, 32585)             | 2 Bits           |
| 13392    | #00 Phillips; 1/8" (3.2 mm) Slotted              | 4-in-1 Electronics Screwdriver (32581, 32585)             | 2 Bits           |
| 13104    | T7, T10 Tamperproof TORX®                        | 4-in-1 Electronics Screwdrivers (32581, 32585)            | 2 Bits           |
| 13105    | T8, T15 TORX®                                    | 4-in-1 Electronics Screwdrivers (32581, 32585)            | 2 Bits           |
| 13231    | Schrader® Valve Core Tool; 1/8" (3.2 mm) Slotted | HVAC 8-in-1 Slide Driver™ Screwdriver/Nut Driver (32596)  | 1 Bit            |



**Meets or exceeds** applicable  
ASME / ANSI and MIL specifications

## Plastic-Handle Screwdrivers

**Nickel-chrome, precision-forged**  
and polished blades with black tips

**Tough amber plastic handle**

**Smooth Comfordome® handles**  
fit the palm of the hand comfortably.

**Chrome-plated shank** helps  
prevent corrosion

**Internal flanges** provide solid,  
twist-resistant shaft anchor.

**MADE IN  
USA**

### Plastic-Handle Screwdrivers

**Includes core Plastic-Handle Screwdriver features plus:**

- Precision-machined Phillips tips provide a more consistent geometric symmetry to ensure accurate fit and torque without slippage
- Small-diameter cabinet-tip shanks for use in recessed holes or tight places and is well-suited for electrical and telecommunications work
- 35% larger than comparable screwdriver handles, the oversized Bull Driver handles deliver up to 50% extra power to perform tough jobs with minimal effort



| Cat. No. | Tip Type                | Shank Type | Shank Length     | Overall Length      | Weight            |
|----------|-------------------------|------------|------------------|---------------------|-------------------|
| P18      | #1 Phillips             | Round      | 8" (203.2 mm)    | 11-1/2" (292.1 mm)  | 0.15 lb (0.07 kg) |
| P28      | #2 Phillips             | Round      | 8" (203.2 mm)    | 11-5/8" (295.3 mm)  | 0.20 lb (0.09 kg) |
| P212     | #2 Phillips             | Round      | 12" (304.8 mm)   | 15-5/8" (396.9 mm)  | 0.25 lb (0.11 kg) |
| P202     | #2 Phillips             | Round      | 20" (508.0 mm)   | 24-1/2" (622.3 mm)  | 0.55 lb (0.25 kg) |
| A000     | 3/32" (2.4 mm) Keystone | Round      | 1-1/2" (38.1 mm) | 2-7/8" (73.0 mm)    | 0.32 oz (9.1 g)   |
| A216-3   | 1/8" (3.2 mm) Cabinet   | Round      | 3" (76.2 mm)     | 6" (152.4 mm)       | 0.80 oz (22.7 g)  |
| A216-4   | 1/8" (3.2 mm) Cabinet   | Round      | 4" (101.6 mm)    | 7" (177.8 mm)       | 0.80 oz (22.7 g)  |
| A216-6   | 1/8" (3.2 mm) Cabinet   | Round      | 6" (152.4 mm)    | 9" (228.6 mm)       | 0.80 oz (22.7 g)  |
| A216-8   | 1/8" (3.2 mm) Cabinet   | Round      | 8" (203.2 mm)    | 11" (279.4 mm)      | 0.80 oz (22.7 g)  |
| A216-10  | 1/8" (3.2 mm) Cabinet   | Round      | 10" (254.0 mm)   | 13" (330.2 mm)      | 0.80 oz (22.7 g)  |
| A316-4   | 3/16" (4.8 mm) Cabinet  | Round      | 4" (101.6 mm)    | 7-5/8" (193.7 mm)   | 0.10 lb (0.05 kg) |
| A316-6   | 3/16" (4.8 mm) Cabinet  | Round      | 6" (152.4 mm)    | 9-5/8" (244.5 mm)   | 0.10 lb (0.05 kg) |
| A316-8   | 3/16" (4.8 mm) Cabinet  | Round      | 8" (203.2 mm)    | 11-5/8" (295.27 mm) | 0.15 lb (0.07 kg) |
| A316-10  | 3/16" (4.8 mm) Cabinet  | Round      | 10" (254.0 mm)   | 13-5/8" (346.1 mm)  | 0.20 lb (0.09 kg) |
| 70155    | 3/16" (4.8 mm) Cabinet  | Round      | 20" (508.0 mm)   | 24-1/2" (622.3 mm)  | 0.45 lb (0.20 kg) |

#### **Bull Driver™ Plastic Handle Screwdrivers**

|       |                         |        |                |                      |                   |
|-------|-------------------------|--------|----------------|----------------------|-------------------|
| BD284 | 1/4" (6.4 mm) Keystone  | Square | 4" (101.6 mm)  | 8-1/2" (215.9 mm)    | 0.25 lb (0.11 kg) |
| BD286 | 1/4" (6.35 mm) Keystone | Square | 6" (152.4 mm)  | 10-1/2" (266.7 mm)   | 0.30 lb (0.14 kg) |
| BD306 | 5/16" (7.9 mm) Keystone | Square | 6" (152.4 mm)  | 11-3/16" (284.2 mm)  | 0.35 lb (0.16 kg) |
| BD308 | 5/16" (7.9 mm) Keystone | Square | 8" (203.2 mm)  | 13-3/16" (335.0 mm)  | 0.40 lb (0.18 kg) |
| BD410 | 3/8" (9.52 mm) Keystone | Square | 10" (254.0 mm) | 15-3/16" (385.8 mm)  | 0.60 lb (0.27 kg) |
| BD412 | 3/8" (9.52 mm) Keystone | Square | 12" (304.8 mm) | 17-3/16" (436.6 mm)  | 0.75 lb (0.34 kg) |
| BD144 | 1/4" (6.4 mm) Keystone  | Round  | 4" (101.6 mm)  | 8-1/2" (215.9 mm)    | 0.25 lb (0.11 kg) |
| BD146 | 1/4" (6.4 mm) Keystone  | Round  | 6" (152.4 mm)  | 10-1/2" (266.7 mm)   | 0.25 lb (0.11 kg) |
| BD156 | 5/16" (7.9 mm) Keystone | Round  | 6" (152.4 mm)  | 11-3/16" (284.2 mm)  | 0.35 lb (0.16 kg) |
| BD408 | 3/8" (9.52 mm) Keystone | Round  | 8" (203.2 mm)  | 13-3/16" (335.0 mm)  | 0.50 lb (0.23 kg) |
| BD510 | 3/8" (9.52 mm) Keystone | Round  | 10" (254 mm)   | 15-3/16" (385.76 mm) | 0.55 lb (0.25 kg) |
| BD512 | 3/8" (9.5 mm) Keystone  | Round  | 12" (305 mm)   | 17-3/16" (437 mm)    | 0.60 lb (0.27 kg) |
| BD111 | #1 Phillips             | Round  | 3" (76.2 mm)   | 6-5/8" (168.3 mm)    | 0.10 lb (0.05 kg) |
| BD122 | #2 Phillips             | Round  | 4" (101.6 mm)  | 8-1/2" (215.9 mm)    | 0.20 lb (0.09 kg) |
| BD133 | #3 Phillips             | Round  | 6" (152.4 mm)  | 11-3/16" (284.2 mm)  | 0.35 lb (0.16 kg) |

| Cat. No. | Set Contains                        | Weight          |
|----------|-------------------------------------|-----------------|
| 85276    | 7 Piece Combination Screwdriver Set | 1.1 lb (0.5 kg) |

#### **Cat. No. Description**

|        |                                          |
|--------|------------------------------------------|
| BD284  | Keystone Tip Screwdriver 4" Square Shank |
| BD306  | 5/16" Keystone Screwdriver 6" Shank      |
| A216-3 | 1/8" Cabinet Tip Screwdriver 3" Shank    |
| A216-4 | Cabinet Tip Screwdriver 4" Round Shank   |
| A216-6 | Cabinet Tip Screwdriver 6" Round Shank   |
| BD111  | Profiled #1 Phillips Screwdriver 3"      |
| BD122  | Profiled #2 Phillips Screwdriver 4"      |

See page 310 for additional information on warnings.



## Plastic-Handle Screwdrivers

### Pocket-Clip Screwdrivers

Includes core Plastic-Handle Screwdriver features plus:

- Specially designed for delicate instrument work



A116-3



| Cat. No. | Tip Type                | Shank Type | Shank Length     | Overall Length     | Weight           |
|----------|-------------------------|------------|------------------|--------------------|------------------|
| A130-2   | 1/8" (3.2 mm) Keystone  | Round      | 2" (50.8 mm)     | 3-7/8" (98.4 mm)   | 0.80 oz (22.7 g) |
| A130-3   | 1/8" (3.2 mm) Keystone  | Round      | 3" (76.2 mm)     | 4-7/8" (123.8 mm)  | 0.64 oz (18.1 g) |
| A116-2   | 3/32" (2.4 mm) Keystone | Round      | 2" (50.8 mm)     | 4-7/16" (112.7 mm) | 0.80 oz (22.7 g) |
| A116-3   | 3/32" (2.4 mm) Keystone | Round      | 3" (76.2 mm)     | 5-7/16" (138.1 mm) | 0.48 oz (13.6 g) |
| A131-2   | 1/8" (3.2 mm) Keystone  | Round      | 2" (50.8 mm)     | 4-7/16" (112.7 mm) | 0.80 oz (22.7 g) |
| P12      | #0 Phillips             | Round      | 2-1/2" (63.5 mm) | 5" (127.0 mm)      | 0.80 oz (22.7 g) |

### Magnetic Plastic-Handle Screwdriver

- Powerful magnet built into its shank to hold interchangeable bits and also screws
- Comfortable handle for easier driving
- Interchangeable bits store inside handle for quick access
- Wide selection of bits for different screw types



70035

| Cat. No. | Phillips Bits | Slotted Bits                   | Shank Length     | Handle Color    | Overall Length | Weight            |
|----------|---------------|--------------------------------|------------------|-----------------|----------------|-------------------|
| 70035    | #1, #2        | 3/16" (4.8 mm), 9/32" (7.1 mm) | 3-3/4" (95.3 mm) | Black and Clear | 3-7/16"        | 0.25 lb (0.11 kg) |

### Slotted Plastic-Handle Screw-Holding Screwdrivers

- Positive gripping action holds, starts, and drives slotted screws in awkward, hard-to-reach places
- Split-blade screw-holding driver wedges into screw slot
- Not designed for torquing or tightening



K36


| Cat. No. | Overall Length     | Shank Type | Tip Type               | Weight            |
|----------|--------------------|------------|------------------------|-------------------|
| K23      | 5-1/4" (133.4 mm)  | Round      | 3/16" (4.8 mm) Slotted | 0.80 oz (22.7 g)  |
| K28      | 10-1/4" (260.4 mm) | Round      | 3/16" (4.8 mm) Slotted | 0.10 lb (0.05 kg) |
| K34      | 7-3/4" (196.9 mm)  | Round      | 1/4" (6.4 mm) Slotted  | 0.10 lb (0.05 kg) |
| K36      | 9-3/4" (247.7 mm)  | Round      | 1/4" (6.4 mm) Slotted  | 0.15 lb (0.07 kg) |
| K38      | 11-3/4" (298.5 mm) | Round      | 1/4" (6.4 mm) Slotted  | 0.20 lb (0.09 kg) |
| K44      | 8-1/4" (209.6 mm)  | Round      | 5/16" (7.9 mm) Slotted | 0.25 lb (0.11 kg) |
| K46      | 10-1/4" (260.4 mm) | Round      | 5/16" (7.9 mm) Slotted | 0.25 lb (0.11 kg) |
| K48      | 12-1/4" (311.2 mm) | Round      | 5/16" (7.9 mm) Slotted | 0.30 lb (0.14 kg) |



| Cat. No. | Set Contains                          | Weight            |
|----------|---------------------------------------|-------------------|
| SK234    | Slotted Holding Screwdriver Set 3 Pc  | 0.40 lb (0.18 kg) |
| Cat. No. | Description                           |                   |
| K23      | 3/16" Screw Holding Screwdriver 3"    |                   |
| K34      | Slotted Screw Holding Screwdriver 4"  |                   |
| K46      | Slotted Holding Screwdriver 10-1/4" L |                   |

Precision blade for use with small precision screws. Blade thickness of 0.028" expanding to 0.045".  
 ‡ Blade thickness of 0.043" expanding to 0.085". K21 and K23 have pocket clips.





## Screw-Holding Screwdrivers

### Phillips-Tip Screw-Holding Screwdrivers

- Positive gripping action holds and starts Phillips screws in awkward, hard-to-reach places
- Blade separates to hold the fastener
- Not designed for torquing or tightening



| Cat. No. | Overall Length | Shank Type | Tip Type | Weight           |
|----------|----------------|------------|----------|------------------|
| K14      | 5" (127.0 mm)  | Round      | Phillips | 0.80 oz (22.7 g) |
| K16      | 7" (177.8 mm)  | Round      | Phillips | 0.80 oz (22.7 g) |
| K19      | 9" (228.6 mm)  | Round      | Phillips | 0.80 oz (22.7 g) |



K16

## Impact and Torque Drivers

### Reversible Impact-Driver Set

- Rugged, hand-impact driver turns rusted, frozen, or other stubborn screws
- Can also be used with 3/8" square-drive impact sockets
- Internal, spring-loaded, helical design transforms the impact of a hammer blow to up to 200 ft.-lbs. of shock torque
- Easily reverses for tightening or loosening screws
- Constructed of high-grade alloy steel that has been heat-treated for added strength
- Reclosable, seal-tight vinyl pouch with hang-up grommet



70229  
BITS FOR IMPACT  
DRIVER SET



70220



| Cat. No. | Phillips Bits | Nut Driver Sizes | Slotted Bits                      | Included                                   | Weight          |
|----------|---------------|------------------|-----------------------------------|--------------------------------------------|-----------------|
| 70220    | #2 and #4     | 5/16"            | 5/16" (7.9 mm) and 1/2" (12.7 mm) | 3/8" (9.5 mm) Square Drive fitting Adapter | 2.2 lb (1.0 kg) |

### Torque Screwdriver Set

- Compact, easy to use set includes the Torque Screwdriver, a 6-piece bit set and a rugged case with foam inserts for a tight, organized fit
- Increased usability and readability plus a wider torque range (5-40 in. lbs)
- Tri-lobular design with a textured finish for better grip
- Lightweight, aluminum frame
- N.I.S.T. traceable calibration certificate
- Set includes six 3-1/2" (89 mm) power drivers and a 1/4" nut driver



| Cat. No. | Included                                                                                                    | Weight          |
|----------|-------------------------------------------------------------------------------------------------------------|-----------------|
| 57032    | Phillips: #1 and #2;<br>Slotted: 3/16" (4.8 mm) and 1/4" (6.4 mm);<br>Square: #1 and #2 and 1/4" Nut Driver | 1.0 lb (0.5 kg) |



57032



# Heavy-Duty Cushion-Grip Nut Drivers

## Through-handle full-hollow shaft

design for torquing hex nuts onto threaded rod of any length




**Wrench-assist**  
feature for  
added torque



**Rare-earth  
magnetic tip**  
holds nut in  
place while  
fastening



**Color-coded  
ends and tips**  
for easy size  
identification



**6 sizes** 1/4", 5/16", 3/8",  
7/16", 1/2" and 9/16" sizes

**MADE IN  
USA**  
GLOBAL  
COMPONENTS

## Heavy-Duty Nut Drivers



635-1/4



635-5/16



635-3/8



635-7/16



635-1/2



635-9/16



| Cat. No. | Nut Driver Sizes | Shaft Length  | Color Code | Overall Length      | Weight            |
|----------|------------------|---------------|------------|---------------------|-------------------|
| 635-1/4  | 1/4"             | 4" (101.6 mm) | Red        | 9" (228.6 mm)       | 0.30 lb (0.14 kg) |
| 635-5/16 | 5/16"            | 4" (101.6 mm) | Yellow     | 9" (228.6 mm)       | 0.30 lb (0.14 kg) |
| 635-3/8  | 3/8"             | 4" (101.6 mm) | Blue       | 9" (228.6 mm)       | 0.30 lb (0.14 kg) |
| 635-7/16 | 7/16"            | 4" (101.6 mm) | Brown      | 9-25/64" (238.5 mm) | 0.40 lb (0.18 kg) |
| 635-1/2  | 1/2"             | 4" (101.6 mm) | Red        | 9-25/64" (238.5 mm) | 0.50 lb (0.23 kg) |
| 635-9/16 | 9/16"            | 4" (101.6 mm) | Orange     | 9-25/64" (238.5 mm) | 0.50 lb (0.23 kg) |


| Cat. No. | Set Contains                      | Weight          |
|----------|-----------------------------------|-----------------|
| 635-6    | 6 Piece Heavy-Duty Nut Driver Set | 2.5 lb (1.1 kg) |
| Cat. No. | Description                       |                 |
| 635-1/4  | 1/4" Heavy-Duty Nut Driver        |                 |
| 635-5/16 | 5/16" Heavy-Duty Nut Driver       |                 |
| 635-3/8  | 3/8" Heavy-Duty Nut Driver        |                 |
| 635-7/16 | 7/16" Heavy-Duty Nut Driver       |                 |
| 635-1/2  | 1/2" Heavy-Duty Nut Driver        |                 |
| 635-9/16 | 9/16" Heavy-Duty Nut Driver       |                 |

| Cat. No. | Set Contains                      | Weight          |
|----------|-----------------------------------|-----------------|
| 635-4    | 4 Piece Heavy-Duty Nut Driver Set | 1.4 lb (0.6 kg) |
| Cat. No. | Description                       |                 |
| 635-1/4  | 1/4" Heavy-Duty Nut Driver        |                 |
| 635-5/16 | 5/16" Heavy-Duty Nut Driver       |                 |
| 635-3/8  | 3/8" Heavy-Duty Nut Driver        |                 |
| 635-7/16 | 7/16" Heavy-Duty Nut Driver       |                 |



## Cushion-Grip Nut Drivers

Meets or exceeds applicable ASME / ANSI and MIL specifications



Handle end is also color coded for easy identification



**Tip-Ident®** quickly identifies nut driver and size



## Magnetic-Tip Hollow-Shaft Nut Drivers

Includes core Cushion-Grip Nut Driver features plus:

- Exclusive hollow shaft\* design with Rare Earth magnetic tip features unobstructed pass-through, even on long bolts



630-3/8M

| Cat. No.   | Nut Driver Sizes | Shaft Length     | Color Code | Overall Length      | Weight            |
|------------|------------------|------------------|------------|---------------------|-------------------|
| 610-1/4M   | 1/4"             | 1-1/2" (38.1 mm) | Red        | 3-1/2" (88.9 mm)    | 0.10 lb (0.05 kg) |
| 610-5/16M  | 5/16"            | 1-1/2" (38.1 mm) | Yellow     | 3-1/2" (88.9 mm)    | 0.10 lb (0.05 kg) |
| 610-3/8M   | 3/8"             | 1-1/2" (38.1 mm) | Blue       | 3-1/2" (88.9 mm)    | 0.10 lb (0.05 kg) |
| 630-3/16M  | 3/16"            | 3" (76.2 mm)     | Black      | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-1/4M   | 1/4"             | 3" (76.2 mm)     | Red        | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-5/16M  | 5/16"            | 3" (76.2 mm)     | Yellow     | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-11/32M | 11/32"           | 3" (76.2 mm)     | Green      | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-3/8M   | 3/8"             | 3" (76.2 mm)     | Blue       | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-7/16M  | 7/16"            | 3" (76.2 mm)     | Brown      | 7-5/16" (185.7 mm)  | 0.25 lb (0.11 kg) |
| 630-1/2M   | 1/2"             | 3" (76.2 mm)     | Red        | 7-5/16" (185.7 mm)  | 0.25 lb (0.11 kg) |
| 646-3/16M  | 3/16"            | 6" (152.4 mm)    | Black      | 9-3/4" (247.7 mm)   | 0.25 lb (0.11 kg) |
| 646-1/4M   | 1/4"             | 6" (152.4 mm)    | Red        | 9-3/4" (247.7 mm)   | 0.25 lb (0.11 kg) |
| 646-5/16M  | 5/16"            | 6" (152.4 mm)    | Yellow     | 9-3/4" (247.7 mm)   | 0.25 lb (0.11 kg) |
| 646-11/32M | 11/32"           | 6" (152.4 mm)    | Green      | 9-3/4" (247.7 mm)   | 0.25 lb (0.11 kg) |
| 646-3/8M   | 3/8"             | 6" (152.4 mm)    | Blue       | 9-3/4" (247.7 mm)   | 0.30 lb (0.14 kg) |
| 646-7/16M  | 7/16"            | 6" (152.4 mm)    | Brown      | 10-5/16" (261.9 mm) | 0.35 lb (0.16 kg) |
| 646-1/2M   | 1/2"             | 6" (152.4 mm)    | Red        | 10-5/16" (261.9 mm) | 0.35 lb (0.16 kg) |
| 618-1/4M   | 1/4"             | 18" (457.2 mm)   | Red        | 21-3/4" (552.5 mm)  | 0.50 lb (0.23 kg) |
| 618-5/16M  | 5/16"            | 18" (457.2 mm)   | Yellow     | 21-3/4" (552.5 mm)  | 0.50 lb (0.23 kg) |

\*3/16" magnetic nut driver does not have a hollow shaft.

| Cat. No. | Set Contains                           | Weight          |
|----------|----------------------------------------|-----------------|
| 631M     | Magnetic Nut Driver Set 3" Shaft, 7 Pc | 1.5 lb (0.7 kg) |

| Cat. No.   | Description                            |
|------------|----------------------------------------|
| 630-3/16M  | 3/16" Magnetic Tip Nut Driver 3" Shaft |
| 630-1/4M   | 1/4" Magnetic Tip Nut Driver 3" Shaft  |
| 630-5/16M  | 5/16" Nut Driver with Hollow Shaft     |
| 630-11/32M | 11/32" Magnetic Nut Driver 3" Shaft    |
| 630-3/8M   | 3/8" Magnetic Tip Nut Driver 3" Shaft  |
| 630-7/16M  | 7/16" Magnetic Tip Nut Driver 3" Shaft |
| 630-1/2M   | 1/2" Magnetic Tip Nut Driver 3" Shank  |

| Cat. No. | Set Contains                            | Weight          |
|----------|-----------------------------------------|-----------------|
| 647M     | Magnetic Nut Driver Set 6" Shafts, 7 Pc | 1.5 lb (0.7 kg) |

| Cat. No.   | Description                            |
|------------|----------------------------------------|
| 646-3/16M  | 3/16" Magnetic Tip Nut Driver 6" Shaft |
| 646-1/4M   | 1/4" Magnetic Tip Nut Driver 6" Shaft  |
| 646-5/16M  | 5/16" Magnetic Nut Driver Cushion-Grip |
| 646-11/32M | 11/32" Magnetic Nut Driver 6" Shaft    |
| 646-3/8M   | 3/8" Magnetic Tip Nut Driver 6" Shaft  |
| 646-7/16M  | 7/16" Magnetic Tip Nut Driver 6" Shaft |
| 646-1/2M   | 1/2" Magnetic Tip Nut Driver 6" Shaft  |

| Cat. No. | Set Contains                          | Weight            |
|----------|---------------------------------------|-------------------|
| 630M     | Magnetic Nut Driver Set 3" Shank 2 Pc | 0.40 lb (0.18 kg) |

| Cat. No.  | Description                           |
|-----------|---------------------------------------|
| 630-1/4M  | 1/4" Magnetic Tip Nut Driver 3" Shaft |
| 630-5/16M | 5/16" Nut Driver with Hollow Shaft    |

| Cat. No. | Set Contains                            | Weight            |
|----------|-----------------------------------------|-------------------|
| 646M     | Nut Driver Set 6" Shafts, Magnetic 2 Pc | 0.50 lb (0.23 kg) |

| Cat. No.  | Description                            |
|-----------|----------------------------------------|
| 646-1/4M  | 1/4" Magnetic Tip Nut Driver 6" Shaft  |
| 646-5/16M | 5/16" Magnetic Nut Driver Cushion-Grip |

| Cat. No. | Set Contains                                      | Weight            |
|----------|---------------------------------------------------|-------------------|
| 610M     | Stubby Nut Driver Set 1-1/2" Shafts Magnetic 2 Pc | 0.20 lb (0.09 kg) |

| Cat. No.  | Description                             |
|-----------|-----------------------------------------|
| 610-1/4M  | Magnetic Nut Driver 1-1/2" Hollow Shaft |
| 610-5/16M | 5/16" Magnetic Nut Driver 1-1/2" Shaft  |



## Cushion-Grip Nut Drivers

### Hollow-Shaft Nut Drivers

Includes core Cushion-Grip Nut Driver features plus:

- 3" (76 mm) length for most long bolt and stud applications
- 6" (152 mm) length reaches into deep recesses and fits over extra-long bolts and studs
- Exclusive hollow shaft\* design with Rare Earth magnetic tip features unobstructed pass-through, even on long bolts

Refer to the insulated section for insulated nut drivers.



| Cat. No.  | Nut Driver Sizes | Shaft Length     | Color Code | Overall Length      | Weight            |
|-----------|------------------|------------------|------------|---------------------|-------------------|
| 610-1/4   | 1/4"             | 1-1/2" (38.1 mm) | Red        | 3-1/2" (88.9 mm)    | 0.10 lb (0.05 kg) |
| 610-5/16  | 5/16"            | 1-1/2" (38.1 mm) | Yellow     | 3-1/2" (88.9 mm)    | 0.10 lb (0.05 kg) |
| 630-3/16  | 3/16"            | 3" (76.2 mm)     | Black      | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-1/4   | 1/4"             | 3" (76.2 mm)     | Red        | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-5/16  | 5/16"            | 3" (76.2 mm)     | Yellow     | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-11/32 | 11/32"           | 3" (76.2 mm)     | Green      | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-3/8   | 3/8"             | 3" (76.2 mm)     | Blue       | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-7/16  | 7/16"            | 3" (76.2 mm)     | Brown      | 7-5/16" (185.7 mm)  | 0.25 lb (0.11 kg) |
| 630-1/2   | 1/2"             | 3" (76.2 mm)     | Red        | 7-5/16" (185.7 mm)  | 0.25 lb (0.11 kg) |
| 630-9/16  | 9/16"            | 4" (101.6 mm)    | Orange     | 9-3/8" (238.1 mm)   | 0.35 lb (0.16 kg) |
| 630-5/8   | 5/8"             | 4" (101.6 mm)    | Yellow     | 9-3/8" (238.1 mm)   | 0.35 lb (0.16 kg) |
| 646-3/16  | 3/16"            | 6" (152.4 mm)    | Black      | 9-3/4" (247.7 mm)   | 0.25 lb (0.11 kg) |
| 646-1/4   | 1/4"             | 6" (152.4 mm)    | Red        | 9-3/4" (247.7 mm)   | 0.25 lb (0.11 kg) |
| 646-5/16  | 5/16"            | 6" (152.4 mm)    | Yellow     | 9-3/4" (247.7 mm)   | 0.25 lb (0.11 kg) |
| 646-11/32 | 11/32"           | 6" (152.4 mm)    | Green      | 9-3/4" (247.7 mm)   | 0.25 lb (0.11 kg) |
| 646-3/8   | 3/8"             | 6" (152.4 mm)    | Blue       | 9-3/4" (247.7 mm)   | 0.30 lb (0.14 kg) |
| 646-7/16  | 7/16"            | 6" (152.4 mm)    | Brown      | 10-5/16" (261.9 mm) | 0.35 lb (0.16 kg) |
| 646-1/2   | 1/2"             | 6" (152.4 mm)    | Red        | 10-5/16" (261.9 mm) | 0.35 lb (0.16 kg) |
| 646-9/16  | 9/16"            | 6" (152.4 mm)    | Orange     | 11-3/8" (288.9 mm)  | 0.40 lb (0.18 kg) |
| 646-5/8   | 5/8"             | 6" (152.4 mm)    | Yellow     | 11-3/8" (288.9 mm)  | 0.40 lb (0.18 kg) |
| Metric    |                  |                  |            |                     |                   |
| 630-4MM   | 4 mm             | 3" (76.2 mm)     | Red        | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-4.5MM | 4.5 mm           | 3" (76.2 mm)     | Yellow     | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-5MM   | 5 mm             | 3" (76.2 mm)     | Black      | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-6MM   | 6 mm             | 3" (76.2 mm)     | Red        | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-7MM   | 7 mm             | 3" (76.2 mm)     | Orange     | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-8MM   | 8 mm             | 3" (76.2 mm)     | Yellow     | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-10MM  | 10 mm            | 3" (76.2 mm)     | Blue       | 6-3/4" (171.5 mm)   | 0.20 lb (0.09 kg) |
| 630-11MM  | 11 mm            | 3" (76.2 mm)     | Brown      | 7-5/16" (185.7 mm)  | 0.20 lb (0.09 kg) |

\*3/16" magnetic nut driver does not have a hollow shaft.



630-11MM

| Cat. No. | Set Contains                   | Weight          |
|----------|--------------------------------|-----------------|
| 631      | Nut Driver Set 3" Shafts, 7 Pc | 1.5 lb (0.7 kg) |

#### Cat. No. Description

|           |                                        |
|-----------|----------------------------------------|
| 630-3/16  | 3/16" Hollow Shaft Nut Driver 3" Shaft |
| 630-1/4   | 1/4" Nut Driver 3" Shaft Cushioned     |
| 630-5/16  | 5/16" Nut Driver Cushion-Grip 3" Shaft |
| 630-11/32 | 11/32" Nut Driver 3" Hollow Shaft      |
| 630-3/8   | 3/8" Hollow Shaft Nut Driver 3" Shaft  |
| 630-7/16  | 7/16" Hollow Nut Driver 3" Cushioned   |
| 630-1/2   | 1/2" Nut Driver 3" Shaft Cushion-Grip  |

| Cat. No. | Set Contains                   | Weight          |
|----------|--------------------------------|-----------------|
| 647      | Nut Driver Set 6" Shafts, 7 Pc | 1.7 lb (0.8 kg) |

#### Cat. No. Description

|           |                                        |
|-----------|----------------------------------------|
| 646-3/16  | 3/16" Nut Driver 6" Shaft              |
| 646-1/4   | 1/4" Hollow Shaft Nut Driver 6" Shaft  |
| 646-5/16  | 5/16" Hollow Shaft Nut Driver 6" Shaft |
| 646-11/32 | 11/32" Nut Driver 6" Hollow Shaft      |
| 646-3/8   | 3/8" Hollow Shaft Nut Driver 6" Shaft  |
| 646-7/16  | 7/16" Nut Driver 6" Hollow Shaft       |
| 646-1/2   | 1/2" Nut Driver 6" Hollow Shaft        |

| Cat. No. | Set Contains                            | Weight          |
|----------|-----------------------------------------|-----------------|
| 65160    | 7 Piece Metric Nut Driver Set 3" Shafts | 1.5 lb (0.7 kg) |

#### Cat. No. Description

|           |                                               |
|-----------|-----------------------------------------------|
| 630-5MM   | 5 mm Cushion Grip Nut Driver 3" Shaft         |
| 630-5.5MM | 5.5 mm Cushion-Grip Hollow-Shank Nut Driver   |
| 630-6MM   | 6 mm Cushion-Grip Nut Driver, 3" Hollow Shaft |
| 630-7MM   | 7 mm Cushion Grip Nut Driver 3" Shaft         |
| 630-8MM   | 8 mm Cushion-Grip Nut Driver, 3" Hollow Shaft |
| 630-9MM   | 9 mm Cushion-Grip Nut Driver, 3" Hollow Shaft |
| 630-10MM  | 10 mm Cushion Grip Nut Driver 3" Shaft        |

| Cat. No. | Set Contains         | Weight          |
|----------|----------------------|-----------------|
| 633      | Nut Driver Set, 4 Pc | 1.3 lb (0.6 kg) |

#### Cat. No. Description


|          |                                        |
|----------|----------------------------------------|
| 630-1/4  | 1/4" Nut Driver 3" Shaft Cushioned     |
| 630-5/16 | 5/16" Nut Driver Cushion-Grip 3" Shaft |
| 630-3/8  | 3/8" Hollow Shaft Nut Driver 3" Shaft  |
| 630-9/16 | 9/16" Hollow Shaft Nut Driver 4" Shaft |

| Cat. No. | Set Contains                             | Weight            |
|----------|------------------------------------------|-------------------|
| 610      | Stubby Nut Driver Set 1-1/2" Shafts 2 Pc | 0.20 lb (0.09 kg) |

#### Cat. No. Description

|          |                                      |
|----------|--------------------------------------|
| 610-1/4  | 1/4" Stubby Nut Driver 1-1/2" Shaft  |
| 610-5/16 | 5/16" Stubby Nut Driver Cushion Grip |





## Cushion-Grip Nut Drivers

### Coated Hollow-Shaft Nut Drivers

Includes core Cushion-Grip Nut Driver features plus:

- Entire shaft plastic coated for circuit protection only. NOT INSULATED
- Special plastic coating resists cutting, cracking and chipping
- Thin coating permits use in confined areas



640-1/2

| Cat. No. | Nut Driver Sizes | Shaft Length  | Color Code | Overall Length     | Weight            |
|----------|------------------|---------------|------------|--------------------|-------------------|
| 640-3/16 | 3/16"            | 3" (76.2 mm)  | Black      | 6-3/4" (171.5 mm)  | 0.25 lb (0.11 kg) |
| 640-1/4  | 1/4"             | 3" (76.2 mm)  | Red        | 6-3/4" (171.5 mm)  | 0.25 lb (0.11 kg) |
| 640-5/16 | 5/16"            | 3" (76.2 mm)  | Yellow     | 6-3/4" (171.5 mm)  | 0.25 lb (0.11 kg) |
| 640-3/8  | 3/8"             | 3" (76.2 mm)  | Blue       | 6-3/4" (171.5 mm)  | 0.25 lb (0.11 kg) |
| 640-7/16 | 7/16"            | 3" (76.2 mm)  | Brown      | 7-5/16" (185.7 mm) | 0.30 lb (0.14 kg) |
| 640-1/2  | 1/2"             | 3" (76.2 mm)  | Red        | 7-5/16" (185.7 mm) | 0.25 lb (0.11 kg) |
| 640-9/16 | 9/16"            | 4" (101.6 mm) | Orange     | 9-3/8" (238.1 mm)  | 0.40 lb (0.18 kg) |
| 640-5/8  | 5/8"             | 4" (101.6 mm) | Yellow     | 9-3/8" (238.1 mm)  | 0.40 lb (0.18 kg) |

\*3/16" magnetic nut driver does not have a hollow shaft.

**WARNING:** NOT insulated. Coating is intended for protection of circuits only.

## Cushion-Grip Multi-Nut Drivers

### Heavy-Duty Multi-Nut Drivers

- Multiple sizes in one convenient tool
- Heavy-duty handle and shaft exceed the torque performance of regular nut drivers
- Wrench-assist feature for added torque




32800

| Cat. No. | Description                        | Nut Driver Sizes                       | Shaft Length  | Overall Length     | Weight          |
|----------|------------------------------------|----------------------------------------|---------------|--------------------|-----------------|
| 32800    | 6-in-1 Multi-Nut Driver Heavy Duty | 3/16", 1/4", 5/16", 3/8", 7/16", 9/16" | 4" (101.6 mm) | 9-1/2" (241.3 mm)  | 1.2 lb (0.5 kg) |
| 32801    | 5-in-1 Multi-Nut Driver Heavy Duty | 3/16", 1/4", 5/16", 3/8", 9/16"        | 4" (101.6 mm) | 9-7/64" (231.4 mm) | 1.0 lb (0.5 kg) |



# Plastic-Handle Nut Drivers

**Meets or exceeds** applicable ASME / ANSI and MIL specifications.



## Hollow-Shaft Nut Drivers

**Includes core Plastic-Handle Nut Driver features plus:**

- Standard length works for most applications
- Fits over long bolts and studs
- Cat. Nos. SS8, SS10 and SS12 have smaller shaft length for work in close quarters



S11

| Cat. No. | Nut Driver Sizes | Shaft Length     | Handle Color | Overall Length    | Weight            |
|----------|------------------|------------------|--------------|-------------------|-------------------|
| SS8      | 1/4"             | 1-1/2" (38.1 mm) | Red          | 3-3/4" (95.3 mm)  | 0.15 lb (0.07 kg) |
| SS10     | 5/16"            | 1-1/2" (38.1 mm) | Amber        | 3-3/4" (95.3 mm)  | 0.15 lb (0.07 kg) |
| SS12     | 3/8"             | 1-1/2" (38.1 mm) | Blue         | 3-3/4" (95.3 mm)  | 0.15 lb (0.07 kg) |
| S5       | 5/32"            | 3" (76.2 mm)     | Amber        | 6-1/2" (165.1 mm) | 0.10 lb (0.05 kg) |
| S6       | 3/16"            | 3" (76.2 mm)     | Black        | 6-5/8" (168.3 mm) | 0.10 lb (0.05 kg) |
| S7       | 7/32"            | 3" (76.2 mm)     | Brown        | 6-5/8" (168.3 mm) | 0.10 lb (0.05 kg) |
| S8       | 1/4"             | 3" (76.2 mm)     | Red          | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| S9       | 9/32"            | 3" (76.2 mm)     | Orange       | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| S10      | 5/16"            | 3" (76.2 mm)     | Amber        | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| S11      | 11/32"           | 3" (76.2 mm)     | Green        | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| S12      | 3/8"             | 3" (76.2 mm)     | Blue         | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| S14      | 7/16"            | 3" (76.2 mm)     | Brown        | 7" (177.8 mm)     | 0.20 lb (0.09 kg) |
| S16      | 1/2"             | 3" (76.2 mm)     | Red          | 7" (177.8 mm)     | 0.20 lb (0.09 kg) |
| S18      | 9/16"            | 4" (101.6 mm)    | Red          | 8-1/2" (215.9 mm) | 0.30 lb (0.14 kg) |
| S20      | 5/8"             | 4" (101.6 mm)    | Red          | 8-1/2" (215.9 mm) | 0.30 lb (0.14 kg) |
| S66      | 3/16"            | 6" (152.4 mm)    | Black        | 9-5/8" (244.5 mm) | 0.15 lb (0.07 kg) |
| S86      | 1/4"             | 6" (152.4 mm)    | Red          | 9-5/8" (244.5 mm) | 0.15 lb (0.07 kg) |
| S106     | 5/16"            | 6" (152.4 mm)    | Amber        | 9-5/8" (244.5 mm) | 0.15 lb (0.07 kg) |
| S116     | 11/32"           | 6" (152.4 mm)    | Green        | 9-5/8" (244.5 mm) | 0.15 lb (0.07 kg) |
| S126     | 3/8"             | 6" (152.4 mm)    | Blue         | 9-5/8" (244.5 mm) | 0.15 lb (0.07 kg) |
| S146     | 7/16"            | 6" (152.4 mm)    | Brown        | 10" (254.0 mm)    | 0.20 lb (0.09 kg) |
| S166     | 1/2"             | 6" (152.4 mm)    | Red          | 10" (254.0 mm)    | 0.20 lb (0.09 kg) |

| Cat. No. | Set Contains                           | Weight          |
|----------|----------------------------------------|-----------------|
| K7       | Nut Driver Set 3" Shanks, 7 Pc         | 1.2 lb (0.5 kg) |
| Cat. No. | Description                            |                 |
| S6       | 3/16" Hollow Shank Nut Driver 3" Shank |                 |
| S8       | 1/4" Hollow Shank Nut Driver 3" Shank  |                 |
| S10      | 5/16" Nut Driver 3" Hollow Shaft       |                 |
| S11      | 11/32" Nut Driver, Plastic Grip 3" L   |                 |
| S12      | 3/8" Hollow Shaft Nut Driver 3" Shaft  |                 |
| S14      | 7/16" Hollow Shank Nut Driver 3" Shank |                 |
| S16      | 1/2" Nut Driver 3" Hollow Shank        |                 |
| Cat. No. | Set Contains                           | Weight          |
| 89904    | 7 Piece Nut Driver Set 6" Shanks       | 1.2 lb (0.5 kg) |
| Cat. No. | Description                            |                 |
| S66      | 3/16" Individual Nut Driver 6" Shank   |                 |
| S86      | 1/4" Individual Nut Driver 6" Shank    |                 |
| S106     | 5/16" Individual Nut Driver 6" Shaft   |                 |
| S116     | 11/32" Individual Nut Driver 6" Shaft  |                 |
| S126     | 3/8" Individual Nut Driver 6" Shaft    |                 |
| S146     | 7/16" Individual Nut Driver 6" Shank   |                 |
| S166     | 1/2" Individual Nut Driver 6" Shank    |                 |

Set Cat. No. K7 includes a vinyl pouch which hangs up or rolls up



## Plastic Handle, Hollow-Shaft Nut Drivers

### Super-Long Nut Drivers - 18" (457 mm) Shafts

Includes core Plastic-Handle Nut Driver features plus:

- Ideal for reaching into walls and other hard-to-reach places where added length is necessary
- Cat. No. S1018 has a non-magnetic tip; Cat. Nos. S818M and S1018M have magnetic tips



S1018



| Cat. No. | Nut Driver Sizes | Shaft Length   | Handle Color | Overall Length      | Weight            |
|----------|------------------|----------------|--------------|---------------------|-------------------|
| S1018    | 5/16"            | 18" (457.2 mm) | Amber        | 21-5/8" (549.27 mm) | 0.25 lb (0.11 kg) |
| S818M    | 1/4"             | 18" (457.2 mm) | Red          | 21-5/8" (549.3 mm)  | 0.25 lb (0.11 kg) |
| S1018M   | 5/16"            | 18" (457.2 mm) | Amber        | 21-5/8" (549.3 mm)  | 0.25 lb (0.11 kg) |

### Metric Nut Drivers

Includes core Plastic-Handle Nut Driver features plus:

- Standard length works for most applications
- Fits over long bolts and studs



70209

| Cat. No. | Nut Driver Sizes | Shaft Length | Handle Color | Overall Length    | Weight            |
|----------|------------------|--------------|--------------|-------------------|-------------------|
| 70204    | 4 mm             | 3" (76.2 mm) | Black        | 6-5/8" (168.3 mm) | 0.10 lb (0.05 kg) |
| 70245    | 4.5 mm           | 3" (76.2 mm) | Black        | 6-5/8" (168.3 mm) | 0.10 lb (0.05 kg) |
| 70205    | 5 mm             | 3" (76.2 mm) | Black        | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| 70255    | 5.5 mm           | 3" (76.2 mm) | Black        | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| 70206    | 6 mm             | 3" (76.2 mm) | Black        | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| 70207    | 7 mm             | 3" (76.2 mm) | Black        | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| 70208    | 8 mm             | 3" (76.2 mm) | Black        | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| 70209    | 9 mm             | 3" (76.2 mm) | Black        | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| 70210    | 10 mm            | 3" (76.2 mm) | Black        | 7" (177.8 mm)     | 0.15 lb (0.07 kg) |
| 70211    | 11 mm            | 3" (76.2 mm) | Black        | 7" (177.8 mm)     | 0.20 lb (0.09 kg) |

| Cat. No. | Set Contains                          | Weight          |
|----------|---------------------------------------|-----------------|
| 70200    | Metric Nut Driver Set 3" Shafts 10 Pc | 1.9 lb (0.8 kg) |

| Cat. No. | Description                       |
|----------|-----------------------------------|
| 70204    | 4 mm Metric Nut Driver 3" Shaft   |
| 70245    | 4.5 mm Metric Nut Driver 3" Shaft |
| 70205    | 5 mm Metric Nut Driver 3" Shaft   |
| 70255    | 5.5 mm Metric Nut Driver 3" Shaft |
| 70206    | 6 mm Metric Nut Driver 3" Shaft   |
| 70207    | 7 mm Metric Nut Driver 3" Shaft   |
| 70208    | 8 mm Metric Nut Driver 3" Shaft   |
| 70209    | 9 mm Metric Nut Driver 3" Shaft   |
| 70210    | 10 mm Metric Nut Driver 3" Shaft  |
| 70211    | 11 mm Metric Nut Driver 3" Shaft  |

Set includes white enameled metal stand with identification labels for easy selection of tool

## Plastic Handle Nut Drivers

### Magnetic Nut Drivers - Solid Shafts

Includes core Plastic-Handle Nut Driver features plus:

- Powerful nut-holding magnet built into solid shaft



S818M



| Cat. No. | Nut Driver Sizes | Shaft Length  | Handle Color | Overall Length    | Weight            |
|----------|------------------|---------------|--------------|-------------------|-------------------|
| S8M      | 1/4"             | 3" (76.2 mm)  | Red          | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| S10M     | 5/16"            | 3" (76.2 mm)  | Amber        | 6-5/8" (168.3 mm) | 0.15 lb (0.07 kg) |
| S86M     | 1/4"             | 6" (152.4 mm) | Yellow       | 9-5/8" (244.5 mm) | 0.15 lb (0.07 kg) |
| S106M    | 5/16"            | 6" (152.4 mm) | Amber        | 9-5/8" (244.5 mm) | 0.15 lb (0.07 kg) |
| S126M    | 3/8"             | 6" (152.4 mm) | Blue         | 9-5/8" (244.5 mm) | 0.15 lb (0.07 kg) |

## Tapping Tools

### Cushion-Grip Multi-Bit Tap Tool Driver

- Increases job speed by combining taps and drivers in one tool
- Six common tap sizes (6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20)
- Each tap size rethreads to next larger size if threads are stripped



32517




| Cat. No. | Nut Driver Sizes  | Phillips Bits | Slotted Bits                  | Other Bits                                    | Shank Length  | Handle Color | Overall Length    | Weight            |
|----------|-------------------|---------------|-------------------------------|-----------------------------------------------|---------------|--------------|-------------------|-------------------|
| 32517    | 1/4", 5/16", 3/8" | #1, #2        | 1/4" (6.4 mm), 3/16" (4.8 mm) | Taps: 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20 | 4" (101.6 mm) | Yellow/Black | 7-3/4" (196.9 mm) | 0.50 lb (0.23 kg) |

### Cushion-Grip 6-in-1 Tap Tool

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions
- Each tap size rethreads to next larger size if threads are stripped



626




| Cat. No. | Tap Sizes                                          | Overall Length    | Weight            |
|----------|----------------------------------------------------|-------------------|-------------------|
| 626      | 6-in-1 Tap 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20 | 7-3/4" (196.9 mm) | 0.25 lb (0.11 kg) |

### 6-in-1 Tapping Tool

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions
- Each tap size rethreads to next larger size if threads are stripped
- Two high-carbon steel taps are secured in reversible holder



627-20




| Cat. No. | Tap Sizes                               | Overall Length    | Weight            |
|----------|-----------------------------------------|-------------------|-------------------|
| 627-20   | 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20 | 7-5/8" (193.7 mm) | 0.35 lb (0.16 kg) |

### Triple Taps

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions
- Each tap size rethreads to next larger size if threads are stripped



625-24



| Cat. No. | Tap Sizes         | Overall Length    | Weight            |
|----------|-------------------|-------------------|-------------------|
| 625-24   | 6-32, 8-32, 10-24 | 7-1/8" (181.0 mm) | 0.20 lb (0.09 kg) |
| 625-32   | 6-32, 8-32, 10-32 | 7-1/8" (181.0 mm) | 0.20 lb (0.09 kg) |

## Scratch Awls

### Cushion-Grip Scratch Awl

- Professional, heavy-duty, hard-pointed awl
- Scribes metal, starts screw holes, performs a variety of piercing and punching jobs
- Rigid, chrome-plated, heat-treated, tempered-steel shank has full reinforcing bolster at handle for extra strength and impact reinforcement
- Cat. No. 650DD has plated metal strike cap to protect handle from hammer blows and is engineered, manufactured and tested for prying, chiseling and punching



Cat. No.  
650 only



650DD

| Cat. No. | Shank Length     | Overall Length    | Weight            |
|----------|------------------|-------------------|-------------------|
| 650      | 3-1/2" (88.9 mm) | 7-7/8" (200.0 mm) | 0.25 lb (0.11 kg) |
| 650DD    | 3-1/2" (88.9 mm) | 7-7/8" (200.0 mm) | 0.30 lb (0.14 kg) |

### Steel Scratch Awl

- One-piece forged-steel blade and bolstered shank
- Heat-treated for long life
- Well-balanced for top efficiency during use
- Black finish for rust resistance



66385

| Cat. No. | Overall Length | Shank Length     | Weight            |
|----------|----------------|------------------|-------------------|
| 66385    | 7" (177.8 mm)  | 3-1/2" (88.9 mm) | 0.30 lb (0.14 kg) |

## Conduit Reamers

### Conduit-Fitting and Reaming Screwdriver

- Hooded-blade design keeps tip from slipping out of screws, especially when tightening hard-to-reach conduit fittings. Thicker hood is designed for rugged use
- Reams both the inside and outside of the conduit at the same time
- 5/16" (8 mm) screwdriver tip with 2-1/2" (64 mm) long shank
- Longer Cushion-Grip handle provides comfort and more torque for reaming
- Replaceable reaming blade is now held in place with a 1/6" (1.5 mm) set screw



85191

| Cat. No. | Conduit Size                                 | Overall Length    | Weight            |
|----------|----------------------------------------------|-------------------|-------------------|
| 85191    | 1/2" (12.7 mm), 3/4" (19.1 mm), 1" (25.4 mm) | 7-1/2" (190.5 mm) | 0.50 lb (0.23 kg) |



19353  
CONDUIT REAMER  
REPLACEMENT BLADE, 2pk

### Conduit Reamer

- Locks onto screwdrivers; reams and smooths thin-wall conduit
- Reams ID and OD at the same time
- Two set-screws for round- and square-shank screwdrivers
- Fits up to 3/8" (10 mm) keystone-tip screwdrivers
- NOT for use on power tools



19352



19353  
CONDUIT REAMER  
REPLACEMENT BLADE, 2pk

| Cat. No. | Conduit Size                                 | Overall Length    | Weight            |
|----------|----------------------------------------------|-------------------|-------------------|
| 19352    | 1/2" (12.7 mm), 3/4" (19.1 mm), 1" (25.4 mm) | 6-3/4" (171.5 mm) | 0.20 lb (0.09 kg) |

### Power Conduit Reamer

**IMPACT RATED!**

- Ream conduit and install fittings in a fraction of the time
- Designed to fit into power drill chucks and quick release adapters; impact ready
- Includes precision engineered replaceable reaming blade
- Replacement blades are available and the only approved blade for use in this tool
- Replacement bits are available but any standard 1/4" hex bit will work

Precision engineered  
replaceable reaming blade



1/4" hex  
quick connect



85091

**4x Stronger**  
Bit Retention



19353  
CONDUIT REAMER  
REPLACEMENT BLADE, 2pk



**NOTE:** Read and follow safety instructions in power tool owner's manual.

| Cat. No. | Conduit Size                                 | Overall Length    | Weight            |
|----------|----------------------------------------------|-------------------|-------------------|
| 85091    | 1/2" (12.7 mm), 3/4" (19.1 mm), 1" (25.4 mm) | 5-3/4" (146.1 mm) | 0.33 lb (0.15 kg) |

See page 310 for additional information on warnings.




## Power Driver Bits

### Power Drivers

- Manufactured in the U.S.A. to ensure proper fit in every application, each power driver is precision machined, heat treated and finished to the gold standards Klein Tools puts into every screwdriver blade. Proprietary processes create the longest life power driver bit in the industry. Tight fitting tips reduce wear and deliver the premium performance you expect from a Klein.
- Precision machined for better fit, more torque and less wear
- Custom heat treated for long life

Klein Lasts Longer Before Cam Out



PH3-6-2



PH2-1-15



C1-35-5

| Cat. No. | Overall Length   | Bit Type               | Package Quantity | Weight           |
|----------|------------------|------------------------|------------------|------------------|
| PH115    | 1" (25.4 mm)     | #1 Phillips            | 5                | 0.10 oz (2.8 g)  |
| PH1355   | 3-1/2" (88.9 mm) | #1 Phillips            | 5                | 0.50 oz (14.2 g) |
| PH162    | 6" (152.4 mm)    | #1 Phillips            | 2                | 0.9 oz (26 g)    |
| PH2115   | 1" (25.4 mm)     | #2 Phillips            | 15               | 0.10 oz (2.8 g)  |
| PH2355   | 3-1/2" (88.9 mm) | #2 Phillips            | 5                | 0.50 oz (14.2 g) |
| PH262    | 6" (152.4 mm)    | #2 Phillips            | 2                | 0.9 oz (26 g)    |
| PH315    | 1" (25.4 mm)     | #3 Phillips            | 5                | 0.10 oz (2.8 g)  |
| PH3355   | 3-1/2" (88.9 mm) | #3 Phillips            | 5                | 0.50 oz (14.2 g) |
| PH362    | 6" (152.4 mm)    | #3 Phillips            | 2                | 0.9 oz (26 g)    |
| SL31615  | 1" (25.4 mm)     | 3/16" (4.8 mm) Slotted | 5                | 0.10 oz (2.8 g)  |
| SL316355 | 3-1/2" (88.9 mm) | 3/16" (4.8 mm) Slotted | 5                | 0.50 oz (14.2 g) |
| SL1415   | 1" (25.4 mm)     | 1/4" (6.4 mm) Slotted  | 5                | 0.10 oz (2.8 g)  |
| SL14355  | 3-1/2" (88.9 mm) | 1/4" (6.4 mm) Slotted  | 5                | 0.50 oz (14.2 g) |

#### Power Driver Sets

| Cat. No. | Overall Length   | Bit Type                                            | Package Quantity | Weight            |
|----------|------------------|-----------------------------------------------------|------------------|-------------------|
| 32234    | 3-1/2" (88.9 mm) | #1 and #2 Phillips, #1 and #2 Square, 3/16" Slotted | 5                | 0.10 lb (0.05 kg) |
| 32235    | 6" (152.4 mm)    | Phillips #1 and #3                                  | 2                | 0.10 lb (0.05 kg) |

### Power Nut Drivers

- Available in several sizes, these hollow shaft magnetic nut drivers are designed for long bolts, studs or threaded rod jobs.
- Rare Earth magnetic head holds nuts and bolts to aid in hard to reach installations.
- The 5" and 10" models feature a wrench assist end, designed for high torque loosening found in many jobs.
- Power Nut Driver Set contains 1/4", 5/16" and 3/8" nut drivers (Cat. No. 32759)



Hollow magnetic\* shafts for nut running



PND7165



PND71610




32759

| Cat. No. | Overall Length       | Shaft Length   | Hollow Depth        | Nut Driver Sizes  | Weight            |
|----------|----------------------|----------------|---------------------|-------------------|-------------------|
| 32759    | 6-5/16" (160.3 mm)   | 2" (50.8 mm)   | 1-7/8" (47.6 mm)    | 1/4", 5/16", 3/8" | 0.10 lb (0.05 kg) |
| PND7165  | 6-5/16" (160.3 mm)   | 5" (127.0 mm)  | 3-11/16" (93.7 mm)  | 7/16"             | 0.16 lb (0.07 kg) |
| PND125   | 6-19/64" (159.9 mm)  | 5" (127.0 mm)  | 3-23/32" (94.5 mm)  | 1/2"              | 0.19 lb (0.09 kg) |
| PND9165  | 6+21/64" (160.7 mm)  | 5" (127.0 mm)  | 3-5/8" (92.1 mm)    | 9/16"             | 0.23 lb (0.10 kg) |
| PND71610 | 11-5/16" (287.3 mm)  | 10" (254.0 mm) | 8-13/16" (223.8 mm) | 7/16"             | 0.25 lb (0.11 kg) |
| PND1210  | 11-19/64" (286.9 mm) | 10" (254.0 mm) | 8-23/32" (221.5 mm) | 1/2"              | 0.31 lb (0.14 kg) |
| PND91610 | 11-5/16" (287.3 mm)  | 10" (254.0 mm) | 8-5/8" (219.1 mm)   | 9/16"             | 0.35 lb (0.16 kg) |

**NOTE:** Read and follow safety instructions in power tool owner's manual.





## Power Driver Bits

### Magnetic Hex Drivers

- For driving sheet metal screws
- Strong rare earth magnets for maximum holding
- 1/4" (6.4 mm) hex shank with quick release groove




86602

| Cat. No. | Description                         | Overall Length   | Weight            |
|----------|-------------------------------------|------------------|-------------------|
| 86600    | 1/4" Magnetic Hex Drivers, 3-pack   | 1-3/4" (44.5 mm) | 0.12 lb (0.05 kg) |
| 86601    | 5/16" Magnetic Hex Drivers, 3-pack  | 1-3/4" (44.5 mm) | 0.14 lb (0.06 kg) |
| 86602    | 3/8" Magnetic Hex Drivers, 3-pack   | 1-3/4" (44.5 mm) | 0.16 lb (0.07 kg) |
| 8660010  | 1/4" Magnetic Hex Drivers, 10-pack  | 1-3/4" (44.5 mm) | 0.43 lb (0.20 kg) |
| 8660110  | 5/16" Magnetic Hex Drivers, 10-pack | 1-3/4" (44.5 mm) | 0.49 lb (0.22 kg) |
| 8660210  | 3/8" Magnetic Hex Drivers, 10-pack  | 1-3/4" (44.5 mm) | 0.57 lb (0.26 kg) |

### Drill/Tap/Deburr Set

- For aluminum, brass, copper, plastic, and up to 10 gauge metal
- 1/4" hex for easier application with quick connect
- Set of six tap sizes plus two extra of the smallest taps
- For use on up to 10 gauge metal
- Made of high speed steel for added durability

**IMPACT RATED!**



32217

| Cat. No. | Tap Sizes                                       | Overall Length    | Weight          |
|----------|-------------------------------------------------|-------------------|-----------------|
| 32217    | 6-32 (2), 8-32 (2), 10-24, 10-32, 12-24, 1/4-20 | 4" (101.6 mm)     | 1.5 lb (0.7 kg) |
| Cat. No. | Tap Sizes                                       | Weight            |                 |
| 32237    | 6-32                                            | 0.25 lb (0.11 kg) |                 |
| 32238    | 8-32                                            | 0.25 lb (0.11 kg) |                 |
| 32239    | 10-32                                           | 0.25 lb (0.11 kg) |                 |
| 32240    | 10-24                                           | 0.25 lb (0.11 kg) |                 |
| 32241    | 12-24                                           | 0.25 lb (0.11 kg) |                 |
| 32242    | 1/4-20                                          | 0.25 lb (0.11 kg) |                 |

**NOTE:** Read and follow safety instructions in power tool owner's manual.

See page 310 for additional information on warnings.

