

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212030006](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form B-10mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/DC, Transparent, Silicone Gasket

Documents:

Drawing (PDF)	Packaging Specification PK-121203-C92-001 (PDF)
Product Specification PS-121201-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification STR-1251-001 (PDF)	

General

Product Family	Field Attachable / Accessories
Series	121203
Form	B - 10mm
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	883906916305

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	19.435/g
Orientation	90° Angle
Pitch - Mating Interface	10.00mm
Poles	2
Temperature Range - Operating	-40°C to +125°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC/DC

Material Info

Engineering Number	C92200T0U
--------------------	-----------

Reference - Drawing Numbers

Packaging Specification	PK-121203-C92-001
Product Specification	PS-121201-001-001, STR-1251-001
Sales Drawing	SD-121203-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
ED/71/2019 (16 July
2019)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[121203](#) Series