

16-Port NetDirector 1U Rackmount Console KVM Switch w/17" LCD

MODEL NUMBER: **B020-016-17**



Description

Tripp Lite's 16-port Console KVM Switch with 17" LCD is the optimal solution for controlling multiple computers from one keyboard, mouse and monitor. This single unit combines a 16 port KVM switch, keyboard, 17" LCD monitor and touchpad; all in a mere 1U of rack space. Stores neatly in the rack, pulls out when needed. Easily switch ports using the On-Console push buttons, On Screen Display (OSD) or keyboard hot key commands. Control PS/2 or USB computers/servers using P774-Series (PS/2) and P776-Series (USB) KVM Cable kits. Includes an extra HD15 and (2) PS/2 ports on the rear of the unit, which allows for connection of a Tripp Lite B051-000 IP Remote Access Unit or an external console. Compatible with all major operating systems except Mac and Sun.

Features

- Combines a 16 port KVM switch, 17" LCD screen, keyboard and touchpad in a 1U rackmountable drawer
- Supports video resolutions up to 1280 x 1024
- Switch between ports via pushbuttons, OSD or keyboard hot key commands
- Includes autoscans feature
- Multi-level password security (administrator/user) to ensure only those with authorization can access connected computers/servers
- Includes additional VGA monitor and PS/2 keyboard/mouse ports, allowing for the connection of an external console, or a Tripp Lite B051-000 IP Remote Access Unit
- Hot pluggable; add or remove computers without having to power down the switch
- Auto-sensing of station position on daisy chained installations; no need for manual DIP switch setting, front panel LED indicates station position
- Port names automatically reconfigured when station sequence is changed
- Firmware upgradeable
- Power Consumption: 120V 60Hz 22.8W; 230V 50Hz 24W
- Compatible with all major operating systems except Mac and Sun
- Constructed of heavy-duty steel housing

Highlights

- Combines a 16 port KVM switch, 17" LCD screen, keyboard, and touchpad in a 1U rackmountable drawer
- Supports video resolutions up to 1280 x 1024
- Two level password security (administrator/user)
- Compatible with all major operating systems except Mac and Sun

System Requirements

- PS/2 or USB computer
- (1) P774-Series (PS/2) or P776-Series (USB) KVM Cable kit is required for each connected computer/server
- Compatible with all major operating systems except Mac and Sun

Package Includes

- 16 Port Console KVM Switch w/17" LCD
- 6 ft. PS/2 KVM Cable Kit
- 6 ft. USB KVM Cable Kit
- C13 to 5-15P power cord
- RJ11 to DB9 Firmware upgrade cable
- Owners Manual CD

Specifications

General Info	
Product Group	KVM SWITCHES
OVERVIEW	
# Of Users	1
Console	Yes
Port Control	Push Buttons, Hotkeys, OSD
Max CPU	16
PC/Server	PS/2
Shipping Weight	47.4 lbs.
Cat5 KVM Switch	No
IP Remote Access	No
UPC ASSIGNMENT	
Unit Carton UPC#	037332125378
PHYSICAL	
Unit Dimensions (hwd / cm)	4.45 x 42.55 x 60.96
Color	Black
Style	1U Rackmount Console
LCD Monitor (in.)	17
LCD Monitor (cm)	43.18
ENVIRONMENTAL	
Relative Humidity	0% TO 80% RH
Operating Temperature	32 DEGREES TO 120 DEGREES F
BTUs	(88 BTUs at 120V, 50Hz) / (93 BTUs at 120V, 50Hz)
CONNECTIONS	
Ports	16
Computer/Server Ports	(x16) HD15 (Female)
Other Ports	DB25 (Male)
Local Console Ports - Port 1	HD15 (Female)
Local Console Ports - Port 2	(x2) MiniDIN6 (Female)

CERTIFICATIONS

Approvals	UL, cUL, CE, FCC, RoHS
-----------	------------------------

WARRANTY

Product Warranty Period (Worldwide)	1-year limited warranty
-------------------------------------	-------------------------

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.