

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

06JUL,06JUL1995

© COPYRIGHT 1995 BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD

G

REVISED FJD0-0256-03

29SEP2004

T.I

D.M


G1

REVISED PER ECO-10-000444


08JAN10

KK

AEG



推奨基板寸法
(RECOMENDED P.C.BOARD DIMENSION)



① FINISH : CONTACT AREA ; TIN PLATING(MATTE) 2.0 μmMIN
OVER ALL Ni PLATING.
ACTION AREA ; TIN PLATING(MATTE) 0.5-2.54 μm
OVER ALL Ni PLATING.
ANOTHER ; TIN PLATING(MATTE) NOT CONTOROL THK.

2. MATCHING SOCKET IS TO BE USE P/N:350550-3,350551-3
350689-3,350919-3,640310-3

3. CURRENT : 15A/PIN MAX.
WHEN USE AWG#14 UL-1015 ×CENTER WIRE N=41/0.28mm
×INSULATION DIA 3.8mm

② FINISH : CONTACT AREA ; GOLD PLATING 0.76 μmMIN
OVER ALL Ni PLATING.
ACTION AREA ; TIN PLATING(MATTE) 0.5-2.54 μm
OVER ALL Ni PLATING.
ANOTHER ; TIN PLATING(MATTE) NOT CONTOROL THK.

5. PRODUCT SPECIFICATION : 108-5222

③ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI


④ メッキ仕様:
コンタクト部: ニッケル下地メッキの上に 2.0 μmMIN のスズめっき(半光沢)を施す。
アクション部: ニッケル下地メッキの上に 0.5-2.54 μm のスズめっき(半光沢)を施す。
それ以外は特に規定しないスズめっき(半光沢)を施す。

2. 相手側ソケットは P/N:350550-3,350551-3,350689-3
350919-3,640310-3 を使用のこと。


3. 規格電流: 15A 最大 (1極当たり)
但し、使用電線 AWG#14 UL-1015
芯線: 4本/0.26mm
被覆外形: φ3.8mm

⑤ メッキ仕様:
コンタクト部: ニッケル下地の上に 0.76 μmMIN の金メッキを施す。
アクション部: ニッケル下地の上に 0.5-2.54 μm のスズめっき(半光沢)を施す。
それ以外は特に規定しないスズめっき(半光沢)を施す。

5. 製品規格: 108-5222



⑥ DATE CODE



基板推奨寸法
(RECOMENDED P.C.BOARD DIMENSION)

⑥ OBSOLETE	↑	↑	△	173924-2
銅合金 COPPER ALLOY	↑	↑	△	173924-1
② コンタクト CONTACT	① ハウジング HOUSING	表面処理 FINISH	型番 PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.KODAIRA 03JUL1995	tyco Electronics Tyco Electronics AMP K.K. Kawasaki, Japan			
DIMENSIONS: 単位: 耗 MM		CHK H.AMIKURA 03JUL1995			NAME 名称 2POS, ACTION PIN U-M-N-L PIN HEADER ASSEMBLY	
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	APVD T.SASAKI 06JUL1995				
	0 PLC ± 1 PLC ± 10 ≤ ±0.2 2 PLC ± 10 ≤ ±30 ±0.25 3 PLC ± 30 ≤ ±100 ±0.3 4 PLC ±	PRODUCT SPEC 製品規格 108-5222				
	ANGLES ±3°	APPLICATION SPEC 取付適用規格				
MATERIAL 材料 SEETABLE	FINISH 仕上 △ △	WEIGHT 2.0 g	SIZE A3	CAGE CODE 00779	DRAWING NO 番号 C-173924	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 尺度 1:1	SHEET 1 OF 1	REV G1	