

Part Number:1200720308

Status:Active

Overview:Brad Micro-Change (M12) Connectors

Description:Micro-Change (1/2"-20 UNF) Single-Ended Cordset, 3 Poles, Male (Straight)to Pigtail, 22 AWG, PVC Cable, 6.10m (20.0') Length



Series image - Reference only

Documents:

図面 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E152210
一般	
Connector End A	Micro-Change (1/2" - 20 UNF)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	銅合金
概要	Brad Micro-Change (M12) Connectors
製品名	Micro-Change (1/2" - 20 UNF)
Protocol	PROFIBUS
Region	America
タイプ	Single Ended
UPC	78678834648
機械的性能/材質	
Cable Diameter	5.72mm (.225")
ケーブル長	6.10m (20.0')
Color - Cable Jacket	イエロー
Coupling Style	ネジ山
ジェンダー	メール-ピッグテール
Keyway	両用
LED Indicator	無
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - O-Ring	Nitrile Rubber
材質 - 嵌合部メッキ	金
実装形態	Straight to Pigtail
Poles	3
使用温度範囲	-20° C to +105° C
電線サイズ (AWG)	22
ケーブル種別	UL 2661
電気的性能	
最大定格電流	4.0A
最大定格電圧	250V AC/DC
参考情報	
Engineering Number	703006D02F200
図面・仕様書情報	
製品図面	SD-120072-005

EU ELV

Not Reviewed

EU RoHSChina RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHSNot Reviewed

ELVNot Reviewed

RoHS PhthalatesNot Reviewed

Search Parts in this Series

120072 Series