

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0733660062](#)
Status: **Active**
Overview:
Description: 50 Ohms, MCX Jack Receptacle, Vertical, Straight, 7.10mm Height, 1.57mm Standoff Height, Nickel (Ni) Plated Body, Tape and Reel

General

Product Family	RF/Coax Connectors
Series	73366
Overview	mcx
Product Name	MCX
Style	PCB
Type	Microminiature
UPC	822350652391
Wire/Cable Type	N/A

Physical

Gender	Jack
Keying to Mating Part	None
Net Weight	0.559/g
Orientation	Straight
PCB Mounting	Through Hole
PCB Thickness - Recommended	1.20mm
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Panel Mount Method	N/A
Reverse Polar	No

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Solder Process Data

Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-73366-006-001, SD-73366-619-000
---------------	------------------------------------

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)
Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[73366](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION