

**General ordering data**

Order No.	1767690000
Part designation	ZDU 10/3AN
Version	Feed-through terminal, 10 mm ² , Tension clamp connection, Wemid, beige, TS 35
EAN	4032248122745
Qty.	20 pc(s).

Product notes

Note, technical data	Cross-connection of ZDU 10 and ZDU 16 is possible using the ZQV 16-10. Cross-connection of ZDU 10 and ZDU 35 is possible using the ZQV 35-10.
Product description	Z-series standard ranges provide solutions for conductor cross-sections from 0.05 to 35 mm ² .

PT OKIECEEx/ATEX rating data

EU-type examination certificate	KEMA00ATEX2107U
Download, German	KEMA00ATEX2107U_d.pdf
Download English	KEMA00ATEX2107U_e.pdf
IECEEx Certificate of Conformity	IECEXULD05.0009U
ATEX voltage	550 V
ATEX current	50 A
ATEX conductor cross-section	10 mm ²
IECEEx voltage	550 V
IECEEx current	50 A
IECEEx conductor cross-section	10 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG-Baumusterprüfbescheinigung/IECEEx-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	beige
Connection direction	top
End plate required	Yes
Explosion-tested version "Ex e"	Yes
Installation advice	TS 35
Insulating material	Wemid
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	3
Open sides	right
Operating temperature range	- 50 °C, + 120 °C
Product family	Z-series
Type of connection	Tension clamp connection
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	Feed-through terminal

CSA rating data

Voltage (CSA)	600 V
CSA current	55 A
Min. cross-section (CSA)	AWG 16
Max. cross-section (CSA)	AWG 6

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	1.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	10 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	1.31 mm ²
Clamping range, max.	16 mm ²
Type of connection	Tension clamp connection
2nd type of connection	clamped
Connection direction	top
No. of connections	3
Stripping length	18 mm
Blade size	1.0 x 5.5 mm
Gauge to IEC 60947-1	A6
Solid, min.	1.5 mm ²
Solid, max.	16 mm ²
Stranded, min.	1.5 mm ²
Stranded, max.	16 mm ²
Flexible, min.	1.5 mm ²
Flexible, max.	10 mm ²
Flexible with ferrule, min. (DIN 46228/1)	1.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	10 mm ²
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	1.5 mm ²
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	10 mm ²

Conductors for clamping (rated connection)

AWG conductor size, min.	AWG 16
AWG conductor size, max.	AWG 6
AWG conductor size, min.	1.31 mm ²
AWG conductor size, max.	13.3 mm ²

Dimensions

Width	10.1 mm
Height of lowest version	50.5 mm
Length	99 mm
TS 35 offset	39 mm

Rating data

Rated cross-section	10 mm ²
Rated voltage	800 V
Rated impulse voltage	8 kV
Rated current	57 A
Standards	IEC 60947-7-1
Current with max. conductor	57 A
Pollution severity	3

UL rating data

Voltage (UL)	600 V
Current (UL)	60 A
Min. cross-section (UL)	AWG 16
Max. cross-section (UL)	AWG 6

Approvals

Approvals institutes

**Downloads**

STEP	1767690000_29572_ZDU_10-3AN_STP.stp
------	-------------------------------------

Classifications

eClass 4.1	27-14-11-20
eClass 5.0	27-14-11-20
eClass 5.1	27-14-11-20

Similar products

Order No.	Part designation	Version
-----------	------------------	---------

1746750000	ZDU 10	Feed-through terminal, 10 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1746760000	ZDU 10 BL	Feed-through terminal, 10 mm ² , Tension clamp connection, Wemid, blue, TS 35
1767700000	ZDU 10/3AN BL	Feed-through terminal, 10 mm ² , Tension clamp connection, Wemid, blue, TS 35