

NOTES:


① MAT'L: PURE NICKEL

PLATING: NONE

STUD SIZES: (±.005)

02 = .094 413 = .413
 04 = .119 209 = .209
 06 = .146
 08 = .173
 10 = .198
 14 = .265
 56 = .328
 38 = .390

ALL DIMENSIONS = INCHES
 M M



FILE NO.

BB-CD-101-04

A

Shown - 125 & 125 in direct
 FOR 70818 @ 97-4-29

WIRE SIZE: 16-14 AWG
 1.0-2.5 MM²

PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	AVAILABLE STUD SIZES	
	.534 13.56	.554 14.07	1.036 26.31	10,14,56,38,413	
BB-U-123-	.250 6.35	.209 5.31	.560 14.22	02,04,06,08	
BB-U-125-	.467 11.86	.388 9.86	.837 21.26	10,14,56	
BB-U-137-	.312 7.92	.285 7.24	.645 16.38	04,06,08,10 209	
	.342 8.69	.310 7.87	.696 17.68	04,06,08,10	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED					
FRAC.	DEC.	ANG.	SCALE:	NTS	DATE
±	±	±	DRAWN. BY: EMF	2-3-87	
			CHKD. BY:		
			APPRO. BY:		
TITLE: TEMP-TERM (1200°) RING TONGUE TERMINAL KRIMPITE 100-SERIES					
DWG. NO.	A	CUSTOMER	DWG.		

ETC
 INCORPORATED