Identification



Identification Products

HellermannTyton

Identification Products

Table of Contents

TagPrint Pro 3.0 Software 4

Printers 6

Thermal Transfer Labels 8

Self Laminating Label 10

ShrinkTrak Labels 12

Foam Nameplates 14

Tip Tags 15

Pre-Printed Warning Labels 16

Continuous Roll Vinyl Labels 18

Specifications 20

TagPrint PRO 3.0

Increase Productivity, Reduce Errors and Decrease Time Spent Producing Labels with a Complete Labeling Management Solution from HellermannTyton

HellermannTyton's labeling system is comprised of the feature-rich labeling design software – TagPrint Pro 3.0, the highest quality thermal transfer, laser and ink jet printable labels, and a complete line of desk top thermal transfer printers.

Simplify Your Label Design and Printing Process with TagPrint Pro 3.0

TagPrint® Pro 3.0 is the cost-effective, easy-to-use label design and printing software in the HellermannTyton labeling system for achieving improved efficiency in wire and component marking, asset tagging, and structured cabling identification. Compatible with Windows® 7, Vista and XP as well as future operating systems such as Windows® 8, TagPrint® Pro 3.0 delivers an individualized, task-based experience that enables a user to easily develop labels with bar codes, text and graphics to meet numerous applications.

Designed for the industry specific needs of a business producing products on a shop floor or labeling products at a remote job site, the intuitive interface of TagPrint Pro 3.0 simplifies the process of creating labels. TagPrint® Pro 3.0 streamlines labeling production by offering a user full control over the importing or entering of data, advanced security features, the option to group label designs under a single file name or job number, and the ability to batch print to either one or more printers at the same time.

Increase efficiency and reduce labor. TagPrint Pro 3.0 allows for complete management of the labeling process with a label design software system that simplifies the label creation process used to identify cables, tubes, conduits, components and equipment.

Familiar Task-based Navigation

TagPrint Pro 3.0 has a Ribbon interface that offers quick and easy access to the commands that are needed to complete a task. Commands are organized in logical groups, which are collected together under tabs. Each tab relates to a type of activity, such as "Label", "Table", "Print" and "Utility".

Batch Printing

3.0 has a"print-later" feature for the purpose of batching under one file name in a simple print utility. Using built-in Macros, design each label and then define print options for execution at time of printing. Access the project file and concurrently print labels to a single printer or multiple printers.

At-a-glance Interface

Whether it is one label or a page of labels, the 3.0 interface was designed to allow ease of control over print jobs from a single screen. Information is viewable at a glance so a user can view object properties, data information, and actual label layout at the same time. When changes are made, information is updated.

Built-in Security

TagPrint Pro 3.0 offers a built-in security system for the restriction of use or protection of data. This feature allows the user to lockout or password protect label designs and data tables from unauthorized label editing. Available for purchase as a single-user or network license.

Expanded Import Capabilities and "Live Sync"

3.0 has the ability to import a database that has been exported from another program (i.e., CAD) or connect to existing database (i.e., Excel) files with the added ability to sync up to that database at timed intervals set by the user. If enabled, this feature allows variable information to be updated automatically so that print data is fully controlled from one location without a manual refresh at each computer terminal.

Editing Convenience

Label designs can be edited in Portrait or Landscape mode, as well as show the direction of label feed next to the design.

"PIN" Favorites

Tagprint Pro 3.0 allows the user to "pin" saved label designs and data tables making them immediately available in the file menu.

Single-user License or Network Version Available

TagPrint Pro 3.0 is available as a single-user license, or as a network version which allows a user to share printers, label designs, and data tables from multiple workstations within a single location.

TT230SM Printer

HellermannTyton's TT230SM thermal transfer printer is the next generation of printer available for small-to-medium volume users looking for an easy to use and functional thermal transfer printer. The TT230SM prints to a wide variety of materials including all of HellermannTyton labels and ShrinkTrak.

- Uses standard ribbons
- Print head 300 dpi
- Barcodes: standard and 2D
- Ethernet network ready

SwiftMark Automatic Label Printer and Applicator

Designed specifically for the wire and cable industry, the SwiftMark sets a new standard in labeling efficiency. The SwiftMark automatic label printer and applicator prints self-laminating vinyl labels and applies them to various sizes of wire and cable, increasing labeling productivity up to 400%.

TTM430 / TTM460 Thermal Transfer Printer

HellermannTyton's TTM430 and TTM460 thermal transfer printers are ideal for medium-to-large volume users looking for an easy to use and extremely functional thermal transfer printer. Both print to a wide variety of materials including all HellermannTyton's labels and ShrinkTrak. Used along with TagPrint Pro, these printers will offer error free printing and seamless operations.

- Printhead 300 (TTM430) and 600 dpi (TTM460) for small text and smooth graphics
- Print speed up to 7.87"per second
- Straight through design allows easy loading of ribbon and labels. (Labels are held in an interchangeable media hub).
- Lightweight/minimal foot print

INDUSTRIAL CONTROL PANEL

HellermannTyton

Serial Number:	RC2356YUP77
Current:	125 Amperes
Largest Motor H.P.	20 Horsepower
Max OCP Device:	60 Amperes
Voltage:	460 - 480 Volts
Phase and Frequency:	3ph, 60 Hz
Short Circuit Current Rating:	100,000 Amperes RMS
Diagram Number:	HT-4322
NEMA Rating:	TYPE 2

TAG80T1-795

2 DISCONNECTS REQUIRED TO DE-ENERGIZE

TAG80T1-795 | 3.0″ x 5.0″

UID MILITARY APPROVED LABEL MATERIAL - 7871

MIL-STD-810
ASTM D3330
ASTM D4060
UL Recognized
British Standard BS-5609

Unique Item Identifier (UID) military compliant labeling system. Tested by the Naval Surface Warfare Center (NSWC) for high and low temperature cycling, salt, fog, chemical and abrasion resistance and adhesive performance.

HellermannTyton

TAG33T1-DTH | 3.0″ x 2.0″

(123) 456-7890

TAGPP3T4-822
.688″ x .25″

TAG75T1-822

DATACOM WIRING INSIDE

TAG75T1-822
2.0″ x .625″

PATCH | PANEL | WALL | PLATE | CLEAR

TAGPP1T6-822C

TAGPP1T6-822C
.625″ x .33″

TERMINAL MARKING BLOCK 01 02 03 04 05 06 07 08 09 10 TAG83T1-822

TAG83T1-822 | 4.0″ x .312″

INCREMENT: 188 SERIAL: 0000BS TAG15T3-795	INCREMENT: 189 SERIAL: 0000BT TAG15T3-795	INCREMENT: 190 SERIAL: 0000BU TAG15T3-795
INCREMENT: 191 SERIAL: 0000BV TAG15T3-795	INCREMENT: 192 SERIAL: 0000BW TAG15T3-795	INCREMENT: 193 SERIAL: 0000BX TAG15T3-795
INCREMENT: 194 SERIAL: 0000BY TAG15T3-795	INCREMENT: 195 SERIAL: 0000BZ TAG15T3-795	
INCREMENT: 197 SERIAL: 0000C1 TAG15T3-795	INCREMENT: 198 SERIAL: 0000C2 TAG15T3-795	

TAG15T3-795 1.0″ x .5″

DANGER

HIGH VOLTAGE CABLE

TAG28T4-250 | 1.43″ x .80″

TAG16T3-822 **01/27/12 9:00 AM**	TAG16T3-822 **01/27/12 9:00 AM**	TAG16T3-822 **01/27/12 9:00 AM**
TAG16T3-822 **01/27/12 9:01 AM**	TAG16T3-822 **01/27/12 9:01 AM**	TAG16T3-822 **01/27/12 9:01 AM**
TAG16T3-822 **01/27/12 9:02 AM**	TAG16T3-822 **01/27/12 9:02 AM**	TAG16T3-822 **01/27/12 9:02 AM**
TAG16T3-822 **01/27/12 9:03 AM**	TAG16T3-822 **01/27/12 9:03 AM**	TAG16T3-822 **01/27/12 9:03 AM**
TAG16T3-822 **01/27/12 9:04 AM**	TAG16T3-822 **01/27/12 9:04 AM**	TAG16T3-822 **01/27/12 9:04 AM**

TAG16T3-822 | .9″ x .25″

TAG71T5-822
.5″ x .43″

TAG82T2-822

TAG82T2-822 | 1.5″ x .25″

A2 A3 A4

TAG82T2-822 | .25″ x .25″

HellermannTyton
7930 N. Faulkner Rd.
Milwaukee, WI 53224
1-800-537-1512

RATING:	678-9854
VOLTS:	120
TYPE:	TAG76T1-795
SERIAL:	SN-000023

TAG76T1-795 | 2.5″ x 2.0″

100V – 7.0 AMPS

TAG69T1-336 | 2.0″ x .275″

TAG73T1-795

Date and time stamp
01/25/12 2:34 PM

TAG73T1-795 | 2.0″ x 1.0″

Self-Laminating Labels

TAG6T1-100B

Self laminating for cables
Flat ribbon cables
Fiber optic cables

TAG6T1-100B | 2.0″ x 3.75″

TAG24T1-100B
WIRE & CABLE MARKING

TAG24T1-100B
2.0″ x 1.437″

Input: 120VAC 60 Hz 15W

TAG
9T3-100B

TAG9T3-100B
1.0″ x 2.25″

General Copper
or Fiber Marker
TAG53T2-100B

TAG53T2-100B
1.5″ x 1.437″

Sequentially Numbered
0021
TAG22T2-100B

TAG22T2-100B
1.0″ x 1.43″

TAG7T1-100B

0 12345 67890 5

LARGE CABLES OR
CABLE BUNDLES

TAG7T1-100B | 2.0″ x 7.347″

TAG 38T4 100B

TAG1T1-100B
.9" x 3.12"

CABLE GiC/81D
CABLE GiC/81D
CABLE GiC/81D
CABLE GiC/81D

TAG10T2-100B | 2.0" x 2.25"

DATA LINE

TAG9T3-100B

TAG51T3-100B

TAG51T3-100B
1.0" x .75"

TAG26T6 -100B

TAG26T6-100B
.5" x .75"

TAG9T3-100B
1.0" x 2.25"

TAG38T4-100B
1.0" x 7.347"

TAG22T2-100B
1.0" x 1.43"

ShrinkTrak Labels



553-50022 | .95" x .42"

553-50021 | 1.9" x .42"

553-50040 | .95" x 1.69"

553-50028 | 1.9" x .420"

553-50026 | 1.9" x .597"

553-50038 | 1.9” x 1.69”

553-50011 | .95” x .312”



553-50033 | 1.9” x 1.2”



553-50078 | 1.9” x .235”

Foam Nameplate Labels

HellermannTyton

TRUE HEPA AIR CLEANER

Model No. 13520

Made in U.S.A. of US and Foreign Components

120V A.C., 60 Hz, 1.5A

Thermally Protected
Patent No. 4392

READ ALL INSTRUCTIONS BEFORE USING
UNPLUG BEFORE SERVICING

For Consumer Relations call 1-800-537-1512

596-00417 | 3″ x 4″

596-00503
BLACK FOAM
NAMEPLATE LABEL

596-00503
1.06″ x .49″

596-00500
WHITE FOAM
NAMEPLATE LABEL

596-00500
1.06″ x .49″

START

596-00412
1.25″ x 1.25″
.88″ hole dia.

STOP

White Foam
Button Label
1.2mm hole
596-00414

596-00414 | 1.75″ x 1.75″

596-00415
Foam Button Label

ON **OFF**

Black Foam
Button Label
1.2mm hole
596-00415

596-00415 | 1.75″ x 1.75″

UNLOCK

596-00413
1.25″ x 1.25″
.88″ hole dia.

596-00507
BLACK FOAM NAMEPLATE LABEL
TOGGLE SWITCH

596-00507 | 2″ x 1″

POWER MODULE

596-00504 | 2″ x 1″



556-26008 | 2.59″ x .68″

556-26006 | 2.59″ x .50″

556-26007 | 3.54″ x .50″

556-26009 | 3.54″ x .68″

Pre-Printed Warning Labels





596-00377 | 5.5" x 2.75"

596-00376 | 5.5" x 2.75"







Shown at 90%

596-00203
6″ x 4″

Continuous Roll Vinyl Labels



558-00330 | 3" wide roll

558-00328 | 2" wide roll

Continuous Roll Vinyl Labels



558-00314 | 2″ wide roll

558-00311

558-00312

558-00313



558-00309
1″ wide roll

558-00307

558-00308

558-00336

558-00310



Thermal Transfer Labels

Product Selection

Article No.	Part No.	Type	Width		Height of Label		Vertical Repeat		Horizontal Repeat		Width of Liner		Labels per Row	Pkg. Qty.
			In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.		
250 Material														
598-00277	TYHCT-250	TYHC	.250	6.35	1.500	38.10	1.625	41.27	.250	6.35	4.120	104.70	16	5000
596-21250	TAG21T6-250	TAG21T6	.5	12.70	.75	19.05	.875	22.22	.5	12.7	3.25	82.55	6	10000
596-11250	TAG11T4-250	TAG11T4	.65	16.50	.2	5.08	.3	7.62	.65	16.5	2.6	66.04	4	5000
596-28250	TAG28T4-250	TAG28T4	.80	20.30	1.43	36.3	1.62	41.1	.80	20.3	3.45	87.6	4	5000
596-15250	TAG15T3-250	TAG15T3	1.0	25.40	.5	12.7	.6	15.24	1.0	25.4	3.35	85.09	3	10000
596-00044	TAG35T2-250	TAG35T2	2.0	50.80	.375	9.53	.50	12.7	2.0	50.8	4.1	104.14	2	10000
336 Material														
596-00026	TAG96T1-336	TAG96T1	1.875	47.60	.25	6.35	.375	9.35	1.875	47.6	2.0	50.8	1	5000
596-00041	TAG69T1-336	TAG69T1	2.0	50.80	.275	6.98	.5	12.7	2.0	50.8	2.125	53.97	1	10000
596-00040	TAG68T1-336	TAG68T1	3.8	96.50	.275	6.98	.5	12.7	3.8	96.5	4.0	101.6	1	10000
795 Material														
596-15795	TAG15T3-795	TAG15T3	1.0	25.40	.5	12.7	.6	15.24	1.0	25.4	3.35	85.09	3	10000
596-27795	TAG27T3-795	TAG27T1	1.5	38.11	.75	19.05	.875	22.2	1.5	38.11	2.20	55.88	1	3000
596-75795	TAG75T1-795	TAG75T1	2.0	50.80	.625	15.87	.75	19.05	2.0	50.8	2.12	53.8	1	2000
596-73795	TAG73T1-795	TAG73T1	2.0	50.80	1.0	25.4	1.125	28.57	1.0	25.4	2.20	55.83	1	3000
596-76795	TAG76T1-795	TAG76T1	2.5	63.50	2.0	50.8	2.12	53.8	2.5	63.5	2.62	66.5	1	1000
596-72795	TAG72T1-795	TAG72T1	2.75	69.85	1.25	31.75	1.375	34.93	2.75	69.85	2.95	74.95	1	3000
596-78795	TAG78T1-795	TAG78T1	3.0	76.20	4.0	101.6	4.12	104.7	3.0	76.2	3.12	79.2	1	500
596-80795	TAG80T1-795	TAG80T1	3.0	76.20	5.0	127	3.0	76.2	3.0	76.2	3.125	79.37	1	500
596-79795	TAG79T1-795	TAG79T1	4.0	101.60	2.0	50.8	2.12	53.97	4.0	101.6	4.25	107.9	1	500
822 Material														
596-27822	TAG27T1-822	TAG27T1	1.5	38.11	.75	19.05	.875	22.2	1.5	38.11	2.20	55.88	1	3000
596-00019	TAG75T1-822	TAG75T1	2.0	50.80	.625	15.87	.75	19.05	2.0	50.8	2.12	53.8	1	2000
596-70822	TAG70T12-822	TAG70T12	.25	6.35	.25	6.35	.5	12.7	.25	6.35	3.2	81.2	12	10000
596-00028	TAGPP1T6-822	TAGPP1T6	.625	15.87	.333	8.45	.75	19.05	.625	15.87	3.8	96.52	6	1000
596-00082	TAGPP1T6-82210M	TAGPP1T6	.625	15.87	.333	8.45	.75	19.05	.625	15.87	3.8	96.52	6	10000
596-11822	TAG11T4-822	TAG11T4	.65	16.50	.2	5.08	.3	7.62	.65	16.5	2.6	66.04	4	5000
596-00046	TAGPP2T6-822	TAGPP2T6	.66	16.70	.33	8.38	.75	19.05	.66	16.7	4.125	104.7	6	1000
596-00083	TAGPP3T4-822	TAGPP3T4	.688	17.40	.25	6.35	.688	17.4	.375	9.52	2.9	73.66	4	1000
596-13822	TAG13T4-822	TAG13T4	.75	19.05	.25	6.35	.35	8.89	.75	19.05	3.35	85.09	4	10000
596-15822	TAG15T3-822	TAG15T3	1.0	25.40	.5	12.7	.6	15.24	1.0	25.4	3.35	85.09	3	10000
596-84822	TAG84T3-822	TAG84T3	1.25	31.75	.375	9.53	.50	12.7	1.25	31.75	4.0	101.6	3	10000
596-00023	TAG83T1-822	TAG83T1	4.0	101.60	.312	7.52	.438	11.13	4.0	101.6	4.1	104.14	1	5000

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.
* TAG17T2-822 not recommended for TT10SM, TT210SM, TT230SM, TT300SM, TT310SM, and TT330SM printers. Use TAG82T2 instead.

Product Selection

Article No.	Part No.	Type	Width		Height of Label		Vertical Repeat		Horizontal Repeat		Width of Liner		Labels per Row	Pkg. Qty.
			In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.		
822 Material (cont.)														
596-00022	TAG81T8-822	TAG81T8	.325	8.25	.20	5.08	.30	7.62	.325	8.25	2.6	66.04	8	5000
596-16822	TAG16T3-822	TAG16T3	.9	22.86	.25	6.35	.35	8.89	.9	22.86	3.35	85.09	3	10000
596-17822	TAG17T2-822	TAG17T2	1.5	38.11	.25	6.35	.35	8.89	1.65	41.98	3.35	85.09	2	10000
596-73822	TAG73T1-822	TAG73T1	2.0	50.80	1.0	25.4	1.125	28.57	1.0	25.4	2.20	55.83	1	3000
596-42822	TAG72T1-822	TAG72T1	2.75	69.85	1.25	31.75	1.375	34.93	2.75	69.85	2.95	74.95	1	3000
596-71822	TAG71T5-822	TAG71T5	.5	12.70	.43	11.1	.662	16.81	.43	11.1	3.35	85.09	5	10000
596-82822	TAG82T2-822	TAG82T2	1.5	38.10	.25	6.35	.30	7.62	1.5	38.1	3.20	81.28	2	10000
822 C Material*														
596-00029	TAGPP1T6-822C	TAGPP1T6	.625	15.87	.333	8.45	.75	19.05	.625	15.87	3.8	96.52	6	1000
596-00030	TAGPP1T6-822C10M	TAGPP1T6	.625	15.87	.333	8.45	.75	19.05	.625	15.87	3.8	96.52	6	10000
596-00003	TAG11T4-822C	TAG11T4	.6	16.50	.2	5.08	.3	7.62	.65	16.5	2.6	66.04	4	5000
596-00047	TAGPP2T6-822C	TAGPP2T6	.66	16.70	.33	8.38	.75	19.05	.66	16.7	4.125	104.7	6	1000
596-00084	TAGPP3T4-822C	TAGPP3T4	.688	17.40	.25	6.35	.375	9.52	.688	17.4	2.9	73.66	4	1000
596-00001	TAG15T3-822C10M	TAG15T3	1.0	25.40	.5	12.7	.6	15.24	1.0	25.4	3.35	85.09	3	10000
596-00043	TAG27T1-822C	TAG27T1	1.5	38.11	.75	19.05	.875	22.2	1.5	38.11	2.20	55.88	1	3000
DTH Material***														
596-00033	TAG13T4-DTH	TAG13T4	.75	19.05	.25	6.35	.35	8.89	.75	19.05	3.35	85.09	4	10000
596-00034	TAG16T3-DTH	TAG16T3	.9	22.86	.25	6.35	.35	8.89	.9	22.86	3.35	85.09	3	10000
596-00035	TAG15T3-DTH	TAG15T3	1.0	25.40	.5	12.7	.6	15.24	1.0	25.4	3.35	85.09	3	10000
596-00036	TAG27T2-DTH	TAG27T2	1.5	38.11	.75	19.05	.875	22.2	1.5	38.11	2.20	55.83	2	10000
596-00037	TAG99T1-DTH	TAG99T1	2.0	50.80	.25	6.35	.375	9.52	2.0	50.8	2.2	55.8	1	2500
596-00038	TAG73T1-DTH	TAG73T1	2.0	50.80	1.0	25.4	1.125	28.57	1.0	25.4	2.20	55.83	1	3000
596-00039	TAG33T1-DTH	TAG33T1	3.0	76.20	2.0	50.8	2.13	53.97	2.0	50.8	3.1	78.74	1	1000
PAP - Non-Adhesive Cardstock														
596-00017	TAG74T2-PAP	TAG74T2	1.75	44.45	.375	9.53	.562	14.2	1.75	44.45	3.5	88.9	2	1000
596-00025	TAG82T2-PAP	TAG82T2	2.0	50.8	.396	10.05	.562	14.2	2.0	50.8	4.05	102.0	2	1000
596-00024	TAG85T1-PAP	TAG85T1	3.0	76.2	.50	12.7	.60	15.24	3.0	76.2	3.2	8.28	1	5000

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.
* Clear ** Not recommended for TT1210 printer *** For use with DTH ribbons only!

Self-Laminating Labels

Thermal Transfer Self-Laminating Labels

Product Selection			Width		Height of Printable Area		Height of Label		Vertical Repeat		Horizontal Repeat		Width of Liner		Labels per Row	Pkg. Qty.
Article No.	Part No.	Type	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.		
100B Material																
596-00009	TAG26T6-100B	TAG26T6	.5	12.70	.375	9.52	.75	19.05	1.0	25.4	.5	12.7	3.35	85.09	6	10000
596-00010	TAG2T5-100B	TAG2T5	.5	12.70	.5	12.7	1.43	36.5	1.62	41.28	.66	16.81	3.35	85.09	5	10000
596-00014	TAG51T3-100B	TAG51T3	1.0	25.40	.35	8.8	.75	19.05	.937	23.7	1.075	27.3	3.35	85.09	3	10000
596-00006	TAG22T2-100B	TAG22T2	1.0	25.40	.5	12.7	1.43	36.5	1.62	41.28	1.075	27.3	2.25	57.1	2	5000
596-00007	TAG22T3-100B	TAG22T3	1.0	25.40	.5	12.7	1.43	36.5	1.62	41.28	1.075	27.3	3.35	85.09	3	5000
596-00027	TAG9T3-100B	TAG9T3	1.0	25.40	.75	19.05	2.25	57.1	2.5	63.5	1.0	25.4	3.35	85.09	3	5000
596-00013	TAG3T3-100B	TAG3T3	1.0	25.40	1.0	25.4	3.75	95.25	4.0	101.6	1.075	27.3	3.35	85.09	3	3000
596-00011	TAG38T4-100B	TAG38T4	1.0	25.40	1.5	38.1	7.35	188.9	7.75	196.80	1.0	25.4	4.10	104.14	4	1000
596-00045	TAG53T2-100B	TAG53T2	1.5	38.1	.7	17.78	1.44	36.49	1.62	41.28	1.5	38.1	3.35	89.05	2	2500
596-00005	TAG1T1-100B	TAG1T1	1.9	48.26	.75	19.05	3.12	79.2	3.42	86.8	1.9	48.2	3.875	98.42	2	2500
596-00008	TAG24T1-100B	TAG24T1	2.0	50.80	.5	12.7	1.44	36.49	1.68	42.6	2.0	50.8	2.2	55.9	1	1000
596-00002	TAG10T2-100B	TAG10T2	2.0	50.80	.75	19.05	2.25	57.1	2.5	63.5	2.0	50.8	3.875	98.42	2	2500
596-00021	TAG7T1-100B	TAG7T1	2.0	50.80	1.5	38.1	7.35	188.9	7.75	196.80	2.0	50.8	4.10	104.14	2	1000
596-00016	TAG6T1-100B	TAG6T1	2.0	50.80	1.5	38.1	3.75	95.25	4.0	101.6	2.0	50.8	2.20	55.88	1	1000

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Self-Laminating Laser Tags

Product Selection			Width		Height of Printable Area		Height of Label		Labels per Row	Labels per Column	Labels per Sheet	Pkg. Qty.
Article No.	Part No.	Type	In.	mm.	In.	mm.	In.	mm.				
105 Material												
594-26105	TAG26L-105	TAG26L	.50	12.7	.375	9.5	.75	19.0	16	16	156	5000
594-02105	TAG2L-105	TAG2L	.50	12.7	.50	12.7	1.43	36.5	16	7	112	5000
594-05105	TAG5L-105	TAG5L	.80	20.3	.50	12.7	1.43	36.4	8	7	56	5000
594-65105	TAG65L-105	TAG65L	.81	20.7	.81	20.7	2.13	53.9	9	4	36	1000
594-51105	TAG51L-105	TAG51L	1.00	25.4	.35	8.89	.75	19.0	8	12	84	5000
594-49105	TAG49L-105	TAG49L	1.00	25.4	.35	8.8	1.00	25.5	8	8	80	2500
594-63105	TAG63L-105	TAG63L	1.00	25.4	.50	12.7	1.33	33.78	8	7	56	2500
594-09105	TAG9L-105	TAG9L	1.00	25.4	.75	19.0	2.25	57.1	7	4	28	1000
594-50105	TAG50L-105	TAG50L	1.00	25.4	1.00	25.4	3.16	80.4	8	3	21	1000
594-64105	TAG64L-105	TAG64L	1.17	29.6	.83	21.08	3.33	84.6	6	3	18	1000
594-01105	TAG1L-105	TAG1L	1.90	48.2	.75	19.0	3.25	82.5	4	3	12	1000
594-52105	TAG52L-105	TAG52L	2.00	50.8	.47	33.7	1.33	33.7	3	7	21	1000
594-10105	TAG10L-105	TAG10L	2.00	50.8	.75	19.1	2.25	57.2	4	4	16	1000

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Ink Jet Self-Laminating Labels

Product Selection			Width		Height of Printable Area		Height of Label		Labels per Row	Labels per Column	Labels per Sheet	Pkg. Qty.
Article No.	Part No.	Type	In.	mm.	In.	mm.	In.	mm.				
100B Material												
593-26994	TAG26J-994	TAG26J	.500	12.70	.350	8.89	.750	19.05	16	8	128	2500
593-05994	TAG5J-994	TAG5J	.800	20.30	.500	12.70	1.430	36.32	10	4	40	1000
593-51994	TAG51J-994	TAG51J	1.000	25.40	.350	8.89	.750	19.05	8	8	64	1000
593-22994	TAG22J-994	TAG22J	1.000	25.40	.500	12.70	1.430	36.32	8	4	32	1000
593-09994	TAG9J-994	TAG9J	1.000	25.40	.750	19.05	2.250	57.15	8	3	24	1000
593-64994	TAG64J-994	TAG64J	1.160	29.60	.860	21.80	3.250	82.60	7	2	14	1000

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Laser Tags Labels

Product Selection

Article No.	Part No.	Type	Width		Height		Labels per Row	Labels per Column	Labels per Sheet	Pkg. Qty.
			In.	mm.	In.	mm.				
788 Material										
594-01788	TAGPP1-788	TAGPP1	1.5	15.87	.37	7.87	12	30	360	1000
594-00001	TAGPP2-788	TAGPP2	.66	16.7	.33	8.38	12	30	360	1000
594-62788	TAG62L-788	TAG62L	1.5	31.75	.37	9.52	5	25	125	1000
594-61788	TAG61L-788	TAG61L	2.62	66.67	1.0	25.4	3	10	30	7500
594-60788	TAG60L-788	TAG60L	2.83	71.88	1.5	38.1	3	7	21	5250
594-59788	TAG59L-788	TAG59L	4.0	101.6	1.5	38.1	2	7	14	3500
594-58788	TAG58L-788	TAG58L	4.0	101.6	2.0	50.8	2	5	10	2500
594-56788	TAG57L-788	TAG56L	4.0	101.6	3.33	84.5	2	3	6	1500
594-57788	TAG56L-788	TAG57L	4.25	107.9	2.75	69.8	2	4	8	2000
594-55788	TAG55L-788	TAG55L	4.25	107.9	5.5	139.7	2	2	4	1000
594-54788	TAG54L-788	TAG54L	8.50	215.9	5.5	139.7	1	2	2	500
594-53788	TAG53L-788	TAG53L	8.50	215.9	10.81	274.6	1	1	1	250
788 C Material										
594-02788	TAGPP1-788C	TAGPP1	.625	15.87	.333	8.45	12	30	360	1000
594-00002	TAGPP2-788C	TAGPP2	.660	16.7	.330	8.38	12	30	360	1000
789 Material										
594-11789	TAG11L-789	TAG11L	.65	16.5	.2	5.08	10	48	480	5000
594-13789	TAG13L-789	TAG13L	.75	19.0	.25	6.35	8	39	312	5000
594-14789	TAG14L-789	TAG14L	1.0	25.4	.375	9.52	7	25	175	5000
594-15789	TAG15L-789	TAG15L	1.0	25.4	.5	12.7	7	19	133	5000
594-96789	TAG96L-789	TAG96L	1.875	47.62	.25	6.3	4	36	144	1000
594-69789	TAG69L-789	TAG69L	2.0	50.8	.275	6.98	4	35	140	1000
594-67789	TAG67L-789	TAG67L	2.87	73.0	.375	9.52	2	25	50	1000
594-66789	TAG66L-789	TAG66L	3.59	91.4	.375	9.52	2	25	50	1000
594-68789	TAG68L-789	TAG68L	3.8	96.5	.275	6.98	2	35	70	2500
594-45789	TAG45L-789	TAG45L	4.0	101.6	.8	20.32	2	12	24	5000
Cardstock Material										
593-00001	TAGPHONE	TAGPHONE	1.75	44.45	.375	9.52	4	21	84	1000

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Product Selection

Article No.	Part No.	Type	Width		Height		Labels per Row	Labels per Column	Labels per Sheet	Pkg. Qty.
			In.	mm.	In.	mm.				
108 Material										
593-01108	TAGPP1J-108	TAGPP1J	.625	15.87	.31	7.87	12	30	360	1000
593-65108	TAG65J-108	TAG65J	1.0	25.4	1.5	31.75	12	10	50	12500
593-59108	TAG59J-108	TAG59J	4.0	101.6	1.5	38.1	2	7	14	3500
593-57108	TAG57J-108	TAG57J	4.25	107.9	2.75	69.8	2	4	8	2000
593-56108	TAG56J-108	TAG56J	3.33	84.5	4.0	101.6	2	3	6	1500
450 Material										
593-11450	TAG11J-450	TAG11J	.20	5.08	.65	16.05	21	12	252	5000
593-13450	TAG13J-450	TAG13J	.25	6.35	.75	19.0	26	12	312	5000
593-14450	TAG14J-450	TAG14J	.375	9.52	1.0	25.4	16	9	144	2500
593-19450	TAG19J-450	TAG19J	.375	9.52	2.0	50.8	15	4	60	1200
593-15450	TAG15J-450	TAG15J	.50	12.7	1.0	25.4	13	9	117	5000
593-21450	TAG21J-450	TAG21J	.50	12.7	.75	19.0	13	12	156	5000
593-28450	TAG28J-450	TAG28J	.80	20.3	1.437	36.49	8	6	48	1000
Cardstock Material										
593-00001	TAGPHONE	TAGPHONE	1.75	44.45	.375	9.52	4	21	84	1000

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

ShrinkTrak Heat Shrinkable Markers

Product Selection

Article No.	Part No.	Type	Color	Center Slit	Width		Height		Pkg. Qty.
					In.	mm.	In.	mm.	
0.125" (3.17mm) - Outside Diameter									
553-50003	553-50003	HST3-1WH	White (WH)	-	1.9	48	1.9	48	1000
553-50078	553-50078	HST3-1WH	White (WH)	-	1.9	48	.235	5.97	2500
553-50004	553-50004	HST3-1WH-S	White (WH)	Single	.95	24	.235	5.97	500
553-50074	553-50074	HST3-1WH-S	White (WH)	Single	.95	24	.235	5.97	2000
553-50067	553-50067	HST3-1WH-S	White (WH)	Single	.95	24	.235	5.97	5000
553-50070	553-50070	HST3-1WH-2S	White (WH)	Double	.63	16	.235	5.97	750
553-50075	553-50075	HST3-1WH-2S	White (WH)	Double	.63	16	.235	5.97	3000
553-50063	553-50063	HST3-1WH-3S	White (WH)	Triple	.475	12	.235	5.97	1000
553-50088	553-50088	HST3-1WH-3S	White (WH)	Triple	.475	12	.475	12	4000
553-50006	553-50006	HST3-1YE	Yellow (YE)	-	1.9	48	.235	5.97	1000
553-50005	553-50005	HST3-1YE	Yellow (YE)	-	1.9	48	.235	5.97	250
553-50007	553-50007	HST3-1YE-S	Yellow (YE)	Single	.95	24	.235	5.97	500
553-50076	553-50076	HST3-1YE-S	Yellow (YE)	Single	.95	24	.235	5.97	2000
553-50071	553-50071	HST3-1YE-2S	Yellow (YE)	Double	.63	16	.235	5.97	750
553-50077	553-50077	HST3-1YE-2S	Yellow (YE)	Double	.63	16	.235	5.97	3000
0.187" (4.74 mm) - Outside Diameter									
553-50008	553-50008	HST4.8-1.6BK	Black (BK)	-	1.9	48.2	.312	7.92	250
553-50009	553-50009	HST4.8-1.6WH	White (WH)	-	1.9	48	.312	7.92	250
553-50010	553-50010	HST4.8-1.6WH	White (WH)	-	1.9	48.2	.312	7.92	1000
553-50177	553-50177	HST4.8-1.6WH	White (WH)	-	1.9	48	.312	7.92	3000
553-50079	553-50079	HST4.8-1.6WH	White (WH)	-	1.9	48	.312	7.92	5000
553-50011	553-50011	HST4.8-1.6WH-S	White (WH)	Single	.95	24	.312	7.92	500
553-50080	553-50080	HST4.8-1.6WH-S	White (WH)	Single	.95	24	.312	7.92	2000
553-50068	553-50068	HST4.8-1.6WH-2S	White (WH)	Double	.63	16	.312	7.92	750
553-50072	553-50072	HST4.8-1.6WH-2S	White (WH)	Double	.633	16	.312	7.92	3000
553-50064	553-50064	HST4.8-1.6WH-3S	White (WH)	Triple	.312	12	.312	7.92	1000
553-50081	553-50081	HST4.8-1.6WH-3S	White (WH)	Triple	.475	12	.312	7.92	4000
553-50013	553-50013	HST4.8-1.6YE	Yellow (YE)	-	1.9	48	.312	7.92	1000
553-50012	553-50012	HST4.8-1.6YE	Yellow (YE)	-	1.9	48	.312	7.92	250
553-50014	553-50014	HST4.8-1.6YE-S	Yellow (YE)	Single	.95	24	.312	7.92	500
553-50069	553-50069	HST4.8-1.6YE-2S	Yellow (YE)	Double	.633	16	.312	7.92	750
553-50073	553-50073	HST4.8-1.6YE-2S	Yellow (YE)	Double	.633	16	.312	7.92	3000
553-50176	553-50176	HST4.8-1.6WH-S	White (WH)	Double	.95	24	.312	7.92	3000

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

ShrinkTrak Heat Shrinkable Markers

Product Selection

Article No.	Part No.	Type	Color	Center Slit	Width		Height		Pkg. Qty.
					In.	mm.	In.	mm.	
0.25" (6.35mm) - Outside Diameter									
553-50015	553-50015	HST6-2BK	Black (BK)	-	1.9	48	.42	10.67	250
553-50016	553-50016	HST6-2WH	White (WH)	-	1.9	48	.42	10.67	250
553-50017	553-50017	HST6-2WH	White (WH)	-	1.9	48	.42	10.67	1000
553-50018	553-50018	HST6-2WH	White (WH)	-	1.9	48	.42	10.67	5000
553-50019	553-50019	HST6-2WH-S	White (WH)	Single	.95	24	.42	10.67	500
553-50020	553-50020	HST6-2YE-S	Yellow (YE)	-	1.9	48	.42	10.67	2000
553-50021	553-50021	HTS6-2YE-2S	Yellow (YE)	-	1.9	48	.42	10.67	1000
553-50022	553-50022	HST6-2YE-S	Yellow (YE)	Single	.95	24	.42	10.67	1000
553-50082	553-50082	HST6-2WH-2S	White (WH)	Double	.633	16	.42	10.67	750
553-50083	553-50083	HST6-2YE-2S	Yellow (YE)	Double	.633	16	.42	10.67	750
553-50084	553-50084	HST6-2WH-S	White (WH)	Single	.95	24	.42	10.67	2000
553-50085	553-50085	HST6-2YE-S	Yellow (YE)	Single	.95	24	.42	10.67	2000
553-50089	553-50089	HST6-2WH-3S	White (WH)	Single	.475	12	.42	10.67	4000
0.375" (9.52mm) - Outside Diameter									
553-50023	553-50023	HST9-3BK	Black (BK)	-	1.9	48	.597	15.16	250
553-50024	553-50024	HST9-3WH	White (WH)	-	1.9	48	.597	15.16	250
553-50025	553-50025	HST9-3WH-S	White (WH)	Single	.95	24	.597	15.16	500
553-50066	553-50066	HST9-3WH-3S	White (WH)	Triple	.475	12	.597	15.16	1000
553-50026	553-50026	HST9-3YE	Yellow (YE)	-	1.9	48	.597	15.16	250
553-50027	553-50027	HST9-3YE-S	Yellow (YE)	Single	.95	24	.597	15.16	500
553-50192	553-50192	HST9-3WH	White (WH)	-	1.9	48	.597	15.16	1000
0.5" (12.7mm) - Outside Diameter									
553-50028	553-50028	HST12-4BK	Black (BK)	-	1.9	48	.77	19.55	250
553-50029	553-50029	HST12-4WH	White (WH)	-	1.9	48	.77	19.55	250
553-50030	553-50030	HST12-4WH-S	White (WH)	Single	.95	24	.77	19.55	500
553-50086	553-50086	HST12-4WH-3S	White (WH)	Triple	.475	12	.77	19.55	1000
553-50031	553-50031	HST12-4YE	Yellow (YE)	-	1.9	48	.77	19.55	250
553-50032	553-50032	HST12-4YE-S	Yellow (YE)	Single	.95	24	.77	19.55	500
553-50087	553-50087	HST12-4YE-3S	Yellow (YE)	Triple	.475	12	.77	19.55	1000
553-50231	553-50231	HST12-4WH	White (WH)	-	.77	48	.77	19.55	1000
553-50232	553-50232	HST12-4WH-S	White (WH)	Single	.77	24	.77	19.55	2000

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

ShrinkTrak Heat Shrinkable Markers

Product Selection

Article No.	Part No.	Type	Color	Center Slit	Width		Height		Pkg. Qty.
					In.	mm.	In.	mm.	
0.75" (19.05mm) - Outside Diameter									
553-50033	553-50033	HST18-6BK	Black (BK)	-	1.9	48	1.2	30.48	250
553-50034	553-50034	HST18-6WH	White (WH)	-	1.9	48	1.2	30.48	250
553-50035	553-50035	HST18-6WH-S	White (WH)	Single	.95	24	1.2	30.48	500
553-50036	553-50036	HST18-6YE	Yellow (YE)	-	1.9	48	1.2	30.48	250
553-50037	553-50037	HST18-6YE-S	Yellow (YE)	Single	.95	24	1.2	30.48	500
553-50233	553-50233	HST18-6WH	White (WH)	-	1.2	48	1.2	30.48	1000
553-50234	553-50234	HST18-6WH-S	White (WH)	Single	1.2	24	1.2	30.48	2000
1.0" (25.4mm) - Outside Diameter									
553-50038	553-50038	HST24-8BK	Black (BK)	-	1.9	48	1.69	42.93	250
553-50039	553-50039	HST24-8WH	White (WH)	-	1.9	48	1.69	42.93	250
553-50040	553-50040	HST24-8WH-S	White (WH)	Single	.95	24	1.69	42.93	500
553-50041	553-50041	HST24-8YE	Yellow (YE)	-	1.9	48	1.69	42.93	250
553-50042	553-50042	HST24-8YE-S	Yellow (YE)	Single	.95	24	1.69	42.93	500
1.5" (38.1mm) - Outside Diameter									
553-50226	553-50226	HFST39-13WH-S	White (WH)	Single	.95	24.13	2.26	57.40	300
553-50209	553-50209	HST39-13WH	White (WH)	-	1.9	48.2	2.26	57.40	150
553-50225	553-50225	HFST39-13YE	Yellow (YE)	-	1.9	48.2	2.26	57.40	150
553-50227	553-50227	HFST39-13YE-S	Yellow (YE)	Single	.95	24.13	2.26	57.40	300

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Foam Nameplate Labels

Product Selection

Article No.	Part No.	Type	Width In.	Width mm.	Height In.	Height mm.	Hole	Color	Pkg. Qty.
Foam Nameplates									
596-00500	596-00500	NPL27X13WH	1.06	27	.49	12.5	N/A	N/A	500
596-00503	596-00503	NPL27X13BK	1.06	27	.49	12.5	N/A	N/A	500
596-00504	596-00504	NPL51X25WH	2	50.8	1	25.4	N/A	N/A	500
596-00507	596-00507	NPL51X25BK	2	50.8	1	25.4	N/A	N/A	500
596-00417	596-00417	NPLH76X101WH	3.0	76	4.0	101.6	N/A	N/A	150
Foam Button Nameplates									
596-00412	596-00412	NPLH31X31WH22.5	1.25	31.7	1.25	31.7	0.88	22.3	250
596-00413	596-00413	NPLH31X31BK22.5	1.25	31.7	1.25	31.7	0.88	22.3	250
596-00414	596-00414	NPLH44X44WH30.5	1.75	44.4	1.75	44.4	1.2	30.4	250
596-00415	596-00415	NPLH44X44BK30.5	1.75	44.4	1.75	44.4	1.2	30.4	250
596-00202	596-00202	NPL60X60YE	2.375	60	2.375	60	1.2	30.4	100

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Continuous Vinyl Labels

Product Selection

Article No.	Part No.	Type	Description	Width In.	Width (mm.)	Length Ft.	Length (M)	Color	Pkg. Qty.	Pkg. Type
Solid Colored Continuous Vinyl Rolls										
558-00309	558-00309	HT1WH250	White vinyl on continuous roll	1	(25.4)	250	(76)	White	250	RL
558-00313	558-00313	HT2WH250	White vinyl on continuous roll	2	(50.8)	250	(76)	White	250	RL
558-00345	558-00345	HT3WH250	White vinyl on continuous roll	3	(76.2)	250	(76)	White	250	RL
558-00350	558-00350	HT4WH250	White vinyl on continuous roll	4	(101.6)	250	(76)	White	250	RL
558-00340	558-00340	HT1GN250	Green vinyl on continuous roll	1	(25.4)	250	(76)	Green	250	RL
558-00342	558-00342	HT2GN250	Green vinyl on continuous roll	2	(50.8)	250	(76)	Green	250	RL
558-00344	558-00344	HT3GN250	Green vinyl on continuous roll	3	(76.2)	250	(76)	Green	250	RL
558-00351	558-00351	HT4GN250	Green vinyl on continuous roll	4	(101.6)	250	(76)	Green	250	RL
558-00336	558-00336	HT1OE250	Orange vinyl on continuous roll	1	(25.4)	250	(76)	Orange	250	RL
558-00337	558-00337	HT2OE250	Orange vinyl on continuous roll	2	(50.8)	250	(76)	Orange	250	RL
558-00338	558-00338	HT3OE250	Orange vinyl on continuous roll	3	(76.2)	250	(76)	Orange	250	RL
558-00339	558-00339	HT1BU250	Blue vinyl on continuous roll	1	(25.4)	250	(76)	Blue	250	RL
558-00341	558-00341	HT2BU250	Blue vinyl on continuous roll	2	(50.8)	250	(76)	Blue	250	RL
558-00343	558-00343	HT3BU250	Blue vinyl on continuous roll	3	(76.2)	250	(76)	Blue	250	RL
558-00310	558-00310	HT1YE250	Yellow vinyl on continuous roll	1	(25.4)	250	(76)	Yellow	250	RL
558-00314	558-00314	HT2YE250	Yellow vinyl on continuous roll	2	(50.8)	250	(76)	Yellow	250	RL
558-00346	558-00346	HT3YE250	Yellow vinyl on continuous roll	3	(76.2)	250	(76)	Yellow	250	RL
558-00308	558-00308	HT1RD250	Red vinyl on continuous roll	1	(25.4)	250	(76)	Red	250	RL
558-00312	558-00312	HT2RD250	Red vinyl on continuous roll	2	(50.8)	250	(76)	Red	250	RL
558-00006	558-00006	HT3RD250	Red vinyl on continuous roll	3	(76.2)	250	(76)	Red	250	RL
558-00370	558-00370	HT4RD250	Red vinyl on continuous roll	4	(101.6)	250	(76)	Red	250	RL
558-00307	558-00307	HT1BK250	Black vinyl on continuous roll	1	(25.4)	250	(76)	Black	250	RL
558-00311	558-00311	HT2BK250	Black vinyl on continuous roll	2	(50.8)	250	(76)	Black	250	RL
558-00374	558-00374	HT3BK250	Black vinyl on continuous roll	3	(76.2)	250	(76)	Black	250	RL
Reflective Continuous Labels										
558-00371	558-00371	HT1RDRF250	Reflective vinyl on continuous roll	1	(25.4)	250	(76)	Red	250	RL
558-00372	558-00372	HT2RDRF250	Reflective vinyl on continuous roll	2	(50.8)	250	(76)	Red	250	RL
558-00373	558-00373	HT3RDRF250	Reflective vinyl on continuous roll	3	(76.2)	250	(76)	Red	250	RL

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.
Not all items in stock. Contact HellermannTyton for stock status before ordering.

Continuous Vinyl Labels

Product Selection

Article No.	Part No.	Type	Description	Width In.	Width (mm.)	Length Ft.	Length (M)	Color	Pkg. Qty.	Pkg. Type
Pre-printed Signal Panel Labels on Continuous Roll										
558-00327	558-00327	HT2OE50250	White vinyl with .5" orange stripe	2	(50.8)	250	(76)	White	250	RL
558-00328	558-00328	HT2YE50250	White vinyl with .5" yellow stripe	2	(50.8)	250	(76)	White	250	RL
558-00330	558-00330	HT3OE75250	White vinyl with .75" orange	3	(76.2)	250	(76)	White	250	RL
558-00331	558-00331	HT3YE75250	White vinyl with .75" yellow stripe	3	(76.2)	250	(76)	White	250	RL
558-00333	558-00333	HT4OE10250	White vinyl with 1" orange stripe	4	(101.6)	250	(76)	White	250	RL
558-00334	558-00334	HT4YE10250	White vinyl with 1" yellow stripe	4	(101.6)	250	(76)	White	250	RL
Terminal Block Labels on Continuous Roll										
596-00380	596-00380	TBL375	White continuous polyester	.375	(9.5)	100	(30.5)	White	100	RL
596-00381	596-00381	TBL500	White continuous polyester	.5	(12.7)	100	(30.5)	White	100	RL
Pre-printed Signal Word Labels										
596-00203	596-00203	4X6DANGER	White with Red DANGER header	4	(101.6)	6	(152.4)	White	250	RL
596-00427	596-00427	4X6CAUTION	White with Yellow CAUTION header	4	(101.6)	6	(152.4)	White	250	RL
596-00371	596-00371	4X6SAFETY	White with green SAFETY header.	4	(101.6)	6	(152.4)	White	250	RL
596-00376	596-00376	WV55X275	Orange WARNING header, yellow voltage safety symbol	5.5	(139.7)	2.75	(69.9)	White	250	RL
596-00377	596-00377	DV55X275	Red DANGER header, yellow voltage safety symbol	5.5	(139.7)	2.75	(69.9)	White	250	RL

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.
Not all items in stock. Contact HellermannTyton for stock status before ordering.

TagPrint Pro 3.0

Product Selection

Article No.	Part No.	Description
556-00035	556-00035	Single User TagPrint Pro 3.0
556-00042	556-00042	Single User Upgrade to TagPrint Pro 3.0
556-00036	556-00036	3 User Network Version
556-00037	556-00037	5 User Network Version
556-00038	556-00038	10 User Network Version
556-00039	556-00039	25 User Network Version
556-00052	556-00052	50 User Network Version

Use **Part No.** for ordering and **Type** for specification purposes.

HellermannTyton

HellermannTyton North American Corporate Headquarters
7930 N. Faulkner Rd, PO Box 245017, Milwaukee, WI 53224-9517
Phone: (414) 355-1130, (800) 537-1512, Fax: (414) 355-7341, (800) 848-9866
email: corp@htamericas.com, www.hellermann.tyton.com
TS16949, ISO 9001, and ISO14001 certified

HellermannTyton Canada
Unit #4, 205 Industrial Parkway North, Aurora, Ontario L4G 4C4 Canada
Phone: (800) 661-2461, Fax: (800) 390-3904
email: sales@hellermanntyton.ca

HellermannTyton Mexico
Anillo Periferico Sur 7980 Edificio 2-D, Parque Industrial Tecnologico II
Santa María Tequepexpan, Tlaquepaque, Jalisco, Mexico 45601
Phone: 011-52-33-3-133-9880, Fax: 011-52-33-3-133-9861
email: info@htamericas.com.mx
ISO 9001 certified

Warranty Policy
HellermannTyton products are warranted to be free from defects in material and workmanship at the time sold by us; but our obligation under this warranty and that of the seller is limited to the replacement of the product, and neither we nor the seller are bound by any other warranty, expressed, implied or statutory. Under no circumstances are we or the seller liable for any loss, damage, expenses or consequential damages of any kind arising out of the use or inability to use these products. All are sold with the understanding that the user will test them in actual use and determine their adaptability for the intended uses.

© HellermannTyton Corporation
LITPD252 Rev. 2, Printed 08.2012