



Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

NTG222-3950

Features

- DO-35 glass package
- High stability
- Wide range of operating temperature from -50°C up to 250°C

High Accuracy NTC Thermistors


Applications

- Low cost probe assemblies
- High temperature printer ink sensing
- Consumer electronics
- High temperature-high speed tire manufacturing
- Printed circuit board temperature sensing
- Air-conditioner

Electrical Characteristics @ 25°C Unless Otherwise Specified

Rated zero-power resistance	R ₂₅	2200 Ω	
Tolerance of R ₂₅		±10%	
Range of B value	B _{25/50}	3950K	
Tolerance of B value		±3%	
Dissipation factor		≥ 2.0mW	In still air
Thermal time constant		≤ 20Sec.	In still air
Rated power		250mW	
Operating temperature range		-50°C ~ + 250°C	

DO-35



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	---	.166	---	4.2	
B	---	.079	---	2.00	
C	---	.020	---	.52	
D	1.000	---	25.40	---	

Type No.

NTG

XXX

XX

①

②

③

① Series Name

② Resistance , for example :

502-----5kohm

103-----10kohm

403-----40kohm

503-----50kohm

104-----100kohm

③ Range of B Value, for example

3850-----B Value is 3850

3950-----B Value is 3950