


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0003061151](#)
Status: **Obsolete**
Overview: [standard_062](#)
Description: 1.57mm (.062") Diameter Standard .062 Pin and Socket Receptacle Housing, 15 Circuits, With Standard Mounting Ears
Replacement Part Number: [03-06-6155](#)



Documents:

Agency Certification

UL E29179

General

Product Family Crimp Housings
Series [1625](#)
Application Power
Comments Polarized to Mating Part
Obsolete Date 2000/06/01
Overview [standard_062](#)
Product Name Standard .062"
Replacement Part Number [03-06-6155](#)

Physical

Circuits (maximum) 15
Circuits Detail 3x5
Color - Resin Natural
Flammability 94V-2
Gender Receptacle
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Nylon
Number of Rows 3
Packaging Type Bag
Panel Mount Yes
Pitch - Mating Interface 3.68mm (.145")
Pitch - Termination Interface 3.68mm (.145")
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40°C to +105°C

Electrical

Current - Maximum per Contact 5A

Material Info

Old Part Number 1625-15R

EU RoHS **China RoHS**
Compliance Status
Not Reviewed
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[1625Series](#)

Mates With
[1625 Plug](#)

Use With
Female Crimp Terminals [1561Link:4559](#) , [4529](#) , [2190](#) , [2189](#) , [1787](#) , [1855](#) . Male Crimp Terminals [1560](#) , [1786](#) , [1854](#) . [1778](#) Male PC Tail Terminals. [1779](#) Female PC Tail Terminals