






Female Header Right Angled 2,54 mm				Series	095
				Rated current	3,0 A
				Rated voltage	250 VRMS / VDC Please consider air- and creepage distances
				Withstand voltage	500 VRMS for one minute
				Material contact	Phosphor bronze
				Material insulator	High temp. thermoplast UL94V-0
				Operating temperature	-40°C to +105°C
				Max. processing temper.	260°C for 10 seconds
All dimensions in mm.				pitch	2,54
				termination	
				mating pin size	□ 0,64
				max. pincount	040 / 080
Variation				PCB Layout	
					
					
Plating: T = Sn F = Au S = Selective Au * No. of contacts: Variation 1 = 001 - 040 Variation 2 = 002 - 080				 www.mpe-connector.de	
Order code: 095 - 2 - 222 - 0 - N 2 X - B S 0					

Product group
4