



#### General ordering data

Order No.	0170420000
Part designation	SAKG 32 II
Version	Special terminal, special connections, 50 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, TS 32
EAN	4008190011369
Qty.	10 pc(s).

#### Product notes

Note, technical data	Conductor connection with cable lugs according to DIN 46234 and DIN 46235, from 10 .. 70 mm <sup>2</sup>
----------------------	----------------------------------------------------------------------------------------------------------

#### Additional technical data

Colour of insulating material	Medium yellow
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	No
Installation advice	TS 32
Insulating material	KrG
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	2
Open sides	Open
Operating temperature range	- 60 °C, + 130 °C
Product family	SAK Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	5VA
Version	Stud terminal

#### CSA rating data

Voltage (CSA)	600 V
CSA current	170 A
Min. cross-section (CSA)	AWG 1
Max. cross-section (CSA)	AWG 2/0

#### Conductors for clamping (rated connection)

Clamping range, min.	10 mm <sup>2</sup>
Clamping range, max.	70 mm <sup>2</sup>
Type of connection	Screw connection

#### Conductors for clamping (rated connection)

2nd type of connection	screwed
Connection direction	on side
No. of connections	1
Clamping screw	M 8
Tightening torque range	6.0...12 Nm
AWG conductor size, min.	AWG 6
AWG conductor size, max.	AWG 3/0
AWG conductor size, min.	26.67 mm <sup>2</sup>
AWG conductor size, max.	67.44 mm <sup>2</sup>

#### Dimensions

Width	32 mm
Height of lowest version	53 mm
Length	80 mm
Weight	154 g
TS 32 offset	40 mm

#### Rating data

Rated cross-section	50 mm <sup>2</sup>
Rated voltage	1,000 V
Rated impulse voltage	8 kV
Rated current	150 A
Standards	IEC 60947-7-1
Current with max. conductor	192 A
Pollution severity	3

#### UL rating data

Voltage (UL)	600 V
Current (UL)	200 A
Min. cross-section (UL)	AWG 6
Max. cross-section (UL)	AWG 3/0

#### Approvals

Approvals institutes



#### Downloads

STEP 0170420000\_01088\_SAKG\_32\_II\_STP.stp

#### Classifications

ETIM 2.0	EC000897
ETIM 3.0	EC000897
eClass 4.1	27-14-11-31
eClass 5.0	27-14-11-31
eClass 5.1	27-14-11-31

## Classifications

### Similar products

Order No.	Part designation	Version
0185120000	SAKG 32 II/GW	Special terminal, special connections, 50 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, TS 32
0286720000	SAKG 32 III	Special terminal, special connections, 50 mm <sup>2</sup> , Screw connection, KrG, Medium yellow, TS 32