

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191640075

Status:

Active

Description:

Perma-Seal™ Male Quick Disconnect Tab for 10-12 AWG Wire, Tab Size 6.35mm (.250") x .81mm (.032")

Documents:

Product Literature (PDF)

RoHS Certificate of Compliance (PDF)

Drawing (PDF)

General	
Product Family	Quick Disconnects
Series	19164
Product Name	Perma-Seal™
Type	Quick Disconnect
Physical	
Barrel Type	Closed
Flammability	94V-0
Gender	Male
Glow-Wire Compliant	No
Insulation	NiAc™
Lock to Mating Part	None
Material - Metal	Brass
Orientation	Straight
Packaging Type	Bag
Tab Thickness	0.81mm (.032")
Tab Width	6.35mm (.250")
Temperature Range - Operating	-55°C to +125°C
Wire Insulation Diameter	5.84mm (.230") max.
Wire Size AWG	10, 12
Wire Size mm²	4.00 - 6.00
Electrical	
CSA	LR18689
UL	E79133
Voltage - Maximum	600V
Material Info	
Old Part Number	SC-9280
Reference - Drawing Numbers	
Sales Drawing	SD-19164-039



Series image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19164Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0640016100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION