

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [02-09-2133](#)
Status: **Active**
Overview: [Standard .093"](#)
Description: 2.36mm Diameter, Standard .093" Pin and Socket PC Tail Terminal, Series 1376, Male, with Tin/Lead (Sn/Pb) Plated Contact, With Detent, Bag Packaged

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-02-09 \(PDF\)](#)

General
Product Family Crimp Terminals
Series [1376](#)
Application Power
Comments PC Tail For Standard .093" Housing
Crimp Quality Equipment Yes
Overview [Standard .093"](#)
Product Name Standard .093"

Physical
Gender Male
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Packaging Type Bag
Plating min - Mating 2.540µm
Plating min - Termination 2.540µm
Termination Interface: Style Through Hole
Wire Insulation Diameter 4.00mm max.
Wire Size AWG N/A
Wire Size mm² N/A

Material Info
Old Part Number 1376-(P909)L

Reference - Drawing Numbers
Product Specification PS-02-09
Sales Drawing SD-1376-*




image - Reference only Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[1376Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extractor Tool for .093 and HCS-125 Product Series	0638240200