




PRODUCT NUMBER
10106814-0XX0X2LF


10106814-0XX0X2LF
HERMAPHRODITIC CONNECTOR
ASSEMBLY




PRINTED
CIRCUIT
BOARD

CONNECTOR ORIENTATION
FEATURE
SEE PCB LAYOUT ON PAGE 5

10106814-0XX0X2LF
HERMAPHRODITIC CONNECTOR
ASSEMBLY


CONNECTOR ORIENTATION
FEATURE
SEE PCB LAYOUT ON PAGE 5

spec ref				---		dr		Stu Stoner		2010/11/22		projection				mm		size		A2		scale		20:1											
tolerance std				ASME Y14.5		eng		Andy Lu		2015/07/15		chr		-		ecn no		ELX-DG-21387-1		rel level		Released													
TOLERANCES UNLESS OTHERWISE SPECIFIED				appr		Pei-Ming Zheng		2015/07/15		product family		MezzoStak																							
surface						linear		0.X		±0.3		0.XX		±0.15		0.XXX		±0.05		FCI		title		HERMAPHRODITIC CONNECTOR, SHORT STYLE		20-90 POS, 0.5MM CTR, 4-7MM STACK HT		dwg no		10106814		rev		D	
ASME Y14.5				angular		0°		±3°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 1 of 8																	



HERMAPHRODITIC CONNECTOR MATING	
CONNECTOR POSITION	MATES WITH CONNECTOR POSITION
1	2
3	4
5	6
7	8
9	10
ETC.	

10106814-024002LF SHOWN
WITHOUT STANDARD PICK-UP CAP

spec ref		---		dr		Stu Stoner		2010/11/22		projection				mm		size		A2		scale		20:1	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Andy Lu		2015/07/15						ecn no		ELX-DG-21387-1		rel level		Released			
ASME Y14.5				chr		-		-						dwg no		10106814							
				appr		Pei-Ming Zheng		2015/07/15		product family		MezzoStak											
surface				linear				title		HERMAPHRODITIC CONNECTOR, SHORT STYLE		dwg no		10106814		rev		D					
				0.X																		±0.3	
				0.XX																		±0.15	
ASME Y14.5		angular		0°		±3°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 2 of 8							



Copyright FCI.

0.5 BTB HERMAPHRODITIC CONNECTOR ASSEMBLY PART NUMBER SCHEME
EXAMPLE: 10106814-XX X X X 2 LF

NUMBER OF POSITIONS
02 = 20 POS
03 = 30 POS
04 = 40 POS
05 = 50 POS
06 = 60 POS
07 = 70 POS
08 = 80 POS
09 = 90 POS

PRACTICAL CONNECTOR HEIGHT NOTE 8
1 = 2.0MM
2 = 2.5MM
3 = 3.0MM
4 = 3.5MM

LEAD FREE INDICATOR

PACKAGING	
2	TAPE AND REEL WITH PICK-UP CAP

CONTACT PLATING	
0	GENERAL PLATING PER PERFORMANCE REQUIRED BY PRODUCT SPECIFICATION
1	30u" GXT(SPECIAL)



PEG OPTION	
0	NO PEGS
2	PEGS

spec ref		---		dr		Stu Stoner		2010/11/22		projection				size		A2		scale		10:1			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Andy Lu		2015/07/15						ecn no		ELX-DG-21387-1							
ASME Y14.5				chr		-		-						rel level		Released							
				appr		Pei-Ming Zheng		2015/07/15		product family		MezzoStak											
surface				linear		0.X		±0.3				title		HERMAPHRODITIC CONNECTOR,SHORT STYLE		dwg no		10106814		rev		D	
				0.XX		±0.15																	
				0.XXX		±0.05																	
ASME Y14.5		angular		0°		±3°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 3 of 8							



PDS: Rev :D


STATUS:Released

Printed: Jul 16, 2015




10106814-024002LF SHOWN
WITH STANDARD PICK-UP CAP




spec ref		---		dr		Stu Stoner		2010/11/22		projection		size		scale					
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Andy Lu		2015/07/15				 mm		A2		20:1			
ASME Y14.5				chr		-		-						ecn no		ELX-DG-21387-1			
				appr		Pei-Ming Zheng		2015/07/15						product family		MezzoStak		rel level	
surface				linear				title		HERMAPHRODITIC CONNECTOR, SHORT STYLE		dwg no		10106814		re			
				0.X														±0.3	
				0.XX														±0.15	
ASME Y14.5		angular		0°		±3°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 4 of 8			

10106814-0932X2LF SHOWN




SCALE 15:1

2X (Ø0.50) PEGS FEATURE
ONLY FOR 10106814-083202LF
AND 10106814-093202LF



PCB LAYOUT FOR 10106814-083202LF AND 10106814-093202LF
OTHER DIMENSIONS, SEE SHEET 5 AND 6

SCALE 15:1

spec ref		---		dr	Stu Stoner		2010/11/22		projection				size	A2		scale		10:1		
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	Andy Lu		2015/07/15						ecn no	ELX-DG-21387-1						
ASME Y14.5				chr	-		-		-		-		rel level		Released					
				appr	Pei-Ming Zheng		2015/07/15		product family		MezzoStack									
surface		- / ✓				title		HERMAPHRODITIC CONNECTOR, SHORT STYLE 20-90 POS, 0.5MM CTR, 4-7MM STACK HT		dwg no		10106814		rev		D				
ASME Y14.5																				
linear		0.X ±0.3 0.XX ±0.15 0.XXX ±0.05																		
angular		0° ±3°		www.fci.com		cat. no.		-		Product - Customer Drw						sheet 7 of 8				



PDS: Rev :D

STATUS:Released

Printed: Jul 16, 2015

NOTES

- 1 - MATERIAL:
HOUSING - HIGH-TEMPERATURE THERMOPLASTIC, UL94-V0, COLOR: BLACK
CONTACTS: COPPER ALLOY
CONTACT PLATING:
SEPARABLE INTERFACE: PERFORMANCE-BASED PLATING, QUALIFIED TO MEET THE REQUIREMENTS OF FCI PRODUCT SPECIFICATION.
SOLDER TAILS: GOLD FLASH.
- 2 - RECOMMENDED LEAD FREE SOLDER PASTE THICKNESS 150µm.
- 3 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDS IN A CONVECTION INFRA RED OR VAPOR PHASE REFLOW OVEN.
- 4 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGUGULATION AS DESCRIBED IN GS-22-008
- 5 - PACKAGING TAPE AND REEL. PACKAGING SPECIFICATION GS-14-1320, PRODUCT SPECIFICATION GS-12-1322.
- 6 - PRACTICAL CONNECTOR HEIGHT AS SPECIFIED IN THE TABLE IS NOT THE DIMENSIONAL HEIGHT OF THE CONNECTOR BUT THE HEIGHT AS IT PERTAINS TO TOTAL STACK HEIGHT. AN EXAMPLE IS A CONNECTOR WITH A 2.5MM PRACTICAL CONNECTOR HEIGHT, WHEN MATED TO ITSELF WILL RESULTING IN A BOARD TO BOARD STACK HEIGHT OF 5MM.
- 7 - DISCRETE CONNECTOR HEIGHT AS SHOWN IN THE TABLE IS THE ACTUAL DIMENSIONAL CONNECTOR HEIGHT. ALSO SEE INFORMATION ON PRACTICAL HEIGHT IN NOTE 6.
- 8 - REFER TO IPC 7525-A FOR STENCIL CREATION.

spec ref				---		dr		Stu Stoner		2010/11/22		projection		mm		size		A2		scale		20:1											
tolerance std				TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Andy Lu		2015/07/15						ecn no		ELX-DG-21387-1													
ASME Y14.5								chr		-		-						2015/07/15		rel level				Released									
								appr		Pei-Ming Zheng		2015/07/15		product family				MezzoStak															
surface				linear		0.X		±0.3				title		HERMAPHRODITIC CONNECTOR,SHORT STYLE 20-90 POS, 0.5MM CTR, 4-7MM STACK HT								cat. no.		-		Product - Customer Drw		sheet 8 of 8		rev		D	
						0.XX		±0.15																									
						0.XXX		±0.05																									
ASME Y14.5				angular		0°		±3°		www.fci.com																							