

REVISION V

SMS-1XX-XX-XX-D

BODY LENGTH SPECIFICATION
-01 THRU -50 POSITIONS

CONTACT SPECIFICATION _____
(SEE TABLE 1)
USE SPECIFIED LEAD STYLE TO
IDENTIFY CONTACT

BODY SPECIFICATION
-D: DOUBLE ROW (USE SMS-50-D)

PLATING SPECIFICATION	STYLE	
-G: GOLD (SPECIFY G IN CONTACT SUFFIX 'X')	01	C-16-1-
-T: TIN (SPECIFY T IN CONTACT SUFFIX 'X')	02	C-16-2-
-S: SELECTIVE (SPECIFY S IN CONTACT SUFFIX 'X')		
-F: FLASH SELECTIVE GOLD (SPECIFY F IN CONTACT SUFFIX 'X')		
(AVAILABLE IN -01 LEAD STYLE ONLY)		
-H: HEAVY GOLD (SPECIFY H IN CONTACT SUFFIX 'X')		
-TM: MATTE TIN (SPECIFY T IN CONTACT SUFFIX 'X')		
-SM: SELECTIVE GOLD, MATTE TIN TAIL (SPECIFY S IN CONTACT SUFFIX 'X')		
-FM: FLASH SELECTIVE GOLD, MATTE TIN TAIL (SPECIFY F IN CONTACT SUFFIX 'X')		
(AVAILABLE IN -01 LEAD STYLE ONLY)		

TITLE:	.050 [1.27] C
\$	SOCKET MICRO STRIP


DWG NO:	SMS-1XX-XX-XX-D
---------	-----------------

TABLE 1

LEAD STYLE	CONTACT	'B'	PKG TUBE (SEE NOTE 5)	PLUG
01	C-16-1-XX	.100 [2.54]	PT-SMS001-D ☒	TP-03
02	C-16-2-XX	.190 [4.83]		

NOTES:

1. MAX. BOWING AFTER ASSEMBLY:
.006 [.15] INCH/INCH
2. MAX. FLASH: .005 [.13]
3.  REPRESENTS A CRITICAL DIMENSION FOR STATISTICAL PROCESS CONTROL USE.
4. PARTS CUT TO POSITION SHOULD BE SYMMETRICAL ABOUT ϕ . END WALLS OF CUT BODIES SHALL BE .012 [.30] MIN. WHEN MEASURED AT CONTACT TAIL.
5. PACKAGE ONLY POSITIONS 10 THROUGH 50 IN TUBES. BOX PACKAGE POSITIONS 01 THROUGH 09.
6. CONTACT PUSHOUT FORCE: 1.5 LBS. MIN



PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

PACKAGING VIEW
SCALE: .5x

samtec EXIST

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: BRYANT 4-9-91

SMS-1XX-XX-XX-D
SHEET 1 OF 1