



Eurocard Packaging: Filler Panels

EUROCARD (VME)
FILLER PANEL KITS


Filler panels are pre-punched, anodized, vertical grained .090" (2,28 mm) thick aluminum covers that fasten to card cage extrusions to cover openings in the front of a card cage. Mounting hardware is included.

Filler panels with handles are fully assembled, and include upper and lower handles (lower only on 3U versions) that extend across the full width of the panel.

Dimensions: in(mm)



*Note: 2 HP width panels have screw thru hole .104 (2.64) from left edge.



Ordering information

Eurocard (VME) Filler Panel Kits — Without Handles

Panel Height		3U		6U		9U	
B in (mm)		5.059(128,5)		10.309(261,85)		15.559(395,2)	
Width	A in.(mm)	Anodize ¹	Conductive ²	Anodize ¹	Conductive ²	Anodize ¹	Conductive ²
Model Number							
2HP	0.384(9,8)	32145-01	32147-01	32146-01	32148-01	32251-01	32253-01
3HP	0.584(14,8)	32145-02	32147-02	32146-02	32148-02	32251-02	32253-02
4HP	0.784(19,9)	32145-03	32147-03	32146-03	32148-03	32251-03	32253-03
6HP	1.184(30,1)	32145-14	32147-14	32146-14	32148-14	32251-14	32253-14
8HP	1.584(40,2)	32145-11	32147-11	32146-11	32148-11	32251-11	32253-11
12HP	2.384(60,6)	32145-05	32147-05	32146-05	32148-05	32251-05	32253-05
16HP	3.184(80,9)	32145-06	32147-06	32146-06	32148-06	32251-06	32253-06
18HP	3.584(91,0)	32145-15	32147-15	32146-15	32148-15	32251-15	32253-15
20HP	3.984(101,2)	32145-07	32147-07	32146-07	32148-07	32251-07	32253-07
22HP	4.384(111,4)	32145-13	32147-13	32146-13	32148-13	32251-13	32253-13
32HP	6.384(162,2)	32145-08	32147-08	32146-08	32148-08	32251-08	32253-08
36HP	7.184(182,5)	32145-09	32147-09	32146-09	32148-09	32251-09	32253-09
40HP	7.984(202,8)	32145-12	32147-12	32146-12	32148-12	32251-12	32253-12
42HP	8.384(213,0)	32145-10	32147-10	32146-10	32148-10	32251-10	32253-10
84HP	16.784(426,3)	32145-04	32147-04	32146-04	32148-04	32251-04	32253-04

Note ¹: Filler panels with clear anodize finish(MIL-A-8625).

Note ²: Filler panels with conductive finish — clear chem film(MIL-C-5541).

Eurocard (VME) Filler Panel Assemblies — With Handles

Width	Panel Height "B" in. (mm)	3U 5.059 (128,5)	6U 10.309 (261,85)	9U 15.559 (395,2)
		Model Number		
4HP	0.784(19,9)	32149-01	32150-01	32252-01
6HP	1.184(30,1)	32149-10	32150-10	32252-10
8HP	1.584(40,2)	32149-04	32150-04	32252-04
12HP	2.384(60,6)	32149-05	32150-05	32252-05
16HP	3.184(80,9)	32149-06	32150-06	32252-06
18HP	3.584(91,0)	32149-14	32150-14	32252-14
20HP	3.984(101,2)	32149-02	32150-02	32252-02
22HP	4.384(111,4)	32149-13	32150-13	32252-13
32HP	6.384(162,2)	32149-07	32150-07	32252-07
36HP	7.184(182,5)	32149-08	32150-08	32252-08
40HP	7.984(202,8)	32149-09	32150-09	32252-09
42HP	8.384(213,0)	32149-03	32150-03	32252-03
84HP	16.784(426,3)	32249-01	32250-01	32254-01

Other sizes are available. Consult factory.

Handle Kits Only (no panel)

Width	For Rack height: "A" in. (mm)	3U	6U/9U
		Model Number	
4HP	0.784(19,9)	60785-104	60785-204
6HP	1.184(30,1)	60785-106	60785-206
8HP	1.584(40,2)	60785-108	60785-208
12HP	2.384(60,6)	60785-112	60785-212
16HP	3.184(80,9)	60785-116	60785-216
18HP	3.584(91,0)	60785-118	60785-218
20HP	3.984(101,2)	60785-120	60785-220
22HP	4.384(111,4)	60785-122	60785-222
32HP	6.384(162,2)	60785-132	60785-232
36HP	7.184(182,5)	60785-136	60785-236
40HP	7.984(202,8)	60785-140	60785-240
42HP	8.383(213,0)	60785-142	60785-242
84HP	16.784(426,3)	60785-184	60785-284