


1907376

REV A0

THIS DRAWING IS A CONTROLLED DOCUMENT.

Restricted to: General Release

USED ON



Connector(s): LC-Duplex Secure
Mode: SM
Housing Color: Yellow
Geom. Spec: N/A

Number of Fibers: 2
Mode: SM
Jacket Diameter: 2.0 mm
Jacket Color: Yellow
FiberType: SM

LC strain relief - 1.6 to 2.0 mm cable
Color: Blue/Blue

Notes:

- 1 Includes dust caps (not shown on print).
- 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	5/25/2006	-				
P	LTR	REVISION RECORD		DATE	DIN	APVD			

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Customer Print

DWG Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
CHK Cable Assy Configurator		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Refer to Engineering Change					
NAME FO C/A - 2 fiber, 2mm, SM, OFNR (Riser) jacket, LC-Duplex Secure to Pigtail - (1.6 to 2.0mm)					
SCALE NTS	SIZE A2	DRAWING NO. C-1907376	SHEET 1 of 3	REV A	

DAG NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	LC-Duplex Secure, Yellow		Right Side - No Connector	
		IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-1907376-1	0.950 - 1.050	0.35	45	-	-
0-1907376-2	1.950 - 2.050	0.35	45	-	-
0-1907376-3	2.950 - 3.050	0.35	45	-	-
0-1907376-4	3.920 - 4.080	0.35	45	-	-
0-1907376-5	4.920 - 5.080	0.35	45	-	-
0-1907376-6	5.920 - 6.080	0.35	45	-	-
0-1907376-7	6.920 - 7.080	0.35	45	-	-
0-1907376-8	7.920 - 8.080	0.35	45	-	-
0-1907376-9	8.850 - 9.150	0.35	45	-	-
1-1907376-0	9.850 - 10.150	0.35	45	-	-
1-1907376-1	10.850 - 11.150	0.35	45	-	-
1-1907376-2	11.850 - 12.150	0.35	45	-	-
1-1907376-3	12.850 - 13.150	0.35	45	-	-
1-1907376-4	13.850 - 14.150	0.35	45	-	-
1-1907376-5	14.850 - 15.150	0.36	45	-	-
1-1907376-6	15.840 - 16.160	0.36	45	-	-
1-1907376-7	16.830 - 17.170	0.36	45	-	-
1-1907376-8	17.820 - 18.180	0.36	45	-	-
1-1907376-9	18.810 - 19.190	0.36	45	-	-
2-1907376-0	19.800 - 20.200	0.36	45	-	-
2-1907376-1	20.790 - 21.210	0.36	45	-	-
2-1907376-2	21.780 - 22.220	0.36	45	-	-
2-1907376-3	22.770 - 23.230	0.36	45	-	-
2-1907376-4	23.760 - 24.240	0.36	45	-	-
2-1907376-5	24.750 - 25.250	0.36	45	-	-
2-1907376-6	25.740 - 26.260	0.36	45	-	-
2-1907376-7	26.730 - 27.270	0.36	45	-	-
2-1907376-8	27.720 - 28.280	0.36	45	-	-
2-1907376-9	28.710 - 29.290	0.37	45	-	-
3-1907376-0	29.700 - 30.300	0.37	45	-	-
3-1907376-1	30.690 - 31.310	0.37	45	-	-
3-1907376-2	31.680 - 32.320	0.37	45	-	-
3-1907376-3	32.670 - 33.330	0.37	45	-	-
3-1907376-4	33.660 - 34.340	0.37	45	-	-
3-1907376-5	34.650 - 35.350	0.37	45	-	-
3-1907376-6	35.640 - 36.360	0.37	45	-	-
3-1907376-7	36.630 - 37.370	0.37	45	-	-
3-1907376-8	37.620 - 38.380	0.37	45	-	-
3-1907376-9	38.610 - 39.390	0.37	45	-	-
4-1907376-0	39.600 - 40.400	0.37	45	-	-
5-1907376-0	49.500 - 50.500	0.38	45	-	-

	A	Rev Per EC#	RELEASE	5/25/2006	-
P	LTR	REVISION RECORD		DATE	DIN

DIMENSIONS;
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED		
0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-

Customer Print

DWN Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
CHK Cable Assy Configurator		 AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Refer to Engineering Change					
NAME FO C/A - 2 fiber, 2mm, SM, OFNR (Riser) jacket, LC-Duplex Secure to Pigtail (1.6 to 2.0mm)					
SCALE NTS	SIZE A2	DRAWING NO C-1907376		SHEET 2 of 3	REV A

A

3

C

D

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.
REV NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



Trace # - Bar Code


Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

	A	Rev Per EC#	RELEASE	5/25/2006	-		
P	LTR	REVISION RECORD		DATE	DIN	APVD	



Customer Print

DIMENSIONS: meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± .
1 PLC ± .
2 PLC ± .
3 PLC ± .
4 PLC ± .

DWG Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK Cable Assy Configurator		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD Refer to Engineering Change				
NAME FO C/A - 2 fiber, 2mm, SM, OFNR (Riser) jacket, LC-Duplex Secure to Pigtail - (1.6 to 2.0mm)				
SCALE NTS	SIZE A2	DRAWING NO C- 1907376	SHEET 3 of 3	REV A

D

C

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[1-1906001-1](#)