

7-outlet, 7-ft cord, 2160 joule, Coaxial protection, Protect It! Surge Suppressor

MODEL NUMBER: **SUPER7COAX**



Description

The SUPER7COAX surge suppressor from Tripp Lite has 7 outlets and a 7-ft. cord with a space-saving right-angle plug. The unit has 2160 joules of surge energy absorption to handle the strongest surges. Built-in 2.2 GHZ gold coax jacks prevent surges from damaging your cable/satellite equipment. Diagnostic LEDs alert the user to potential power problems. \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 7 outlets
- 7-ft. cord with space-saving right-angle plug
- Surge suppression rating: 2160 joules
- 1 set of 2.2 GHz gold coaxial jacks
- EMI/RFI noise filtering
- Can accommodate up to 3 transformers without blocking remaining outlets
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting

Specifications

OVERVIEW

| | |
|----------------------|--------------------------|
| Intended Application | Home/Office; Audio/Video |
| Style | Strip |

OUTPUT

Highlights

- 7 outlets/7 ft. cord
- 2160 joule rating
- 2.2 GHz gold coaxial surge protection
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Audio/visual devices, cable television connections, home theater systems, personal computers, CAD/CAM/CAE workstations, network nodes, fileservers, point-of-sale terminals, and more.

Package Includes

- Super7Coax Surge Suppressor
- 6-ft gold coax cable
- Warranty information with instruction manual

| | |
|------------------------------------|--|
| Frequency Compatibility | 50 / 60 Hz |
| Output (Watts) | 1800 |
| Circuit Breaker (amps) | 15 |
| Outlet Quantity / Type | 7 NEMA 5-15R |
| Number of Outlets | 7 |
| Transformer Accommodation | Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 5 transformers total |
| Outlet Orientation | Single row of 5, plus 2 side mounted outlets |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Connection Type | NEMA 5-15P |
| Input Plug Features | Space-saving right angle input plug |
| Input Cord Length (ft.) | 7 |
| Input Cord Length (m) | 2.13 |
| Input Cord Gauge Type | 14 gauge, SJT |
| Voltage Compatibility (VAC) | 120 |
| Maximum Surge Amps | 144000 |
| UPC ASSIGNMENT | |
| Unit Carton UPC# | 037332010902 |
| LEDS ALARMS & SWITCHES | |
| Switches | Two position on/off power switch |
| Diagnostic LEDs | Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 2160 |
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping Voltage (RMS) | 150 |
| UL1449 Let Through Rating | 330V L-G; 400V L-N; 400V N-G |
| EMI / RFI Filtering | Up to 20 dB |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection | No |

| | |
|--|---|
| Cable (Coax) Protection | Yes |
| Cable (Coax) Protection Details | 1 line |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Shipping Dimensions (hwd / in.) | 12.40 x 5.90 x 1.77 |
| Shipping Dimensions (hwd / cm) | 31.50 x 14.99 x 4.50 |
| Shipping Weight (lbs.) | 1.56 |
| Shipping Weight (kg) | 0.71 |
| Unit Dimensions (hwd / in.) | 1.54 x 2.72 x 10.3 |
| Unit Dimensions (hwd / cm) | 3.91 x 6.91 x 26.16 |
| Unit Weight (lbs.) | 1.39 |
| Unit Weight (kg) | 0.63 |
| Material of Construction | Plastic |
| Integrated Keyhole Mounting Tabs | Keyhole mounting tabs enable wall mounting |
| Housing Color | Light Gray |
| Receptacle Color | Light gray |
| Color (AC Line Cord) | Light Gray |
| Outlets Measurement (Center to Center) | Between Standard Outlets = 29mm; Between Transformer Outlets = 48mm |
| Keyhole Slot Mounting Measurement (Center to Center) | Distance Between Slots = 78mm; Distance Between Slot Height = 24mm |
| SPECIAL FEATURES | |
| Right-Angle Plug | Yes |
| CERTIFICATIONS | |
| UL1449 3rd Edition (AC Suppression) | UL1449 3RD EDITION |
| UL1363 (Power Tap) | UL1363 |
| UL497A (Communications) | UL497A |
| FCC Part 68 (Communications) | FCC Part 68 |
| cUL / CSA (Canada) | cUL |
| Industry Canada (Communications) | Industry Canada |
| Approvals | Exceeds IEEE 587 category A&B specifications |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connected Equipment Insurance
(U.S., Canada & Puerto Rico)

\$75,000 [Ultimate Lifetime Insurance](#)

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.