

2,000 V - 5,000 V Rectifiers

2.0 A - 5.0 A Forward Current

70 ns Recovery Time

1N6513U

1N6515U

1N6517U

SURFACE MOUNT
HERMETICALLY SEALED



JANTX JANTXV



ELECTRICAL CHARACTERISTICS AND MAXIMUM RATINGS

Part Number	Working Reverse Voltage	Average Rectified Current		Reverse Current @ Vrwm		Forward Voltage		1 Cycle Surge Current tp=8.3ms (Ifsm)	Repetitive Surge Current (Ifrm)	Reverse Recovery Time (3) (Trr)	Thermal Impd. θ_{J-C}	Junction Cap. @50VDC @1kHz (Cj)
	(Vrwm)	(Io)		(Ir)		(Vf)						
		55°C(1)	100°C(2)	25°C	100°C	25°C	25°C	25°C	25°C	25°C	25°C	25°C
	Volts	Amps	Amps	μA	μA	Volts	Amps	Amps	Amps	ns	°C/ W	pF
1N6513U	2000	5.0	3.3	1.0	25	3.5	2.0	100	15	70	4	25
1N6515U	3000	3.5	2.3	1.0	25	6.0	1.5	60	10	70	4	20
1N6517U	5000	2.0	1.3	1.0	25	8.0	1.0	40	8	70	4	16

(1)TC=55°C (2)TC=100°C (3)If=0.5A, Ir=1.0A, Irr=0.25A *Op. Temp.= -65°C to +175°C Stg. Temp.= -65°C to +200°C

Markings:

Three Dots for polarity.



1N6513U 1N6515U 1N6517U

