

HC-B 10-SML-52/O1M25

Order No.: 1604749

The photo shows the 74 mm high version



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1604749>

HEAVYCON box mounting base B10, with single locking latch, height 52 mm, with support 1xM25

Commercial data

GTIN (EAN)	4 017918 881665
sales group	D002
Pack	10 pcs.
Customs tariff	85389099
Catalog page information	Page 197 (PC-2002)

Product notes

WEEE/RoHS-compliant since:
03/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Note	For contact inserts HC-B10, BB18, DD42, M, K8/24
Design	B10
Height	52 mm
Width	52 mm
Length	93 mm

Housing type	Box mounting bases
Locking type	With single locking latch
Cable exit	Conductor exit direction to the left (looking into the open single locking latch)
Type of the screw connection	1x M25
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Material lock	High-grade steel, handle: PA-GF
Material grip body interlock	PA-GF

Certificates / Approvals




Certification

GOST

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;