

**FUSION G7™, TYPE 4, 12**
**FUSION G7™**

**INDUSTRY STANDARDS**

*Wall-mounting brackets required to maintain UL/CSA external mounting requirement.*

UL 508A Listed; Type 4, 12; File No. 61997  
cUL Listed per CSA C22.2 No. 94; Type 4, 12; File No. 61997

NEMA/EEMAC Type 4, 12, 13  
CSA File No. 42186: Type 4, 12  
IEC 60529, IP66

**APPLICATION**

Innovative, metric-dimensioned wall-mount enclosure designed to house and protect electrical and electronic components in industrial environments. Provides traditional enclosure functionality with scalable internal component mounting capability using the optional internal mounting system and accessory components.

**FEATURES**

- Ninety-degree external formed flange trough collar around body opening
- Three-point latching on enclosures 1000-mm high and taller
- Door alignment device on doors with 3-point latching and 800 mm or wider
- Pre-cut gland plate opening(s) in enclosure bottom

- Quarter-turn latch(es) with 3-mm double-bit insert
- Corner-formed door
- Simple, easy-to-remove and install hinge pins with captivation clip
- High-torque threadless studs and fasteners on door
- Wide assortment of user-friendly internal accessories to increase internal mounting area capability and design flexibility
- Includes hardware package with grounding and sealing hardware and illustrated instruction sheet

**SPECIFICATIONS**

- Constructed from 1.2-mm, 1.5-mm and 2-mm thick steel (18, 16 and 14 gauge) (see table)
- Seamless foam-in-place gasket
- Reversible door with sealed hinges and hinge brackets
- Gland plate(s) for enclosure bottom
- Bonding provision on door; grounding studs (2) on body
- Full-height galvanized steel back panel included

**FINISH**


RAL 7035 textured, light-gray polyester powder paint inside and out  
Panel is galvanized

**BULLETIN: A4G**

## Standard Product

| Catalog Number | AxBxC mm/in.                              | Body Thickness mm | Body Thickness Gauge | Door Thickness mm | Door Thickness Gauge | Latch Type         | D x E mm/in.                | G x H mm/in.                | J mm/in.     | P x Q mm/in.              | S mm/in.    |
|----------------|-------------------------------------------|-------------------|----------------------|-------------------|----------------------|--------------------|-----------------------------|-----------------------------|--------------|---------------------------|-------------|
| G300300225G    | 300 x 300 x 225<br>11.81 x 11.81 x 8.86   | 1.2               | 18                   | 1.2               | 18                   | Quarter-turn       | 255 x 255<br>10.04 x 10.04  | 262 x 262<br>10.31 x 10.31  | 150<br>5.91  | 180 x 90<br>7.09 x 3.54   | 39<br>1.55  |
| G300400200G    | 300 x 400 x 200<br>11.81 x 15.75 x 7.87   | 1.2               | 18                   | 1.2               | 18                   | Quarter-turn       | 255 x 355<br>10.04 x 13.98  | 262 x 362<br>10.31 x 14.25  | 150<br>5.91  | 280 x 90<br>11.02 x 3.54  | 39<br>1.55  |
| G400300150     | 400 x 300 x 150<br>15.75 x 11.81 x 5.91   | 1.2               | 18                   | 1.2               | 18                   | Quarter-turn       | 355 x 255<br>13.98 x 10.04  | 362 x 262<br>14.25 x 10.31  | 200<br>7.87  | —<br>—                    | 39<br>1.55  |
| G400300225G    | 400 x 300 x 225<br>15.75 x 11.81 x 8.86   | 1.2               | 18                   | 1.2               | 18                   | Quarter-turn       | 355 x 255<br>13.98 x 10.04  | 362 x 262<br>14.25 x 10.31  | 200<br>7.87  | 180 x 90<br>7.09 x 3.54   | 39<br>1.55  |
| G400400225G    | 400 x 400 x 225<br>15.75 x 15.75 x 8.86   | 1.2               | 18                   | 1.2               | 18                   | Quarter-turn       | 355 x 355<br>13.98 x 13.98  | 362 x 362<br>14.25 x 14.25  | 200<br>7.87  | 280 x 90<br>11.02 x 3.54  | 39<br>1.55  |
| G400600225G    | 400 x 600 x 225<br>15.75 x 23.62 x 8.86   | 1.2               | 18                   | 1.2               | 18                   | Quarter-turn       | 355 x 555<br>13.98 x 21.85  | 362 x 562<br>14.25 x 22.13  | 200<br>7.87  | 180 x 90<br>7.09 x 3.54   | 39<br>1.55  |
| G500400225G    | 500 x 400 x 225<br>19.69 x 15.75 x 8.86   | 1.2               | 18                   | 1.2               | 18                   | Quarter-turn       | 455 x 355<br>17.91 x 13.98  | 462 x 362<br>18.19 x 14.25  | 250<br>9.84  | 280 x 90<br>11.02 x 3.54  | 39<br>1.55  |
| G500500225G    | 500 x 500 x 225<br>19.69 x 19.69 x 8.86   | 1.2               | 18                   | 1.2               | 18                   | Quarter-turn       | 455 x 455<br>17.91 x 17.91  | 462 x 462<br>18.19 x 18.19  | 250<br>9.84  | 280 x 90<br>11.02 x 3.54  | 39<br>1.55  |
| G500500300G    | 500 x 500 x 300<br>19.69 x 19.69 x 11.81  | 1.5               | 16                   | 1.2               | 18                   | Quarter-turn       | 455 x 455<br>17.91 x 17.91  | 462 x 462<br>18.19 x 18.19  | 250<br>9.84  | 280 x 150<br>11.02 x 5.91 | 39<br>1.55  |
| G600400225G    | 600 x 400 x 225<br>23.62 x 15.75 x 8.86   | 1.2               | 18                   | 1.2               | 18                   | Quarter-turn       | 555 x 355<br>21.85 x 13.98  | 562 x 362<br>22.13 x 14.25  | 300<br>11.81 | 280 x 90<br>11.02 x 3.54  | 39<br>1.55  |
| G600500200G    | 600 x 500 x 200<br>23.62 x 19.69 x 7.87   | 1.2               | 18                   | 1.5               | 16                   | Quarter-turn       | 555 x 455<br>21.85 x 17.91  | 562 x 462<br>22.13 x 18.19  | 300<br>11.81 | 280 x 90<br>11.02 x 3.54  | 39<br>1.55  |
| G600500300G    | 600 x 500 x 300<br>23.62 x 19.69 x 11.81  | 1.5               | 16                   | 1.5               | 16                   | Quarter-turn       | 555 x 455<br>21.85 x 17.91  | 562 x 462<br>22.13 x 18.19  | 300<br>11.81 | 280 x 150<br>11.02 x 5.91 | 39<br>1.55  |
| G600600225G    | 600 x 600 x 225<br>23.62 x 23.62 x 8.86   | 1.5               | 16                   | 1.5               | 16                   | Quarter-turn       | 555 x 555<br>21.85 x 21.85  | 562 x 562<br>22.13 x 22.13  | 125<br>4.92  | 180 x 90<br>7.09 x 3.54   | 39<br>1.55  |
| G600600325G    | 600 x 600 x 325<br>23.62 x 23.62 x 12.80  | 1.5               | 16                   | 1.5               | 16                   | Quarter-turn       | 555 x 555<br>21.85 x 21.85  | 562 x 562<br>22.13 x 22.13  | 125<br>4.92  | 180 x 150<br>7.09 x 5.91  | 39<br>1.55  |
| G600600400G    | 600 x 600 x 400<br>23.62 x 23.62 x 15.75  | 2.0               | 14                   | 1.5               | 16                   | Quarter-turn       | 555 x 555<br>21.85 x 21.85  | 562 x 562<br>22.13 x 22.13  | 125<br>4.92  | 180 x 150<br>7.09 x 5.91  | 39<br>1.55  |
| G600800300G    | 600 x 800 x 300<br>23.62 x 31.50 x 11.81  | 1.5               | 16                   | 1.5               | 16                   | Quarter-turn       | 555 x 755<br>21.85 x 29.72  | 562 x 762<br>22.13 x 30.00  | 125<br>4.92  | 180 x 150<br>7.09 x 5.91  | 102<br>4.02 |
| G700500250G    | 700 x 500 x 250<br>27.56 x 19.69 x 9.84   | 1.5               | 16                   | 1.5               | 16                   | Quarter-turn       | 655 x 455<br>25.79 x 17.91  | 662 x 462<br>26.06 x 18.19  | 125<br>4.92  | 280 x 90<br>11.02 x 3.54  | 39<br>1.55  |
| G800600225G    | 800 x 600 x 225<br>31.50 x 23.62 x 8.86   | 1.5               | 16                   | 1.5               | 16                   | Quarter-turn       | 755 x 555<br>29.72 x 21.85  | 762 x 562<br>30.00 x 22.13  | 125<br>4.92  | 180 x 90<br>7.09 x 3.54   | 39<br>1.55  |
| G800600325G    | 800 x 600 x 325<br>31.50 x 23.62 x 12.80  | 1.5               | 16                   | 1.5               | 16                   | Quarter-turn       | 755 x 555<br>29.72 x 21.85  | 762 x 562<br>30.00 x 22.13  | 125<br>4.92  | 180 x 150<br>7.09 x 5.91  | 39<br>1.55  |
| G800600425G    | 800 x 600 x 425<br>31.50 x 23.62 x 16.73  | 2.0               | 14                   | 1.5               | 16                   | Quarter-turn       | 755 x 555<br>29.72 x 21.85  | 762 x 562<br>30.00 x 22.13  | 125<br>4.92  | 180 x 150<br>7.09 x 5.91  | 39<br>1.55  |
| G800800225G    | 800 x 800 x 225<br>31.50 x 31.50 x 8.86   | 1.5               | 16                   | 2.0               | 14                   | Quarter-turn       | 755 x 755<br>29.72 x 29.72  | 762 x 762<br>30.00 x 30.00  | 125<br>4.92  | 280 x 90<br>11.02 x 3.54  | 39<br>1.55  |
| G800800300G    | 800 x 800 x 300<br>31.50 x 31.50 x 11.81  | 2.0               | 14                   | 2.0               | 14                   | Quarter-turn       | 755 x 755<br>29.72 x 29.72  | 762 x 762<br>30.00 x 30.00  | 125<br>4.92  | 180 x 150<br>7.09 x 5.91  | 102<br>4.02 |
| G1000600250G   | 1000 x 600 x 250<br>39.37 x 23.62 x 9.84  | 2.0               | 14                   | 2.0               | 14                   | 3-pt. Quarter-turn | 955 x 555<br>37.60 x 21.85  | 962 x 562<br>37.87 x 22.13  | 500<br>19.68 | 180 x 90<br>7.09 x 3.54   | 39<br>1.55  |
| G1000800300G   | 1000 x 800 x 300<br>39.37 x 31.50 x 11.81 | 2.0               | 14                   | 2.0               | 14                   | 3-pt. Quarter-turn | 955 x 755<br>37.60 x 29.72  | 962 x 762<br>37.87 x 30.00  | 500<br>19.68 | 180 x 150<br>7.09 x 5.91  | 102<br>4.02 |
| G1000800400G   | 1000 x 800 x 400<br>39.37 x 31.50 x 15.75 | 2.0               | 14                   | 2.0               | 14                   | 3-pt. Quarter-turn | 955 x 755<br>37.60 x 29.72  | 962 x 762<br>37.87 x 30.00  | 500<br>19.68 | 180 x 150<br>7.09 x 5.91  | 102<br>4.02 |
| G1200800300G   | 1200 x 800 x 300<br>47.24 x 31.50 x 11.81 | 2.0               | 14                   | 2.0               | 14                   | 3-pt. Quarter-turn | 1155 x 755<br>45.47 x 29.72 | 1162 x 762<br>45.75 x 30.00 | 600<br>23.62 | 180 x 150<br>7.09 x 5.91  | 102<br>4.02 |
| G1200800400G   | 1200 x 800 x 400<br>47.24 x 31.50 x 15.75 | 2.0               | 14                   | 2.0               | 14                   | 3-pt. Quarter-turn | 1155 x 755<br>45.47 x 29.72 | 1162 x 762<br>45.75 x 30.00 | 600<br>23.62 | 180 x 150<br>7.09 x 5.91  | 102<br>4.02 |
| G1200900325G   | 1200 x 900 x 325<br>47.24 x 35.43 x 12.80 | 2.0               | 14                   | 2.0               | 14                   | 3-pt. Quarter-turn | 1155 x 855<br>45.47 x 33.66 | 1162 x 862<br>45.75 x 33.94 | 600<br>23.62 | 280 x 150<br>11.02 x 5.91 | 102<br>4.02 |
| G1500900325G   | 1500 x 900 x 325<br>59.06 x 35.43 x 12.80 | 2.0               | 14                   | 2.0               | 14                   | 3-pt. Quarter-turn | 1455 x 855<br>57.28 x 33.66 | 1462 x 862<br>57.57 x 33.94 | 750<br>29.53 | 280 x 150<br>11.02 x 5.91 | 102<br>4.02 |
| G1500900425G   | 1500 x 900 x 425<br>59.06 x 35.43 x 16.73 | 2.0               | 14                   | 2.0               | 14                   | 3-pt. Quarter-turn | 1455 x 855<br>57.28 x 33.66 | 1462 x 862<br>57.57 x 33.94 | 750<br>29.53 | 280 x 150<br>11.02 x 5.91 | 102<br>4.02 |

G400300150 does not have a gland plate.



89000887

## Accessory Selection Matrix


| FUSION G7™   | Full Back Panel | Half Back Panel | Full Side Panel | Half Side Panel | Side-Mount Accessory Rail | Horizontal Separator | 100-mm Plinth Base | Aluminum Swing Panel | Front and Back Vertical Accessory Mounting Rails | Top/Bottom Mounting Brackets |
|--------------|-----------------|-----------------|-----------------|-----------------|---------------------------|----------------------|--------------------|----------------------|--------------------------------------------------|------------------------------|
| G300300225G  | G300P300        | G300P300H       | G300SMP225      | G300SMP225H     | G50SMR225                 | GHS300225            | —                  | —                    | GAMR300                                          | GTBMTBKT300                  |
| G300400200G  | G400P300        | G300P400H       | G300SMP200      | G300SMP200H     | G50SMR200                 | GHS400200            | —                  | —                    | GAMR300                                          | GTBMTBKT400                  |
| G400300150   | G400P300        | G400P300H       | G400SMP150      | G400SMP150H     | G50SMR150                 | —                    | —                  | —                    | GAMR400                                          | GTBMTBKT300                  |
| G400300225G  | G400P300        | G400P300H       | G400SMP225      | G400SMP225H     | G50SMR225                 | GHS300225            | —                  | GSP400300A           | GAMR400                                          | GTBMTBKT300                  |
| G400400225G  | G400P400        | G400P400H       | G400SMP225      | G400SMP225H     | G50SMR225                 | GHS400225            | —                  | —                    | GAMR400                                          | GTBMTBKT400                  |
| G400600225G  | G600P400        | G400P600H       | G400SMP225      | G400SMP225H     | G50SMR225                 | GHS600225            | —                  | —                    | GAMR400                                          | GTBMTBKT600                  |
| G500400225G  | G500P400        | G500P400H       | G500SMP225      | G500SMP225H     | G50SMR225                 | GHS400225            | —                  | GSP500400A           | GAMR500                                          | GTBMTBKT400                  |
| G500500225G  | G500P500        | G500P500H       | G500SMP225      | G500SMP225H     | G50SMR225                 | GHS500225            | —                  | GSP500500A           | GAMR500                                          | GTBMTBKT500                  |
| G500500300G  | G500P500        | G500P500H       | G500SMP300      | G500SMP300H     | G50SMR300                 | GHS500300            | —                  | GSP500500A           | GAMR500                                          | GTBMTBKT500                  |
| G600400225G  | G600P400        | G600P400H       | G600SMP225      | G600SMP225H     | G50SMR225                 | GHS400225            | —                  | —                    | GAMR600                                          | GTBMTBKT400                  |
| G600500200G  | G600P500        | G600P500H       | G600SMP200      | G600SMP200H     | G50SMR200                 | GHS500200            | —                  | GSP600500A           | GAMR600                                          | GTBMTBKT500                  |
| G600500300G  | G600P500        | G600P500H       | G600SMP300      | G600SMP300H     | G50SMR300                 | GHS500300            | —                  | GSP600500A           | GAMR600                                          | GTBMTBKT500                  |
| G600600225G  | G600P600        | G600P600H       | G600SMP225      | G600SMP225H     | G50SMR225                 | GHS600225            | —                  | GSP600600A           | GAMR600                                          | GTBMTBKT600                  |
| G600600325G  | G600P600        | G600P600H       | G600SMP325      | G600SMP325H     | G50SMR325                 | GHS600325            | —                  | GSP600600A           | GAMR600                                          | GTBMTBKT600                  |
| G600600400G  | G600P600        | G600P600H       | G600SMP400      | G600SMP400H     | G50SMR400                 | GHS600400            | —                  | GSP600600A           | GAMR600                                          | GTBMTBKT600                  |
| G600800300G  | G800P600        | G600P800H       | G600SMP300      | G600SMP300H     | G50SMR300                 | GHS800300            | GPB800300          | —                    | GAMR600                                          | GTBMTBKT800                  |
| G700500250G  | G700P500        | G700P500H       | G700SMP250      | G700SMP250H     | G50SMR250                 | GHS500250            | —                  | GSP700500A           | GAMR700                                          | GTBMTBKT500                  |
| G800600225G  | G800P600        | G800P600H       | G800SMP225      | G800SMP225H     | G50SMR225                 | GHS600225            | —                  | GSP800600A           | GAMR800                                          | GTBMTBKT600                  |
| G800600325G  | G800P600        | G800P600H       | G800SMP325      | G800SMP325H     | G50SMR325                 | GHS600325            | —                  | GSP800600A           | GAMR800                                          | GTBMTBKT600                  |
| G800600425G  | G800P600        | G800P600H       | G800SMP425      | G800SMP425H     | G50SMR425                 | —                    | —                  | GSP800600A           | GAMR800                                          | GTBMTBKT600                  |
| G800800225G  | G800P800        | G800P800H       | G800SMP225      | G800SMP225H     | G50SMR225                 | —                    | —                  | —                    | GAMR800                                          | GTBMTBKT800                  |
| G800800300G  | G800P800        | G800P800H       | G800SMP300      | G800SMP300H     | G50SMR300                 | GHS800300            | GPB800300          | —                    | GAMR800                                          | GTBMTBKT800                  |
| G1000600250G | G1000P600       | G1000P600H      | G1000SMP250     | G1000SMP250H    | G50SMR250                 | GHS600250            | —                  | GSP1000600A          | GAMR1000                                         | GTBMTBKT600                  |
| G1000800300G | G1000P800       | G1000P800H      | G1000SMP300     | G1000SMP300H    | G50SMR300                 | GHS800300            | GPB800300          | GSP1000800A          | GAMR1000                                         | GTBMTBKT800                  |
| G1000800400G | G1000P800       | G1000P800H      | G1000SMP400     | G1000SMP400H    | G50SMR400                 | GHS800400            | GPB800400          | GSP1000800A          | GAMR1000                                         | GTBMTBKT800                  |
| G1200800300G | G1200P800       | G1200P800H      | G1200SMP300     | G1200SMP300H    | G50SMR300                 | GHS800300            | GPB800300          | GSP1200800A          | GAMR1200                                         | GTBMTBKT800                  |
| G1200800400G | G1200P800       | G1200P800H      | G1200SMP400     | G1200SMP400H    | G50SMR400                 | GHS800400            | GPB800400          | GSP1200800A          | GAMR1200                                         | GTBMTBKT800                  |
| G1200900325G | G1200P900       | G1200P900H      | G1200SMP325     | G1200SMP325H    | G50SMR325                 | GHS900325            | GPB900325          | GSP1200900A          | GAMR1200                                         | GTBMTBKT900                  |
| G1500900325G | G1500P900       | G1500P900H      | G1500SMP325     | G1500SMP325H    | G50SMR325                 | GHS900325            | GPB900325          | GSP1500900A          | GAMR1500                                         | GTBMTBKT900                  |
| G1500900425G | G1500P900       | G1500P900H      | G1500SMP425     | G1500SMP425H    | G50SMR425                 | GHS900425            | GPB900425          | GSP1500900A          | GAMR1500                                         | GTBMTBKT900                  |

## GLAND PLATE



Constructed of 1.5-mm thick (16 gauge) steel and designed for use with FUSION G7™ enclosures. Provides a removable cable egress and entry plate while maintaining IP/UL/CSA integrity of the enclosure. RAL 7035 textured, light-gray polyester powder paint finish. Foam-in-place gasket, fasteners and instructions provided. Maintains IP66/UL/CSA Type 4 and 12 when properly installed on a Hoffman enclosure.

## BULLETIN: A4GY



89000888

| Catalog Number | Cutout Size (mm) | Cutout Size (in.) | W x H (mm) | W x H (in.)  |
|----------------|------------------|-------------------|------------|--------------|
| GGP90180       | 90 x 180         | 3.54 x 7.09       | 165 x 255  | 6.50 x 10.04 |
| GGP90280       | 90 x 280         | 3.54 x 11.02      | 165 x 355  | 6.50 x 13.98 |
| GGP150180      | 150 x 180        | 5.91 x 7.09       | 225 x 255  | 8.86 x 10.04 |
| GGP150280      | 150 x 280        | 5.91 x 11.02      | 225 x 355  | 8.86 x 13.98 |


## FRONT AND BACK VERTICAL ACCESSORY MOUNTING RAILS



Constructed of galvanized steel. Front rail is 2.0-mm thick (14 gauge) and back rail is 1.5-mm thick (16 gauge). Package includes two front and two back rails and mounting screws.

*Required for side-mount and adjustable-depth accessory installation.*

**BULLETIN: A4GY**



**Front Rail**

**Back Rail**


| Catalog Number | Fits A (mm) | Fits A (in.) |
|----------------|-------------|--------------|
| GAMR300        | 300         | 11.81        |
| GAMR400        | 400         | 15.75        |
| GAMR500        | 500         | 19.68        |
| GAMR600        | 600         | 23.62        |
| GAMR700        | 700         | 27.56        |
| GAMR800        | 800         | 31.50        |
| GAMR1000       | 1000        | 39.37        |
| GAMR1200       | 1200        | 47.24        |
| GAMR1500       | 1500        | 59.05        |

FULL-HEIGHT BACK PANEL




Galvanized steel full-height panels. See table for thickness.  
M8 panel mounting nuts provided with 50-mm front-to-back side-mount  
accessory rails and side-mount accessory rail brackets.

BULLETIN: A4GY




| Catalog Number | D x E (mm) | D x E (in.)   | Thickness (mm) | Thickness (Gauge) | Fits A x B (mm)           | Fits A x B (in.)                  |
|----------------|------------|---------------|----------------|-------------------|---------------------------|-----------------------------------|
| G300P300       | 255 x 255  | 10.04 x 10.04 | 1.5            | 16                | 300 x 300                 | 11.81 x 11.81                     |
| G400P300       | 355 x 255  | 13.98 x 10.04 | 1.5            | 16                | 400 x 300<br>or 300 x 400 | 15.75 x 11.81<br>or 11.81 x 15.75 |
| G400P400       | 355 x 355  | 13.98 x 13.98 | 1.5            | 16                | 400 x 400                 | 15.75 x 15.75                     |
| G500P400       | 455 x 355  | 17.91 x 13.98 | 1.5            | 16                | 500 x 400                 | 19.68 x 15.75                     |
| G600P400       | 555 x 355  | 21.85 x 13.98 | 1.5            | 16                | 600 x 400<br>or 400 x 600 | 23.62 x 15.75<br>or 15.75 x 23.62 |
| G500P500       | 455 x 455  | 17.91 x 17.91 | 1.5            | 16                | 500 x 500                 | 19.68 x 19.68                     |
| G600P500       | 555 x 455  | 21.85 x 17.91 | 1.5            | 16                | 600 x 500                 | 23.62 x 19.68                     |
| G700P500       | 655 x 455  | 25.79 x 17.91 | 2.0            | 14                | 700 x 500                 | 27.56 x 19.68                     |
| G600P600       | 555 x 555  | 21.85 x 21.85 | 2.0            | 14                | 600 x 600                 | 23.62 x 23.62                     |
| G800P600       | 755 x 555  | 29.72 x 21.85 | 2.0            | 14                | 800 x 600<br>or 600 x 800 | 31.50 x 23.62<br>or 23.62 x 31.50 |
| G1000P600      | 955 x 555  | 37.60 x 21.85 | 2.5            | 12                | 1000 x 600                | 39.37 x 23.62                     |
| G800P800       | 755 x 755  | 29.72 x 29.72 | 2.5            | 12                | 800 x 800                 | 31.50 x 31.50                     |
| G1000P800      | 955 x 755  | 37.60 x 29.72 | 2.5            | 12                | 1000 x 800                | 39.37 x 31.50                     |
| G1200P800      | 1155 x 755 | 45.47 x 29.72 | 2.5            | 12                | 1200 x 800                | 47.24 x 31.50                     |
| G1200P900      | 1155 x 855 | 45.47 x 33.66 | 2.5            | 12                | 1200 x 900                | 47.24 x 35.43                     |
| G1500P900      | 1455 x 855 | 57.28 x 33.66 | 2.5            | 12                | 1500 x 900                | 59.05 x 35.43                     |

## HALF-HEIGHT BACK PANEL



Galvanized steel half-height back panels. See table for thickness.  
*M8 panel mounting nuts provided with 50-mm front-to-back side-mount accessory rails and side-mount accessory rail brackets.*

**BULLETIN: A4GY**




| Catalog Number | D x E (mm) | D x E (in.)   | Thickness (mm) | Thickness (Gauge) | Fits A x B (mm) | Fits A x B (in.) |
|----------------|------------|---------------|----------------|-------------------|-----------------|------------------|
| G300P300H      | 120 x 255  | 4.72 x 10.04  | 1.5            | 16                | 300 x 300       | 11.81 x 11.81    |
| G300P400H      | 120 x 355  | 4.72 x 13.98  | 1.5            | 16                | 300 x 400       | 11.81 x 15.75    |
| G400P300H      | 170 x 255  | 6.69 x 10.01  | 1.5            | 16                | 400 x 300       | 15.75 x 11.81    |
| G400P400H      | 170 x 355  | 6.69 x 13.98  | 1.5            | 16                | 400 x 400       | 15.75 x 15.75    |
| G400P600H      | 170 x 555  | 6.69 x 21.85  | 1.5            | 16                | 400 x 600       | 15.75 x 23.62    |
| G500P400H      | 220 x 355  | 8.66 x 13.98  | 1.5            | 16                | 500 x 400       | 19.68 x 15.75    |
| G500P500H      | 220 x 455  | 8.66 x 17.91  | 1.5            | 16                | 500 x 500       | 19.68 x 19.68    |
| G600P400H      | 270 x 355  | 10.63 x 13.98 | 1.5            | 16                | 600 x 400       | 23.62 x 15.75    |
| G600P500H      | 270 x 455  | 10.63 x 17.91 | 1.5            | 16                | 600 x 500       | 23.62 x 19.68    |
| G600P600H      | 270 x 555  | 10.63 x 21.85 | 1.5            | 16                | 600 x 600       | 23.62 x 23.62    |
| G600P800H      | 270 x 755  | 10.63 x 29.72 | 1.5            | 16                | 600 x 800       | 23.62 x 32.50    |
| G700P500H      | 320 x 455  | 12.60 x 17.91 | 1.5            | 16                | 700 x 500       | 27.56 x 19.68    |
| G800P600H      | 370 x 555  | 14.57 x 21.85 | 1.5            | 16                | 800 x 600       | 31.50 x 23.62    |
| G800P800H      | 370 x 755  | 14.57 x 29.72 | 1.5            | 16                | 800 x 800       | 32.50 x 32.50    |
| G1000P600H     | 470 x 555  | 18.50 x 21.85 | 1.5            | 16                | 1000 x 600      | 39.37 x 23.62    |
| G1000P800H     | 470 x 755  | 18.50 x 29.72 | 2.0            | 14                | 1000 x 800      | 39.37 x 31.50    |
| G1200P800H     | 570 x 755  | 22.44 x 29.72 | 2.0            | 14                | 1200 x 800      | 47.24 x 31.50    |
| G1200P900H     | 570 x 855  | 22.44 x 33.66 | 2.0            | 14                | 1200 x 900      | 47.24 x 35.43    |
| G1500P900H     | 720 x 855  | 28.35 x 33.66 | 2.0            | 14                | 1500 x 900      | 59.05 x 35.43    |

FULL-HEIGHT SIDE PANEL



Galvanized steel full-height side panels. Panel mounting hardware is furnished with the panel. See table for thickness.

BULLETIN: A4GY



| Catalog Number | D x E (mm) | D x E (in.)   | Thickness (mm) | Thickness (Gauge) | Fits A x C (mm) | Fits A x C (in.) |
|----------------|------------|---------------|----------------|-------------------|-----------------|------------------|
| G300SMP200     | 255 x 142  | 10.04 x 5.59  | 1.5            | 16                | 300 x 200       | 11.71 x 7.87     |
| G300SMP225     | 255 x 167  | 10.01 x 6.57  | 1.5            | 16                | 300 x 255       | 11.71 x 10.04    |
| G400SMP150     | 355 x 92   | 13.98 x 3.62  | 1.5            | 16                | 400 x 150       | 15.75 x 5.91     |
| G400SMP225     | 355 x 167  | 13.98 x 6.57  | 1.5            | 16                | 400 x 225       | 15.75 x 10.04    |
| G500SMP225     | 455 x 167  | 17.91 x 6.57  | 1.5            | 16                | 500 x 255       | 19.68 x 10.04    |
| G500SMP300     | 455 x 242  | 17.91 x 9.53  | 1.5            | 16                | 500 x 300       | 19.68 x 11.71    |
| G600SMP200     | 555 x 142  | 21.85 x 5.59  | 1.5            | 16                | 600 x 200       | 23.62 x 7.87     |
| G600SMP225     | 555 x 167  | 21.85 x 6.57  | 1.5            | 16                | 600 x 225       | 23.62 x 10.04    |
| G600SMP300     | 555 x 242  | 21.85 x 9.53  | 1.5            | 16                | 600 x 300       | 23.62 x 11.71    |
| G600SMP325     | 555 x 267  | 21.85 x 10.51 | 1.5            | 16                | 600 x 325       | 23.62 x 12.80    |
| G600SMP400     | 555 x 342  | 21.85 x 13.46 | 1.5            | 16                | 600 x 400       | 23.62 x 15.75    |
| G700SMP250     | 655 x 192  | 25.79 x 7.56  | 1.5            | 16                | 700 x 250       | 27.56 x 9.84     |
| G800SMP225     | 755 x 167  | 29.72 x 6.57  | 1.5            | 16                | 800 x 225       | 31.50 x 10.04    |
| G800SMP300     | 755 x 242  | 29.72 x 9.53  | 1.5            | 16                | 800 x 300       | 31.50 x 11.71    |
| G800SMP325     | 755 x 267  | 29.72 x 10.51 | 1.5            | 16                | 800 x 325       | 31.50 x 12.80    |
| G800SMP425     | 755 x 367  | 29.72 x 14.45 | 1.5            | 16                | 800 x 425       | 31.50 x 16.73    |
| G1000SMP250    | 955 x 192  | 37.60 x 7.56  | 1.5            | 16                | 1000 x 250      | 39.37 x 9.87     |
| G1000SMP300    | 955 x 242  | 37.60 x 9.53  | 1.5            | 16                | 1000 x 300      | 39.37 x 11.71    |
| G1000SMP400    | 955 x 342  | 37.60 x 13.46 | 1.5            | 16                | 1000 x 400      | 39.37 x 15.75    |
| G1200SMP300    | 1155 x 242 | 45.47 x 9.53  | 1.5            | 16                | 1200 x 300      | 47.24 x 11.71    |
| G1200SMP325    | 1155 x 267 | 45.47 x 10.51 | 1.5            | 16                | 1200 x 325      | 47.24 x 12.80    |
| G1200SMP400    | 1155 x 342 | 45.47 x 13.46 | 1.5            | 16                | 1200 x 400      | 47.24 x 15.75    |
| G1500SMP325    | 1455 x 267 | 57.28 x 10.51 | 1.5            | 16                | 1500 x 325      | 59.05 x 12.80    |
| G1500SMP425    | 1455 x 367 | 57.28 x 14.45 | 1.5            | 16                | 1500 x 425      | 59.05 x 16.73    |




HALF-HEIGHT SIDE PANEL



Galvanized steel half-height side panels are 1.5-mm thick (16 gauge). Panel mounting hardware is furnished with the panel.

BULLETIN: A4GY




| Catalog Number | D x E (mm) | D x E (in.)   | Fits A x C (mm) | Fits A x C (in.) |
|----------------|------------|---------------|-----------------|------------------|
| G300SMP200H    | 120 x 142  | 4.72 x 5.59   | 300 x 200       | 11.81 x 7.87     |
| G300SMP225H    | 120 x 167  | 4.72 x 6.57   | 300 x 225       | 11.81 x 8.86     |
| G400SMP150H    | 170 x 92   | 6.69 x 3.62   | 400 x 150       | 15.75 x 5.91     |
| G400SMP225H    | 170 x 167  | 6.69 x 6.57   | 400 x 225       | 15.75 x 8.86     |
| G500SMP225H    | 220 x 167  | 8.66 x 6.57   | 500 x 225       | 19.68 x 8.86     |
| G500SMP300H    | 220 x 242  | 8.66 x 9.53   | 500 x 300       | 19.68 x 11.81    |
| G600SMP200H    | 270 x 142  | 10.63 x 5.59  | 600 x 200       | 23.62 x 7.87     |
| G600SMP225H    | 270 x 167  | 10.63 x 6.57  | 600 x 225       | 23.62 x 8.86     |
| G600SMP300H    | 270 x 242  | 10.63 x 9.53  | 600 x 300       | 23.62 x 11.81    |
| G600SMP325H    | 270 x 267  | 10.63 x 10.51 | 300 x 325       | 11.81 x 12.76    |
| G600SMP400H    | 270 x 342  | 10.63 x 13.46 | 600 x 400       | 23.62 x 15.75    |
| G700SMP250H    | 320 x 192  | 12.60 x 7.56  | 700 x 250       | 27.56 x 9.84     |
| G800SMP225H    | 370 x 167  | 14.57 x 6.57  | 800 x 225       | 31.50 x 8.86     |
| G800SMP300H    | 370 x 242  | 14.57 x 9.53  | 800 x 300       | 31.50 x 11.81    |
| G800SMP325H    | 370 x 267  | 14.57 x 10.51 | 800 x 325       | 31.50 x 12.76    |
| G800SMP425H    | 370 x 367  | 14.57 x 14.45 | 800 x 425       | 31.50 x 16.73    |
| G1000SMP250H   | 470 x 192  | 18.50 x 7.56  | 1000 x 250      | 39.37 x 9.84     |
| G1000SMP300H   | 470 x 242  | 18.50 x 9.53  | 1000 x 300      | 39.37 x 11.81    |
| G1000SMP400H   | 470 x 342  | 18.50 x 13.46 | 1000 x 400      | 39.37 x 15.75    |
| G1200SMP300H   | 570 x 242  | 22.44 x 9.53  | 1200 x 300      | 47.24 x 11.81    |
| G1200SMP325H   | 570 x 267  | 22.44 x 10.51 | 1200 x 325      | 47.24 x 12.76    |
| G1200SMP400H   | 570 x 342  | 22.44 x 13.46 | 1200 x 400      | 47.24 x 15.75    |
| G1500SMP325H   | 720 x 267  | 28.35 x 10.51 | 1500 x 325      | 59.05 x 12.80    |
| G1500SMP425H   | 720 x 367  | 28.35 x 14.45 | 1500 x 425      | 59.05 x 16.73    |

SIDE-MOUNT ACCESSORY RAIL



Easy-to-install side (front-to-back) mounting rails provide side and depth mounting capability using minimal tools. Rails are 1.5-mm thick (16 gauge) galvanized steel. Qty. 4 per package. Includes panel-mount brackets, nuts and screws.

BULLETIN: A4GY




| Catalog Number | Fits Depth (mm) | Fits Depth (in.) |
|----------------|-----------------|------------------|
| G50SMR150      | 150             | 5.91             |
| G50SMR200      | 200             | 7.87             |
| G50SMR225      | 225             | 8.86             |
| G50SMR250      | 250             | 9.84             |
| G50SMR300      | 300             | 11.81            |
| G50SMR325      | 325             | 12.80            |
| G50SMR400      | 400             | 15.75            |
| G50SMR425      | 425             | 16.73            |

HORIZONTAL SEPARATOR



Horizontal Separator mounts onto side-mount accessory rails to divide the FUSION G7™ into separate compartments. Galvanized 1.5-mm thick (16 gauge) steel. Mounting hardware provided.

BULLETIN: A4GY




| Catalog Number | Fits B x C (mm) | Fits B x C (in.) | W x D (mm) | W x D (in.)   | S (mm) | S (in.) |
|----------------|-----------------|------------------|------------|---------------|--------|---------|
| GHS300225      | 300 x 225       | 11.81 x 8.86     | 255 x 148  | 10.04 x 5.83  | 100    | 3.94    |
| GHS400200      | 400 x 200       | 15.75 x 7.87     | 355 x 123  | 13.98 x 4.84  | 75     | 2.95    |
| GHS400225      | 400 x 225       | 15.75 x 8.86     | 355 x 148  | 13.98 x 5.83  | 100    | 3.94    |
| GHS500200      | 500 x 200       | 19.68 x 7.87     | 455 x 123  | 17.91 x 4.84  | 75     | 2.95    |
| GHS500225      | 500 x 225       | 19.68 x 8.86     | 455 x 148  | 17.91 x 5.83  | 100    | 3.94    |
| GHS500250      | 500 x 250       | 19.68 x 9.84     | 455 x 173  | 17.91 x 6.81  | 125    | 4.92    |
| GHS500300      | 500 x 300       | 19.68 x 11.81    | 455 x 223  | 17.91 x 8.87  | 175    | 6.89    |
| GHS600225      | 600 x 225       | 23.62 x 8.86     | 555 x 148  | 21.85 x 5.83  | 100    | 3.94    |
| GHS600250      | 600 x 250       | 23.62 x 9.84     | 555 x 173  | 21.85 x 6.81  | 125    | 4.92    |
| GHS600325      | 600 x 325       | 23.62 x 12.80    | 555 x 248  | 21.85 x 9.76  | 200    | 7.78    |
| GHS600400      | 600 x 400       | 23.62 x 15.75    | 555 x 323  | 21.85 x 12.72 | 275    | 10.83   |
| GHS800300      | 800 x 300       | 32.50 x 11.81    | 755 x 223  | 29.72 x 8.78  | 175    | 6.89    |
| GHS800400      | 800 x 400       | 32.50 x 15.75    | 755 x 323  | 29.72 x 12.72 | 275    | 10.83   |
| GHS900325      | 900 x 325       | 35.43 x 12.50    | 855 x 248  | 33.66 x 9.76  | 200    | 7.87    |
| GHS900425      | 900 x 425       | 35.43 x 16.73    | 855 x 348  | 33.66 x 13.70 | 300    | 11.81   |

PADLOCK INSERTS



Padlock Inserts fit into standard quarter-turn latches. They are made of black composite material (PBT) with zinc insert and replace the standard 3-mm double-bit insert when padlocking security is required. Available with 3-mm double bit or slotted screwdriver tool to open. Accommodate up to 5/16-in. diameter padlock shank.

BULLETIN: A4GY




| Catalog Number | Description                        |
|----------------|------------------------------------|
| GPDLOCK3MM     | 3-mm double-bit padlock insert     |
| GPDLOCKSL0T    | Slotted screwdriver padlock insert |

## HANDLES



These black composite handles with zinc insert can replace the standard quarter-turn 3-mm double bit insert on all FUSION G7™ wall-mount enclosures. The keylocking handle is available for applications requiring quick access and keylocking security. The padlocking handle accommodates up to a 5/16-in. diameter padlock shank. Each latch system can be converted from clockwise to counter-clockwise opening. Maintains IP66 and UL/CSA Type 4 and 12 when properly installed in a Hoffman FUSION G7 enclosure.

**BULLETIN: A4GY**



| Catalog Number | Description        |
|----------------|--------------------|
| GKEYLOCKHDL    | Key-Locking Handle |
| GPDLOCKHDL     | Padlocking Handle  |

## HINGE PIN KITS



Easy-to-remove and replace hinge pins facilitate door removal or reversing. Available in plated or stainless steel.

**BULLETIN: A4GY, VM3**

| Catalog Number | Description     | Pkg. Qty. |
|----------------|-----------------|-----------|
| GHPINSS        | Stainless steel | 2         |
| GHPINMS        | Plated steel    | 2         |

## DIN RAIL MOUNTING ADAPTER



Allows quick and simple installation of TS35 x 7.5 DIN (DIN3) rail. Black composite (PBT) material. DIN rail not included.

**BULLETIN: A4GY**


| Catalog Number | Pkg. Qty. |
|----------------|-----------|
| GDINRAILBKT    | 10        |

100-MM PLINTH BASE



Install 100-mm Plinth Base under FUSION G7™ enclosure to provide space for cables to enter from below. Constructed of 1.5-mm thick (16 gauge) steel sides and 2.5-mm thick (12 gauge) corners with textured RAL 9005 black finish. Mounting hardware included with base.

BULLETIN: A4GY




| Catalog Number | Fits B x C (mm) | Fits B x C (in.) | W x D (mm) | W x D (in.)   |
|----------------|-----------------|------------------|------------|---------------|
| GPB800300      | 800 x 300       | 31.50 x 11.81    | 800 x 279  | 31.50 x 10.98 |
| GPB800400      | 800 x 400       | 31.50 x 15.75    | 800 x 379  | 31.50 x 14.92 |
| GPB900325      | 900 x 325       | 35.43 x 12.80    | 900 x 304  | 35.43 x 11.97 |
| GPB900425      | 900 x 425       | 35.43 x 16.73    | 900 x 404  | 35.43 x 15.91 |

ALUMINUM SWING PANEL



2.5-mm (.100-in.) thick Aluminum Swing Panel provides a convenient way to install controls and instruments near the front of the FUSION G7™ enclosure while providing access and security. Mounting hardware and 3-mm double-bit key included with panel.

BULLETIN: A4GY



| Catalog Number | Fits A x B (mm) | Fits A x B (in.) | H x W (mm) | H x W (in.)   |
|----------------|-----------------|------------------|------------|---------------|
| GSP400300A     | 400 x 300       | 15.75 x 11.81    | 315 x 233  | 12.40 x 9.16  |
| GSP500400A     | 500 x 400       | 19.68 x 15.75    | 415 x 333  | 16.34 x 13.11 |
| GSP500500A     | 500 x 500       | 19.68 x 19.68    | 415 x 433  | 16.34 x 17.05 |
| GSP600500A     | 600 x 500       | 23.62 x 19.68    | 515 x 433  | 20.27 x 17.05 |
| GSP600600A     | 600 x 600       | 23.62 x 23.62    | 515 x 533  | 20.27 x 20.98 |
| GSP700500A     | 700 x 500       | 27.56 x 19.68    | 615 x 433  | 24.21 x 17.05 |
| GSP800600A     | 800 x 600       | 32.50 x 23.62    | 715 x 533  | 28.15 x 20.98 |
| GSP1000600A    | 1000 x 600      | 39.37 x 23.62    | 915 x 533  | 36.02 x 20.98 |
| GSP1000800A    | 1000 x 800      | 39.37 x 31.50    | 915 x 733  | 36.02 x 28.86 |
| GSP1200800A    | 1200 x 800      | 47.24 x 31.50    | 1115 x 733 | 28.24 x 28.86 |
| GSP1200900A    | 1200 x 900      | 47.24 x 35.43    | 1115 x 833 | 28.24 x 32.80 |
| GSP1500900A    | 1500 x 900      | 59.05 x 35.43    | 1415 x 833 | 55.71 x 32.80 |

DOUBLE-BIT KEYS



Black non-metallic 3-mm double-bit keys. Package of two.

BULLETIN: A4GY

| Catalog Number | Description              | Pkg. Qty. |
|----------------|--------------------------|-----------|
| GKEY3MMDB      | 3-mm black, non-metallic | 2         |

### SCREW PACKAGE



5-mm screws for FUSION G7™ internal accessories. Package of 20.

**BULLETIN: A4GY**

| Catalog Number | Description              | Pkg. Qty. |
|----------------|--------------------------|-----------|
| GSM5           | 5-mm screw M5 x 0.8 x 10 | 20        |

### PANEL MOUNTING BRACKETS




Package includes four mounting brackets, four M8 nuts and eight 5-mm screws.

**BULLETIN: A4GY**

| Catalog Number | Description                                             |
|----------------|---------------------------------------------------------|
| GSMRBKTS       | Panel mounting brackets; fit side-mount accessory rails |

### FULL-WIDTH TOP AND BOTTOM MOUNTING-BRACKET KITS WITH STUDS



Use to mount FUSION G7™ to a wall or another enclosure. Includes two 2.5-mm thick (12 gauge) steel external mounting brackets and mounting hardware. Finished with RAL 7035 textured light-gray polyester powder paint.

*Mounting brackets are required to maintain UL/CSA external mounting requirement.*

**BULLETIN: A4GY**

| Catalog Number | Fits B (mm) | Fits B (in.) | L (mm) | L (in.) | S (mm) | S (in.) |
|----------------|-------------|--------------|--------|---------|--------|---------|
| GTBMTBKT300    | 300         | 11.81        | 296    | 11.65   | 262    | 10.31   |
| GTBMTBKT400    | 400         | 15.75        | 396    | 15.59   | 362    | 14.25   |
| GTBMTBKT500    | 500         | 19.68        | 496    | 19.53   | 462    | 18.19   |
| GTBMTBKT600    | 600         | 23.62        | 596    | 23.46   | 562    | 22.12   |
| GTBMTBKT800    | 800         | 31.50        | 796    | 31.34   | 762    | 30.00   |
| GTBMTBKT900    | 900         | 35.43        | 896    | 35.62   | 862    | 33.93   |

FUSION G7™ DOOR STOP KIT



Designed for use on FUSION G7 enclosures to secure the door in the open position. Door Stop Kit can be mounted at the top or bottom of the door opening, as well as left- or right-hand hinged. Door stop is stainless steel with plated and stainless steel mounting hardware. Maintains IP66 and UL/CSA Type 4 and 12 when properly installed in a Hoffman FUSION G7 enclosure.

BULLETIN: A4GY

| Catalog Number | Description             |
|----------------|-------------------------|
| GDSTOPK        | FUSION G7 Door Stop Kit |

LOCK INSERTS



Lock inserts can be substituted for the standard 3-mm double-bit latch insert. Inserts have a chrome finish. Matching key is zinc die-cast.

BULLETIN: A4GY, CWY

| Catalog Number | Description                     |
|----------------|---------------------------------|
| CLKTM7         | Triangular 7-mm insert with key |
| CLKSM7         | Square 7-mm insert with key     |
| CLKDBM3        | Double bit with key             |
| CLKSLOT        | Slotted Insert no key           |

MOUNTING-BRACKET KITS



Mounting-Bracket Kits are field installable. Composite and stainless steel brackets are rated to Type 4X. Set of four (4) brackets can support 500 lb. maximum load. All hardware is included. Four brackets per kit. *Mounting brackets are required to maintain UL/CSA external mounting requirement.*

BULLETIN: A80

| Catalog Number | Description     |
|----------------|-----------------|
| CMFK           | Steel           |
| CMFKSS         | Stainless Steel |
| CMTGFT         | Composite       |

DOOR BARS



Non-metallic door bar includes pressure-sensitive tape adhesive.

BULLETIN: CWY


| Catalog Number | Description | Length         | Qty. |
|----------------|-------------|----------------|------|
| ADB305MM       | Door Bar    | 8 in. (203 mm) | 4    |

## THERMOPLASTIC DATA POCKET



Provides a convenient place to store wiring diagrams, operation manuals and other documentation inside the enclosure. Adhesive-backed pockets mount inside the solid enclosure cover. Mounting hardware included. Thermoplastic pockets are dark gray and have cut-away areas for easy inspection of contents.

**BULLETIN: UX1Y**



| Catalog Number | Description  | Size L x W<br>in./mm       |
|----------------|--------------|----------------------------|
| ADP1           | Small pocket | 6.00 x 6.00<br>152 x 152   |
| ADP2           | Large pocket | 12.00 x 12.00<br>305 x 305 |


## VELCRO® CABLE WRAP



Securely holds cable to cable manager and unfastens easily for cable maintenance. VELCRO® is 0.5-in. (12.7-mm) wide. Available in 8- and 12-in. (203- and 305-mm) lengths in both screw fastener and wrap styles. M5 self-tapping screw is used on Net Series or PROLINE™ frames.

*VELCRO is a trademark of Velcro Industries B.V.*

**BULLETIN: DACCY**



| Catalog Number | Description                                          | L (in.) | L (mm) | Color  | Pkg. Qty. |
|----------------|------------------------------------------------------|---------|--------|--------|-----------|
| ECWTD8B        | Screw fastener style.<br>Includes M5 mounting screw. | 8.00    | 203    | Black  | 10        |
| ECWTD12B       | Screw fastener style.<br>Includes M5 mounting screw. | 12.00   | 305    | Black  | 10        |
| ECW8B          | Wrap style                                           | 8.00    | 203    | Black  | 10        |
| ECW8R          | Wrap style                                           | 8.00    | 203    | Red    | 10        |
| ECW8BL         | Wrap style                                           | 8.00    | 203    | Blue   | 10        |
| ECW8Y          | Wrap style                                           | 8.00    | 203    | Yellow | 10        |
| ECW12B         | Wrap style                                           | 12.00   | 305    | Black  | 10        |
| ECW12R         | Wrap style                                           | 12.00   | 305    | Red    | 10        |
| ECW12BL        | Wrap style                                           | 12      | 305    | Blue   | 10        |
| ECW12Y         | Wrap style                                           | 12      | 305    | Yellow | 10        |

Notes