

**Model 7286**  
**XLR (M) / Triple Binding Post**



Model 7286 XLR (M) / Triple Binding Post

## Features

- 5-way binding posts accept banana plugs vertically or horizontally, dual or triple banana plugs vertically or horizontally, bare wire via through-holes, alligator clips or spade lugs.
- XLR plug enables connection to audio cable links or broadcast system panels.
- Gold plated pins and binding posts for excellent conductivity.
- $\frac{3}{4}$ " Spacing between banana jacks allows dual or triple banana plug connections.
- Cross holes have large 3.8mm (0.150") diameter for easy wire access.
- Rugged body exterior.

## Materials

- Adapter body is made of rugged ABS.
- Binding posts: gold plated brass. Nylon 6 hex nuts.
- XLR Body: Die cast zinc.
- XLR male center pin contacts: gold plated brass.


**USA:** Sales: 800-490-2361

**Technical Support:** 800-241-2060 **Fax:** 888-403-3360


**Europe:** 31-(0) 40 2675 150 **International:** 425-446-5500

e-mail: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)

**Where to Buy:** [www.pomonaelectronics.com](http://www.pomonaelectronics.com)



## Connection Schematic



## Specifications

- Voltage: 33 Vrms / 70 Vdc

## Ordering Information

Model: 7286, XLR (M) / Triple Binding Post

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02"$  (.51 mm), .xxx =  $\pm .005"$  (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[7284](#)