



Heyco® Original Strain Relief Bushings


Pigtail with Integral Nylon Spring, for Flat and Round Cables

| UL Type | WILL FIT THESE CABLES | | | PANEL DIMENSIONS | | | PART NO. Black | DESC | PART DIMENSIONS | | Mounting Hole Plug PART NO. | | | |
|-------------------------------|-----------------------|---------------------|---------|-----------------------------------|------------------------------------|--|-------------------|------|--------------------------------|--------------------------------|-------------------------------------|--|--|--|
| | AWG/ Conductors | Approximate Size | | A Mounting Hole Dia. in. | B To Prevent Rotation in. | Finished Fit Panel Thickness* in. mm. | | | C HEAD LENGTH in. mm. | D BODY LENGTH in. mm. | | | | |
| | | in. | mm. | | | | | | | | | | | |
| For Flat Cables | | | | | | | | | | | | | | |
| SPT-1 | 18/3 | .12x.30 | 3.0x7.6 | | | | | | | | | | | |
| SPT-2 & HPN | 18/2 | .15x.28 | 3.8x7.1 | .500 | 12.7 | .465 | 11.8 | .062 | 1.6 | 1541 | SR 4N-7 1.718 43.6 1.984 50.4 2491 | | | |
| For Round Cables | | | | | | | | | | | | | | |
| SV & SVT | 18/2 | .250 | 6.4 | .500 | 12.7 | | | | | | | | | |
| | 18/3 | .255 | 6.5 | .500- .515 | 12.7- 13.1 | | | | | | | | | |
| HPD | 18/2 | .270 | 6.9 | .500 | 12.7 | | | | | | | | | |
| | 16/2 | .290 | 7.4 | .500- .515 | 12.7- 13.1 | | | | | | | | | |
| Same as SR 5N-7 above except | | | | | | | | | | | | | | |
| SJ, SJO & SJT | 18/2 | .300 | 7.6 | .625 | 15.9 | .550 | 14.0 | .062 | 1.6 | 1596 | SR 6N-7 1.718 43.6 2.109 53.6 2497 | | | |
| Same as SR 6N-7 above except | | | | | | | | | | | | | | |
| SJ, SJO & SJT | 16/2 | .315 | 8.0 | | | | | | | | | | | |
| | 18/3 | .320 | 8.1 | | | | | | | | | | | |
| | 14/2 | .350 | 8.9 | .625 | 15.9 | .550 | 14.0 | .062 | 1.6 | 1599 | SR 6N3-7 1.718 43.6 2.109 53.6 2497 | | | |
| | 16/3 | .355 | 9.0 | | | | | | | | | | | |
| | 18/4 | .360 | 9.1 | | | | | | | | | | | |
| Same as SR 6N3-7 above except | | | | | | | | | | | | | | |
| SJT | 18/4 | .360 | 9.1 | | | | | | | | | | | |
| SJT & SJT0 | 14/3 | .370 | 9.4 | | | | | | | | | | | |
| S & ST | 18/2 | .390 | 9.9 | .750 | 19.0 | | | | | | | | | |
| | 18/3 | .405 | 10.3 | | | | | | | | | | | |
| | 16/2 | .405 | 10.3 | | | | | | | | | | | |
| | 16/3 | .430 | 10.9 | .750- .781 | 19.0- 19.8 | | | | | | | | | |

Standard color black. Consult Heyco for white and other colors.

*Maximum Panel Thickness. Part has additional clearance. Consult Heyco for your Custom Finished Fit Panel Thickness.

**For use in split housings only: Larger locking step on body and key, for additional pull out resistance.



| | |
|---------------------|---|
| Material | Nylon 6/6 |
| Certifications | Recognized under the Component Program of Underwriters' Laboratories File E15331 Certified by the Canadian Standards Association File 8919 |
| Flammability Rating | 94V-2 |
| Temperature Range | -.04°F (-18°C) to 221°F (105°C) |

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Heyco:

[1593](#) [1599](#) [1590](#) [1611](#) [1605](#) [1602](#) [1596](#) [1541](#) [1604](#)