



List Price \$246.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Ampere Rating	25A
General Application	Short circuit and overcurrent protection
For Use With	OEM Panels and Enclosures
Circuit Breaker Type	Standard
Voltage Rating	240VAC - 125VDC
HACR Rated	Yes
Terminal Type	Line: Box Lug - Load: Box Lug
Mounting Type	Flush, Surface or DIN Rail (35mm)
Weight	8.70 Ounces
Number of Poles	2-Pole
Approvals	UL489 Listed - CSA 22.2 #5.1 Certified - IEC Rated 60947-2
Marketing Trade Name	Multi 9
Enclosure Rating	IP40
Short Circuit Current Rating	10kA@240VAC
Type	C60N
Wire Size	#18 to #4 AWG
Depth	3.00 Inches (76mm)
Height	4.21 Inches (107mm)
Trip Curve	C Curve - Magnetic operates between 7 to 10 times
Width	1.42 Inches (36mm)

Shipping and Ordering

Category	00915 -
Discount Schedule	DE2
GTIN	00785901410157
Package Quantity	1
Weight	0.57 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 08/06/2012 06:57:48