




- 1 FOR MINI APPLICATOR.
- 2 FOR HAND TOOL USE ONLY.
- 3. WIRE RANGE OF 22-28, INSULATION RANGE OF .030-.040.
- 4 GOLD PLATING PER MIL-G-45204, NICKEL PLATING PER QQ-N-290, TIN PLATING PER MIL-T-10727.
- 5 PLATED WITH .000030 GOLD IN LOCALIZED GOLD PLATE AREA, TIN PLATED WIRE BARRELS, OVER .000050 NICKEL.
- 6 PLATED WITH GOLD FLASH IN LOCALIZED GOLD PLATE AREA, TIN PLATED WIRE BARRELS, OVER .000030 NICKEL.
- 7 PLATED WITH .000050 GOLD ON INSIDE OF LOCALIZED GOLD PLATE AREA, .000050 GOLD ON REMAINDER, ALL OVER .000050 NICKEL UNDERPLATE.
- 8 GOLD PLATING ON THE CARRIER STRIP IS NOT REQUIRED.
- 9 OBSOLETE.

SMALL PACK	6	9	748610-7	9	1-748610-1
-	7	8	748610-9	9	748610-8
STANDARD	6	9	748610-7	9	748610-5
-	5	9	748610-4	9	748610-2
PACKAGING	FINISH 4	LOOSE PIECE 2	PART NUMBER 1		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
PHOS BRONZE PER QQ-B-750

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	.005
4 PLC	±	-
ANGLES	±	0° 30'

FINISH

DWN
C.RICHARD
1-12-88

CHK
W.LENKER
1-14-88

APVD
V.KUMAR
1-19-88

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

SOCKET CONTACT, SIZE 22 DF, 22-28 AWG, W/.030-.040 DIA INSULATION SUPPORT

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-748610

RESTRICTED TO

SCALE
10:1

SHEET
1 of 1

REV
H1