


NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING: 4A @125VAC/28VDC, 2A @250VAC
5. DIELECTRI STRENGTH: 1KV RMS min. AT SEA LEVEL
6. ELECTRICAL LIFE: 10,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
7. KEYCODE: A126




CIRCUIT: SP (45°/45° INDEXING)
CONTACT CONFIGURATION

SWITCH FUNCTION		
CONNECTED TERMINAL #		
POS. 1	POS. 2	POS. 3
8-1	1-2	2-3

LEGEND

 = DETENT POSITIONS
 = KEY PULL POSSIBLE IN
THESE POSITIONS



RECOMENDED PANEL CUTOUT



TITLE K0130A

B	21651	REDRAWN INTO INVENTOR FORMAT	10/22/14	A
REV	PCB NO	DESCRIPTION	DATE	APPROVED

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 1:1 DATE 10/21/2014 DR AS DWG K200210 REV B