


Current refinements (click ☐ to remove) Search Tips

☒ Region **USA** ☒ Product Family **Military Standard Nylon Grommet Edging** ☒ Text Search: 'GE52-C69'

Your search criteria matched only one product, shown below.



Part Number:	GE52-C69
RoHS Compliancy Status:	Compliant
Part Description:	Military Specification Nylon Grommet Edging in 12.75" strips.
Material:	Flame Retardant Nylon 6.6
Color:	Natural
Height (In.):	.16
Height (mm):	3.9
Length (In.):	12.75
Length (mm):	323.9
Width (In.):	.15
Width (mm):	3.8
Flammability Rating:	UL94 V-0
Outside Depth (In.):	.155
Outside Depth (mm):	3.9
Outside Width (In.):	.150
Outside Width (mm):	3.8
Panel Thickness Range (In.):	.015 – .052
Panel Thickness Range (mm)	0.4 – 1.3
Temperature Range:	-40°F to 149°F (-40°C to 65°C)
Min. Order UOM:	PC
Min. Order Qty.:	100
BOM Qty. (# of Pkgs.)	0
Add to My Catalog	€

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.