





|           |                                     |          |                                         |           |         |
|-----------|-------------------------------------|----------|-----------------------------------------|-----------|---------|
| PART NAME | NEMA 4X DIE CAST ALUMINUM ENCLOSURE | PART No. | AN-1300, AN-1300-G, AN-2800 & AN-2800-B | REV. DATE | 12-6-07 |
|-----------|-------------------------------------|----------|-----------------------------------------|-----------|---------|



SECTION "C-C"  
\* DIMENSIONS ARE AT  
BOTTOM OF ENCLOSURE



BODY




COVER

MATERIAL: ALUMINUM ALLOY #ADC-12

FINISH: NATURAL (NO SUFFIX)  
GRAY (SUFFIX -G)  
SMOOTH BLACK (SUFFIX -B)

NOTES:

- 1) FOUR (4) M3 x 10mm (0.393") LG. SCREWS SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
- 2) ALL HOLE DIAMETERS HAVE  $\pm 0.005$  TOLERANCE  
ALL OTHER DIMENSIONS HAVE  $\pm 0.015$  TOLERANCE



PART NO. AN-2800 & AN-2800-B  
ARE SUPPLIED WITH A WELDED  
ON MOUNTING BRACKET ONLY.