

Miniature Fuse, 6.3 x 32 mm, Super-Time-Lag TT, NNO, 220 VAC



220 VAC · Super-Time-Lag TT



NNO

Description


- Low Breaking Capacity

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

Rated Voltage	32 - 220 VAC
Rated Current	1.6 - 30 A
Breaking Capacity	100 A
Characteristic	Super-Time-Lag TT
Mounting	Fuseholder / Clip
Admissible Ambient Air Temp.	-40 °C to 85 °C
Climatic Category	40/085/56 acc. to IEC 60068-1
Material: Tube	Glass
Unit Weight	1.5 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	TD3AG, Current, Characteristic

Dimensions**Pre-Arcing Time**

Rated Current In	1.1 x In min.	1.45 x In max.	2.0 x In min.	2.0 x In max.	3.0 x In min.	3.0 x In max.	5.0 x In min.	5.0 x In max.
1.6 A - 30 A	60 min	60 min	12 s	30 s	4 s	9 s	1 s	4 s

Variants

Rated Current [A]	Rated Voltage [VAC]	Breaking Capacity	Voltage Drop 1.0 In typ. [mV]	NNO	Order Number
1.6	220	1)	620	●	7045.1110
2	220	1)	470		7045.1120
2.5	220	1)	470	●	7045.1130
3.15	220	1)	370	●	7045.1140
4	220	1)	290		7045.1150
5	220	1)	320		7045.1160
6.3	220	1)	230	●	7045.1170
8	220	1)	170	●	7045.1180
10	220	1)	180	●	7045.1190
12.5	220	1)	120	●	7045.1210
16	220	1)	130	●	7045.1230
20	32	1)	80		7045.1310
25	32	1)	70		7045.1410
30	32	1)	40		7045.1420

1) 100 A @ 220 VAC

Packaging Unit

Small Box Pack (10 pcs.)

Time-Current-Curves

