




LOC		DIST		REV		REVISIONS		DATE	APPD
AJ	16	P	F	ZONE	LTR	DESCRIPTION			
✓	✓			Y		REVISED AND REDRAWN PER AJ-40408-29-89		02/02/89	JPD
✓	✓			Z		OBS -4 PER AJ-3015			

- 1 BRASS PER QQ-B-626
- 2 BRASS PER MIL-C-50
- 3 POLYPROPYLENE, GENERAL PURPOSE.
- 4 GOLD PLATE PER MIL-G-45204, .000030 MIN THK.
- 5 TIN-LEAD PLATE PER ASTM-B-545
- 6. FOR USE WITH .062 MAX PRINTED CIRCUIT BOARD.
- 7. SEE I.S. 1204.



OBsolete	5	50084-4
	4	50084-1
SHELL FINISH		PART NUMBER

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± .01 3 PLC DEC ± .008 ANGLES ± MATERIAL		DR J.L. GROFT CHK S.J. MAGARO APPD M. SNEED M. SNEED PRODUCT SPEC 108-12081	6-30-89 9-28-89 1-16-90 1-16-90	NAME	SIZE FSCH NO DRAWING NO C 00779 50084	
FINISH A B C		APPLICATION SPEC	WEIGHT	SCALE 10:1	SHEET 1 OF 1	

AMP
AMP INCORPORATED
Merrillburg, Pa. 17105

SOCKET, PCB, SPRING
LATCH, MINIATURE