


防水ワッシャー

WATERPROOF WASHERS





PAT.PEND.

C-1029-WP



使用例
Example of application

ワッシャー内の樹脂が筐体に密着し確実に防水
Resin inside the washer is contacted tightly with the cabinet, providing a secure watertight seal.



C-1029-WP

ステンレス製

特 徴 Feature

- ボルトを締込むとワッシャー内のブッシュがパネルに密着し、確実に防水します。
- コーキング等の作業が省けます。
- The bushing in the washer contacts the panel tight as the bolt is tightened and watertightness is provided securely.
- Calking can be skipped.

仕 様 ● 材 質: キャップ/ステンレス鋼板(SUS304)
ブッシュ/エラストマー(TPE)

納 期 ● 標準在庫品
備 考 ● 均一に締込むため、防水ワッシャーとねじ頭の間に平座金を追加することをお奨め致します。
● 締結部材の材質、板厚、締結方法(ナット止め、タップ等)及び取付け環境により条件が異なります。締付トルクは参考数値に基づいて実装検証のうえ決定ください。

Specifications ● Material: Cap: Stainless steel plate (SUS304)
Remarks Bushing: Elastomer (TPE)

- For even tightening, a plain washer between the waterproof washer and the head of the screw is recommended.
- Conditions depend on the material of the workpiece being fastened, panel thickness, fastening method (notted, tapped, etc.), and installation environment. Decide on tightening torque after verifying an actual installation based on the reference values.

C-1029-WP 参考締込トルク表

C-1029-WP Reference tightening torque table

ねじサイズ Thread size	T系列締込トルク[N・m] T-series tightening torque [N・m]	0.5T系列締込トルク[N・m] 0.5T-series tightening torque [N・m]
M3	0.634	0.317
M4	1.48	0.738
M5	2.98	1.49
M6	5.07	2.53
M8	12.3	6.15
M10	24.4	12.2
M12	42.5	21.2
M16	106	52.8
M20		103

T系列: 締込部材 鉄、SUSなど

0.5T系列: 締込部材 銅、アルミ、樹脂など

商品番号 Product No.	RoHS	CAD	φD1	φD2	H1	H2	製品質量(g) Mass	コード Code	単 価 Price	量販価格 Bulk Price 数量 Quantity 単価 Price
C-1029-WP-M3	●	2D	3	8	3.1	2.5	0.4	24782	¥35	100個～ ¥34
C-1029-WP-M4	●	2D/3D	4.1	10	3.5	3	0.6	22833	¥35	100個～ ¥34
C-1029-WP-M5	●	2D/3D	5.1	12	3.5	3	1	21739	¥35	100個～ ¥34
C-1029-WP-M6	●	2D/3D	6.1	14	3.5	3	1	21740	¥38	100個～ ¥36
C-1029-WP-M8	●	2D/3D	8.1	18	4	3	2	21741	¥40	100個～ ¥38
C-1029-WP-M10	●	2D/3D	10.1	23	4	3	3	21742	¥40	100個～ ¥38
C-1029-WP-M12	●	2D/3D	12.1	25	4	3	4	21743	¥43	100個～ ¥41
C-1029-WP-M16	●	2D/3D	16.1	30	4.5	3	6	22858	¥80	100個～ ¥77
C-1029-WP-M20	●	2D/3D	20.1	37	4.5	3	9	22859	¥100	100個～ ¥96

●: RoHS指令対応品

▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。

ファスナー
ラッチ錠・キャッチ
錠前装置・周辺機器

C

ファスナー

ラッチ錠

ドア
キャッチスナッチ
ロックコントロール
センター太陽光
関連金具グレーチング
ロック工業用
錠前電磁波
対策

パッシブ