



Black 

Duroplast




PA 6.6




ABS




I



II



III



THE PRODUCT

The comprehensive range of boxes for potting electronic assemblies. With special cost advantages for series-type production.

Potted assemblies are protected from shock as well as temperature, dampness and chemical influences. The versions made of Duroplast are not highly resistant to fracture.

YOUR ADVANTAGE

Duroplast

Resistant to deformation and extreme temperatures.

Polyamide 6.6

Good value for money. High-impact.

ABS

Good value for money. Preferably for potting small assemblies.

APPLICATIONS

For protecting and potting electronic assemblies.

ENCLOSURES*1

POTTING BOXES	Outside dim. in mm			Wall-thickness in mm	Version	Part-No.	
	L	W	H			case	lid
Duroplast	20	20	13.1	0.85	I	A 80 20 130	—
	25	25	14.8	0.8	I	A 80 25 150	—
	25	25	25	0.8	I	A 80 25 251	—
	30.2	20.15	15.1	0.95	I	A 80 30 150	A 81 30 200
	40.5	13.8	16.1	1.1	I	A 80 40 160	A 81 40 130
	40.2	13.55	25	0.85	I	A 80 40 250	A 81 40 130
	40	40	12.8	1.0	I	A 80 40 130	A 81 40 400
	40.2	40.2	20	1.0	I	A 80 40 200	A 81 40 400
	45.1	30.1	15	1.15	I	A 80 45 150	A 81 45 300
	45.1	30	24.9	1.1	I	A 80 45 250	A 81 45 300
	49.9	13.1	15	1.0	I	A 80 50 150	—
	50.15	50.15	15.1	1.3	I	A 80 50 160	A 81 50 500
	50.1	50.1	25.1	1.3	I	A 80 50 250	A 81 50 500
	50.7	50.7	49.7	1.7	I	A 80 50 500	A 81 50 500
	70	50.4	20	1.4	I	A 80 70 200	A 81 70 500
	70.6	50.4	35	1.4	I	A 80 70 350	A 81 70 500
	90.3	60.3	20	1.6	I	A 80 90 200	—
	100.1	50.2	24.8	1.5	I	A 80 10 250	—
	100.0	100.0	40	1.8	I	A 80 10 400	—
PA 6.6	14	14	11.5	0.7	II	case	
	17.4	15	10.5	0.7	III	A 80 14 118	
	17.4	15	15.3	0.6	II	A 80 17 108	
	18.6	18.6	13.7	0.6	III	A 80 17 158	
	20.8	20.8	12.6	0.8	III	A 80 18 138	
	21.3	13.3	17.7	0.9	III	A 80 20 128	
	22.4	22.4	14	0.8	III	A 80 21 178	
	26.4	26.4	35.2	1.1	III	A 80 22 148	
	29	29	19.2	1.0	III	A 80 26 358	
	30.3	30.3	50.3	1.5	III	A 80 29 198	
	32.4	32.4	20	1.0	III	A 80 30 508	
	38.8	38.8	26.6	1.2	II	A 80 32 208	
	38.9	38.9	38.8	1.2	II	A 80 39 268	
	40	10	20.2	1.0	II	A 80 39 398	
	46.2	46.2	40.8	1.1	III	A 80 40 208	
	46.2	46.2	40.8	1.1	III	A 80 46 408	
ABS	12.3	12.3	15.3	1.0	III	A 80 12 159	
	21.2	21.2	12.1	1.0	III	A 80 21 129	
	25.3	25.3	15.2	1.0	III	A 80 25 159	
	38.3	20.4	20.2	1.0	III	A 80 38 209	
	45.5	30.5	15.7	1.2	III	A 80 45 169	
	67.5	35.8	46.3	1.7	III	A 80 67 469	

*1 cases supplied bulk packed