


LOC	DIST	REVISIONS					DATE	DWN	APVD
GW	-	P	LTR	DESCRIPTION					
		A1		REVISED PER ECO-11-005294			06APR11	RK	HMR



6) Application : DIN 41612 type M.


5 Only on 1-1393589-1

4 Not applicable on 1393589-7

3 Measured with spring moved towards the mating face

2 Max dimension

1 Min dimension



Cross reference table


Old part number	part number	Current	ϕa	ϕb	dim c	Material	Plating
1-1393589-1	C42334-A347-A96	10 A	1.7	2.6	3	Brass	1 μ m Au or Pd in contact area
1393589-9	C42334-A347-A95	20 A	2.8	3.7	4	Brass	1 μ m Au or Pd in contact area
1393589-7	C42334-A347-A94	40 A	4.8	5.6	5.2	Brass	1 μ m Au or Pd in contact area

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm$
1 PLC $\pm$
2 PLC $\pm$
3 PLC $\pm$
4 PLC $\pm$
ANGLES $\pm$



DWN

B. Lenvain

23APR2001

CHK

K. Mattheeuws

23APR2001

APVD

R. Leeman

23APR2001

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

MATERIAL

-

FINISH

-



TE Connectivity

NAME

High current socket
with wire connection

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-1393589-7

-

SCALE

5/1

SHEET

1

OF

1

REV

A1