



Low Energy Jet-Light 36 Watt spotlight

Robust, compact and powerful worklamp.

- Perfect for tradesmen and advanced DIY workers.
- Can be used in three positions - standing, suspended or lying flat.
- Compact for carrying purposes.
- Robust, shockproof housing with protective enclosure made of polycarbonate.
- Stable, adjustable base.
- 2 x 18 W energy-saving, longlife lamps included.
- Very bright light equivalent to a 200 W bulb.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Output	Fittings	Voltage
1 17256 3 110	166145	1	5 m	H05VV-F 2x1,0	2 x 18 W	2G11	110 V

Available while stocks last!

Recommended accessories:

Article No.	EAN-Code 4007123...	UP	Description	Output	Fittings
1 17747 0 110	596423	1	Replacement compact light	18 W	2G11



Power Jet-Light ELP 55 spotlight

For use indoors and outdoors.

- Perfect for tradesmen and advanced DIY workers.
- Electronic ballast for energy efficiency, flicker-free light and minimum heat output.
- Very bright light.
- Water-jet protected socket outlets with self-closing protective caps.
- ON/OFF switch.
- Robust, break- and impact-resistant plastic housing with rubberized wrap for additional shock protection. Cover made from break resistant polycarbonate.
- Adjustable folding stand, also suitable for mounting on a tripod.
- With special rubber cable.
- 55 W bulb included.



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Output	Fittings	Voltage	Sockets
1 17272 3	592623	1	1,8 m	H07RN-F 3G1,5	55 W	GR10q	240 V	2
1 17272 3 110	592630	1	1,8 m	H07RN-F 3G1,5	55 W	GR10q	110 V	2

Recommended accessories:

Article No.	EAN-Code 4007123...	UP	Description	Output	Luminous flux	Lamp efficacy	Colour temperature	Colour rendering index	Fittings	Mercury content	Energy efficiency class
1 17765 0	210206	1	Jet-Light bulb	55 W	3600 lm	66 lm/W	6400 K	80	GR10q	5 mg	B