

Data sheet

770-233

PLUG WITHOUT RELIEF HOUSING
PIN SPACING 10 MM / 0.394 IN 100% PROTECTED AGAINST MISMATING CAGE
CLAMP S CONNECTION



Technical data

Package size 100 pieces.

pole count	3
Cross section from [mm ²]	0.5 mm ²
Cross section to [mm ²]	4 mm ²
Cross section from [AWG]	20 AWG
Cross section to [AWG]	12 AWG
Number of strands	2
Measured voltage EN	250 V
Measured shock voltage	4 kV
Pollution degree	3
Current intensity EN	25 A
Weight	10.105 g
Color	white
No. of connection Points	6
No. of potentials	3
Height	12.9 mm
Height	0.508 in
Width	30 mm
Width	1.181 in
Depth	37.5 mm
Depth	1.476 in
Strip length from	9 mm
Strip length to	9 mm
Strip length	0.35 in

Data sheet**770-233**

**PLUG WITHOUT RELIEF HOUSING
PIN SPACING 10 MM / 0.394 IN 100% PROTECTED AGAINST MISMATING CAGE
CLAMP S CONNECTION**

Strip length

0.35 in

Data sheet

770-233

PLUG WITHOUT RELIEF HOUSING
PIN SPACING 10 MM / 0.394 IN 100% PROTECTED AGAINST MISMATING CAGE
CLAMP S CONNECTION

Approval	Voltage	Current	Approval number	Notes
CBCertificateVDE	250/400	25	DE1-29543	
CCA	250	25	NL5567	
cURus	600	20	E45171	
DNV	250	25	E6188	
GL	250	25	42875-02HH	
KEMA	250	25	2060958.02	
LR	250	25	02/20050(E1)	

Data sheet

770-233

PLUG WITHOUT RELIEF HOUSING
PIN SPACING 10 MM / 0.394 IN 100% PROTECTED AGAINST MISMATING CAGE
CLAMP S CONNECTION

Accessories

Item number

CODING FINGER FOR PLUG	770-401
FIXING FLANGE MANUALLY OPERATED	770-101
FIXING FLANGE MANUALLY OPERATED	770-121
FIXING FLANGE OPERATED WITH TOOL	770-111
FIXING FLANGE OPERATED WITH TOOL	770-131
SCREWDRIVER WITH PARTIALLY INSULATED SHAFT Type 2, bar (3,5 x 0,5) mm	210-620