

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300530002

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Brad RJ-Lnxx R-J45 110 Punchdown Ethernet Receptacle, with Hex Nut and Bulkhead Gasket, 1" - 14 UNC Threads, 0.056m (2.19") Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Receptacles
Series	130053
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Industrial Ethernet Solutions
Product Name	Brad, RJ-Lnxx
Type	110 Punchdown
UPC	78678846635
Physical	
Coupling Type	External Thread
Gender	Female
Keyway	None
Length	0.056m
Material - Component	ABS
Mounting Thread Size	1" - 14 UNC
Net Weight	0.030/kg
Orientation	Straight
Panel Mount	Front
Poles	N/A
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	125V DC
Material Info	
Engineering Number	ENDR2FB5
Reference - Drawing Numbers	
Sales Drawing	SD-130053-002



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)4578-DC (25 June 2020)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

130053 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION