









TYPICAL APPLICATION

| PART NO.   | PANEL THICKNESS RANGE | MOUNTING HOLE DIAMETER                                                           | "A" REF      | "B" MAX. HOLDING BUNDLE DIA. | "C"±.010 [±0.25] | "D"        |
|------------|-----------------------|----------------------------------------------------------------------------------|--------------|------------------------------|------------------|------------|
| PGSB-0609A | .028-.067 [0.7-1.7]   | .375±.004 [9.5±0.1]                                                              | .450 [11.4]  | .260 [6.6]                   | .26 [6.5]        | .051 [1.3] |
| PGSB-1A    | .031-.125 [0.8-3.2]   | .375±.004 [9.5±0.1]                                                              | .421 [10.7]  | .265 [6.7]                   | .390 [9.9]       | .051 [1.3] |
| PGSB-2A    | .031-.125 [0.8-3.2]   | .437±.004 [11.1±0.1]                                                             | .500 [12.7]  | .312 [7.9]                   | .406 [10.3]      | .063 [1.6] |
| PGSB-1013A | .031-.138 [0.8-3.5]   | .512±.004 [13±0.1]                                                               | .587 [14.9]  | .35 [9]                      | .41 [10.5]       | .059 [1.5] |
| PGSB-3A    | .031-.125 [0.8-3.2]   | .562±.004 [14.3±0.1]                                                             | .640 [16.3]  | .390 [9.9]                   | .406 [10.3]      | .063 [1.6] |
| PGSB-1216A | .028-.130 [0.7-3.3]   | .650±.004 [16.5±0.1]                                                             | .734 [18.6]  | .48 [12.3]                   | .39 [10]         | .039 [1]   |
| PGSB-1316A | .047-.138 [1.2-3.5]   | .630±.004 [16±0.1]                                                               | .709 [18]    | .41 [10.5]                   | .41 [10.5]       | .063 [1.6] |
| PGSB-1519A | .047-.130 [1.2-3.3]   | .748±.004 [19±0.1]                                                               | .811 [20.6]  | .57 [14.5]                   | .43 [11]         | .051 [1.3] |
| PGSB-1822A | .039-.138 [1-3.5]     | .866±.004 [22±0.1]                                                               | .976 [24.8]  | .68 [17.3]                   | .45 [11.5]       | .063 [1.6] |
| PGSB-4A    | .031-.125 [0.8-3.2]   | 1.000 <sup>+.020</sup> <sub>-.005</sub> [25.4 <sup>+.0.5</sup> <sub>-0.1</sub> ] | 1.047 [26.6] | .812 [20.6]                  | .406 [10.3]      | .063 [1.6] |
| PGSB-5A    | .031-.125 [0.8-3.2]   | 1.093 <sup>+.020</sup> <sub>-.005</sub> [27.8 <sup>+.0.5</sup> <sub>-0.1</sub> ] | 1.156 [29.4] | .875 [22.2]                  | .406 [10.3]      | .063 [1.6] |
| PGSB-6A    | .031-.125 [0.8-3.2]   | 1.250 <sup>+.020</sup> <sub>-.005</sub> [31.8 <sup>+.0.5</sup> <sub>-0.1</sub> ] | 1.343 [34.1] | 1.046 [26.6]                 | .406 [10.3]      | .063 [1.6] |
| PGSB-7A    | .031-.125 [0.8-3.2]   | 1.375 <sup>+.020</sup> <sub>-.005</sub> [34.9 <sup>+.0.5</sup> <sub>-0.1</sub> ] | 1.468 [37.3] | 1.171 [29.7]                 | .406 [10.3]      | .063 [1.6] |
| PGSB-8A    | .031-.125 [0.8-3.2]   | 1.500 <sup>+.020</sup> <sub>-.005</sub> [38.1 <sup>+.0.5</sup> <sub>-0.1</sub> ] | 1.578 [40.1] | 1.250 [31.7]                 | .421 [10.7]      | .063 [1.6] |



OPEN



NOTES:  
1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01)  
2. COLOR: BLACK.  
COLOR WHITE, AVAILABLE BY SPECIAL ORDER ONLY.

|      |                             |       |          |
|------|-----------------------------|-------|----------|
| D    | SEE CO 200097 FOR CHANGES   | SK    | 01/04/08 |
| -    | SEE ENGINEERING FOR REV A-C | --    | ----     |
| REV. | DESCRIPTION                 | ENGR. | DATE     |

|                                                                               |                |                                                      |              |            |        |                |            |
|-------------------------------------------------------------------------------|----------------|------------------------------------------------------|--------------|------------|--------|----------------|------------|
| TITLE: <b>SNAP BUSHING OPEN</b>                                               |                |                                                      |              |            |        | DWG IN IN [MM] |            |
| CREATED USING SOLIDWORKS                                                      | FILE #: PGSB-A | DWN: SK                                              | APP: S.K.    | FINAL      |        |                |            |
| TOLERANCES UNLESS NOTED<br>.XX=±.010<br>.XXX=±.005<br>FRAC.=±1/64<br>ANG.=±1° | SHEET: 1 OF 1  | SHEET SIZE: B                                        | DT: 06/14/06 | CHKD: D.Z. | PART # |                | PRINT TYPE |
| RE: RICHCO, INC.                                                              |                | RICHCO, INC.<br>ENG@RICHCO-INC.COM<br>(773) 539-4060 |              | SEE TABLE  |        | CA             |            |