

➡ **Power MOSFET TO-220**

Part No.	BV _{DSS} (V)	R _{DS(ON)} Max(mohm)			I _D (A)	P _D (W)	Application
		V _{GS} @10V	V _{GS} @4.5V	V _{GS} @2.5V			
N-channel							
AP40T03P	25V	25	45		28	31.3	M/B,DC/DC
AP70T03P		9	18		60	53	M/B,DC/DC
AP50L02P		17	35		40	45	M/B,DC/DC,SPS
AP60L02P		12	26		50	62.5	M/B,DC/DC
AP70L02P		9	17		66	66	M/B,DC/DC
AP85L02P		6	10		85	96	M/B,DC/DC
AP88L02P		5	10		88	96	M/B,DC/DC
AP15N03P	30V	80	100		15	28	M/B,DC/DC,Cards
AP20N03P		52	85		20	31	M/B,DC/DC,Cards
AP40N03P		17	23		40	50	M/B,DC/DC,SPS
AP60N03P		13.5	20		55	62.5	M/B,DC/DC,SPS
AP70N03P		9	14		70	68	M/B,DC/DC
AP80N03P		8	12		80	83.3	M/B,DC/DC
AP90N03P		4	5		85	125	M/B,DC/DC
AP630P	200V	400			9	74	CRT,monitor
AP730P	400V	1000			5.5	74	Ballast,monitor, driver
AP2761P	600V	1000			10	90	SPS,Adapter

AP01L60P		12000			1	34	Charger
AP01N60P		8000			1.6	39	Charger
AP02N60P	650V	8000			2	39	Charger
AP03N70P -A		3600			3.3	45	Charger,Adapter
AP04N70BP -A	675V	2400			4	62.5	Charger,Adapter
AP07N70CP -A		1200			7	89	SPS,Adapter
AP09N70P -A	700V	750			9	156	SPS,Adapter
AP03N70P -H		3600			3.3	45	Charger,Adapter
AP04N70BP -H		2400			4	62.5	Charger,Adapter

