



FK28M

Heavy duty penetration probe



Copyright © 2007 Test Products International, Inc.

Application

Heavy duty penetration into
semi-solids and liquids tapered
shaft resist bending

Range°F°C

-58° to 500°F
-50° to 250°C

Probe tip

22

Dimensions

Stem Length: 6.3" (160mm)
Diameter: 0.13" (3.2mm)
Lead Length: 39.4" (1M)

Insulation Material

Polyurethane