


**General ordering data**

Order No.	1792710000
Part designation	IDU 1.5N/ZF BL
Version	Special terminal, special connections, 1.5 mm ² , Insulation displacement connection, Wemid, blue, TS 35
EAN	4032248281725
Qty.	100 pc(s).

Product notes

Note, technical data	Conductor < 0.5mm ² / AWG 24 with IRH 1.5Continuous current of cross-connection: 32A (to power supply)
----------------------	---

PT OKIECEEx/ATEX rating data

EU-type examination certificate	KEMA02ATEX2241U
Download, German	KEMA02ATEX2241U_d.pdf
Download English	KEMA02ATEX2241U_e.pdf
ATEX voltage	275 V
ATEX current	15 A
ATEX conductor cross-section	1.5 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG- Baumusterprüfbescheinigung/IECEx-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	blue
Connection direction	top
End plate required	Yes
Explosion-tested version "Ex e"	Yes
Installation advice	TS 35
Insulating material	Wemid

Additional technical data

Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	1
Open sides	right
Operating temperature range	- 50 °C, + 120 °C
Product family	I-Series
Type of connection	Insulation displacement connection
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	Feed-through terminal

CSA rating data

Voltage (CSA)	300 V
CSA current	10 A
Min. cross-section (CSA)	AWG 24
Max. cross-section (CSA)	AWG 16

Conductors for clamping (additional connection)

Type of connection	Tension clamp connection
Stripping length (B1)	10 mm
Blade size	0.6 x 3.5 mm
Solid, min.	0.5 mm ²
Solid, max.	4 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	4 mm ²
Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	2.5 mm ²
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	0.5 mm ²
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	2.5 mm ²
AWG conductor size, min.	AWG 26
AWG conductor size, max.	AWG 12
AWG conductor size, min.	0.13 mm ²
AWG conductor size, max.	3.31 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.21 mm ²
Clamping range, max.	1.5 mm ²
Type of connection	Insulation displacement connection
Connection direction	top
No. of connections	1
Blade size	0.6 x 3.5 mm
Solid, min.	0.21 mm ²
Solid, max.	1.5 mm ²
Flexible, min.	0.21 mm ²
Flexible, max.	1.5 mm ²
AWG conductor size, min.	AWG 24
AWG conductor size, max.	AWG 16

Conductors for clamping (rated connection)

AWG conductor size, min.	0.21 mm²
AWG conductor size, max.	1.31 mm²

Dimensions

Width	5.1 mm
Height of lowest version	40.5 mm
Length	59.5 mm
Weight	40.5 g
TS 35 offset	33.5 mm

Mounting rail

Installation advice	TS 35
Length	59.5 mm
Standards	IEC 60947-7-1 / IEC 60352-4

Rating data

Rated cross-section	1.5 mm²
Rated voltage	500 V
Rated impulse voltage	6 kV
Rated current	17.5 A
Standards	IEC 60947-7-1 / IEC 60352-4
Pollution severity	3

UL rating data

Voltage (UL)	300 V
Current (UL)	10 A
Min. cross-section (UL)	AWG 24
Max. cross-section (UL)	AWG 16

Approvals

Approvals institutes

**Classifications**

ETIM 2.0	EC000897
ETIM 3.0	EC000897
eClass 4.1	27-14-11-31
eClass 5.0	27-14-11-31
eClass 5.1	27-14-11-31

Similar products

Order No.	Part designation	Version
1806170000	IDU 1.5N/3AN/ZB	Special terminal, special connections, 1.5 mm², Insulation displacement connection, Wemid, dark beige, TS 35
1819480000	IDU 1.5N/3AN/ZB BL	Special terminal, special connections, 1.5 mm², Insulation displacement connection, Wemid, blue, TS 35
1806150000	IDU 1.5N/3AN/ZF	Special terminal, special connections, 1.5 mm², Insulation displacement connection, Wemid, dark beige, TS 35
1819470000	IDU 1.5N/3AN/ZF BL	Special terminal, special connections, 1.5 mm², Insulation displacement connection, Wemid, blue, TS 35
1792730000	IDU 1.5N/ZB	Special terminal, special connections, 1.5 mm², Insulation displacement connection, Wemid, dark beige, TS 35
1792740000	IDU 1.5N/ZB BL	Special terminal, special connections, 1.5 mm², Insulation displacement connection, Wemid, blue, TS 35
1792700000	IDU 1.5N/ZF	Special terminal, special connections, 1.5 mm², Insulation displacement connection, Wemid, dark beige, TS 35