




NUMBER OF POSITIONS	DIMENSION	
	A	B
06	5.08	12.32
08	7.62	14.86
10	10.16	17.40
12	12.7	19.94
14	15.24	22.48
16	17.78	25.02
18	20.32	27.56
20	22.86	30.10
24	27.94	35.18
26	30.48	37.72
28	33.02	40.26
30	35.56	42.80
34	40.64	47.88
40	48.26	55.5
44	53.34	60.85
50	60.96	68.20
60	73.66	80.90
64	78.74	85.98

MATERILA&FINISH
insulator:PBT Glass Fiber<UL94V-0>BLAKC
Contact:Brass
Contact: Tin-Plated Over Nickel
SPECIFICATIONS
Current Rating:1A AV,DC
Voltage Rating:250V AC,DC
Temperature Range:-40°C TO +150°C
Contact Resistance:20mΩ Min
Insulation Resistance:1000mΩ Min
withstanding Voltage:500V AC/Min

UNLESS OTHERWISE SPECIFIED TOLERANCE : X. ±0.20 ANGLES : ±2° X.X ±0.15 X.XX ±0.10 DO NOT SCALE DRAWING		CnC Tech, LLC Industrial Cable and Connector Technology			
		PART NO. 3030-03-XX-0302			
DRAWN BY		SIZE A	UNIT MM	TITLE 2.54/IDC	REV B0
CHECKED BY		SCALE		THIRD ANGLE PROJECTION	PAGE 1 OF 1
APPROVED BY					DATE 2005/07/17
DWG NO.				ITEM NO.	